

Printed-circuit board connector - CCV 2,5/ 6-GSF-5,08GNP26THRR56 - 1799866

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)


PCB headers, nominal current: 12 A, number of positions: 2, pitch: 5.08 mm, color: green, contact surface: Tin, mounting: THR soldering



The figure shows a 6-position version

Your advantages

- ✓ Designed for integration into the SMT soldering process
- ✓ Maximum flexibility when it comes to device design – one header for connectors with different connection technologies
- ✓ Screwable flange for superior mechanical stability
- ✓



Key Commercial Data

| | |
|------------------------|---------------|
| Packing unit | 140 pc |
| Minimum order quantity | 140 pc |
| GTIN | |
| GTIN | 4046356659260 |

Technical data

Dimensions

| | |
|--------------------------|----------|
| Length [l] | 8.6 mm |
| Pitch | 5.08 mm |
| Dimension a | 5.08 mm |
| Height [h] | 12 mm |
| Height | 13 mm |
| Length of the solder pin | 2.6 mm |
| Pin dimensions | 1 x 1 mm |
| Length | 8.6 mm |

Printed-circuit board connector - CCV 2,5/ 6-GSF-5,08GNP26THRR56 - 1799866

Technical data

General

| | |
|----------------------------------|-----------------|
| Range of articles | CCV 2,5/...-GSF |
| Rated voltage (III/3) | 250 V |
| Connection in acc. with standard | EN-VDE |
| Nominal current I _N | 12 A |
| Color | green |
| Number of positions | 2 |

Standards and Regulations

| | |
|----------------------------------|--------|
| Connection in acc. with standard | EN-VDE |
| | CUL |

Environmental Product Compliance

| | |
|------------|---|
| REACH SVHC | Lead 7439-92-1 |
| China RoHS | Environmentally Friendly Use Period = 50 |
| | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |

Approvals


Approvals


Approvals

EAC / cULus Recognized

Ex Approvals

Approval details

| | | |
|-----|---|---------|
| EAC |  | B.01742 |
|-----|---|---------|

| | | | |
|--------------------------------|---|---|-----------------|
| cULus Recognized |  | http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm | E60425-19931011 |
| | D | B | |
| Nominal voltage U _N | 300 V | 300 V | |
| Nominal current I _N | 10 A | 16 A | |

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1799866](#)