

Feed-through header - MDSTBA 2,5/ 8-G BK - 1800742

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




The figure shows a 10-position version of the product

PCB headers, nominal current: 10 A, rated voltage (III/2): 320 V, number of positions: 8, pitch: 5 mm, color: black, contact surface: Tin, mounting: Wave soldering, The article can be aligned to create different nos. of positions! In combination with MVSTB or FKCV plug components, both an MVSTBW (or FKCVW) and an MVSTBR plug (or FKCVR) must be used. Combination with TMSTBP plug components is not possible!

Your advantages

- ✓ Maximum flexibility when it comes to device design – one header for connectors with different connection technologies
- ✓ Easy PCB replacement thanks to plug-in modules
- ✓ Well-known mounting principle allows worldwide use
- ✓ Conductor connection on several levels enables higher contact density



Key Commercial Data

| | |
|--------------|---------------|
| Packing unit | 50 pc |
| GTIN | |
| GTIN | 4055626188317 |

Technical data

Dimensions

| | |
|--------------------------|----------|
| Pitch | 5 mm |
| Length of the solder pin | 3.2 mm |
| Pin dimensions | 1 x 1 mm |

General

| | |
|--|-----------------|
| Range of articles | MDSTBA 2,5/..-G |
| Insulating material group | IIIa |
| Rated voltage (III/2) | 320 V |
| Nominal current I_N | 10 A |
| Flammability rating according to UL 94 | V0 |
| Color | black |

Feed-through header - MDSTBA 2,5/ 8-G BK - 1800742

Technical data

General

| | |
|---------------------|---|
| Number of positions | 8 |
|---------------------|---|

Standards and Regulations

| | |
|--|----|
| Flammability rating according to UL 94 | V0 |
|--|----|

Environmental Product Compliance

| | |
|------------|---|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
| | No hazardous substances above threshold values |

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1800742](#)