

Electronic housing - ME MAX 90 3-3 KMGY VPE1 - 2201339

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Complete housing, length: 99 mm, with vents, Cross connection: DIN rail bus connector, color: light gray, width: 90 mm, height: 114.5 mm, number of positions cross connector: 5

Your advantages

- ✔ Item is from the ME-MAX product range
- ✔ Easy mounting
- ✔ Available in overall widths from 6.2 mm to 90 mm, modular extension is possible
- ✔ Inflammability class V0 according to UL 94
- ✔ Variety of connection technologies
- ✔ Can be mounted on the DIN rail
- ✔ Optional with bus connector for DIN rail mounting as well as power connection system
- ✔ Plug-in connection with screw, spring-cage or fast connection technology
- ✔ DIN rail bus connector as an option
- ✔ Large PCB surface despite compact housing dimensions
- ✔ Large front surface for high-pos. plugs or operating and setting elements
- ✔ The fitted cover is easy to adapt and print
- ✔ Easy module replacement without interrupting the contact chain
- ✔ Transparent front cover can be swiveled
- ✔ Functional earth ground contact as an option
- ✔ Fixed or plug-in connection technology can be combined on up to three connection levels, with different pitches

Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4046356767149

Technical data

General

Housing type	Complete housing
--------------	------------------

Electronic housing - ME MAX 90 3-3 KMGY VPE1 - 2201339

Technical data

General

Housing material	Polyamide
Color (RAL)	light gray (7035)

Ambient conditions

Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)

Dimensions

Length	99 mm
Height	114.5 mm
Width	90 mm
Depth	99 mm

Technical data

Power dissipation without gap	10.4 W
Power dissipation with 20 mm gap	18.9 W
Number of positions	96

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2201339](#)