

Interface module - FLK 20 - 2280019


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



VARIOFACE module, with screw connection and flat-ribbon cable connector, for mounting on NS 32 or NS 35/7.5, with male connector and short and long locking latches for sockets, 20-pos. (separate test socket for each channel)



Key Commercial Data

| | |
|--------------|---|
| Packing unit | 10 pc |
| GTIN |  4 017918 054304 |
| GTIN | 4017918054304 |

Technical data

Dimensions

| | |
|--------|---------|
| Width | 60 mm |
| Height | 50 mm |
| Depth | 58.5 mm |

Ambient conditions

| | |
|---|------------------|
| Ambient temperature (operation) | -20 °C ... 50 °C |
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |

General

| | |
|---------------------------------|----------------------|
| Max. perm. operating voltage | < 50 V AC 60 V DC |
| Max. perm. current (per branch) | 1 A |
| Number of positions | 20 |
| Status display | No |
| Mounting position | any |

Connection data for connection 1

| | |
|----------------------------------|----------------|
| Connection name | PCB connection |
| Connection in acc. with standard | IEC / EN |

Interface module - FLK 20 - 2280019

Technical data

Connection data for connection 1

| | |
|----------------------------------|---|
| Connection method | Screw connection |
| Stripping length | 8 mm |
| Screw thread | M3 |
| Conductor cross section solid | 0.2 mm ² ... 4 mm ² |
| Conductor cross section flexible | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross section AWG | 24 ... 12 |

Standards and Regulations

| | |
|-----------------------|--------------|
| Standards/regulations | IEC 60664 |
| | DIN EN 50178 |
| Degree of pollution | 2 |
| Overvoltage category | II |

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2280019](#)