

## Conductor marker carrier - PATG 3/18 - 0820536

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 4 ... 7 mm, lettering field size: 18 x 4 mm

### Your advantages

- ✓ The corresponding UC-WMT ..., US-WMT ..., UCT-WMT ... and EMT ... insert labels are used for marking
- ✓ The PATG ... collar is a captive marker carrier
- ✓ These conductor marking systems consist of marker carriers and insert labels
- ✓ Can be used to mark conductors with a diameter of 0.6 ... 50 mm

### Key Commercial Data

Packing unit	500 pc
Minimum order quantity	500 pc
GTIN	 4 046356 294829
GTIN	4046356294829

### Technical data

#### Dimensions

Length (b)	18 mm
Width (a)	7.5 mm
Cable diameter	4 mm ... 7 mm

#### Ambient conditions

Ambient temperature (operation)	-50 °C ... 80 °C
---------------------------------	------------------

#### General

Color	transparent
Type	Profile
Components	Silicone-free
Flammability rating according to UL 94	V0

# Conductor marker carrier - PATG 3/18 - 0820536

## Technical data

### General

Material	PVC
RoHS compliant	Yes
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Marking mounting type	slide-on
Min. cross section	4 mm <sup>2</sup>
Max. cross section	7 mm <sup>2</sup>

### Standards and Regulations

Flammability rating according to UL 94	V0
--	----

## Classifications

### eCl@ss

eCl@ss 10.0.1	27400401
eCl@ss 4.0	27061700
eCl@ss 4.1	27061700
eCl@ss 5.0	27400400
eCl@ss 5.1	27400400
eCl@ss 6.0	27149100
eCl@ss 7.0	27149153
eCl@ss 8.0	27400401
eCl@ss 9.0	27400401

### ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC002248
ETIM 6.0	EC001530
ETIM 7.0	EC001530

### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[0820536](#)