

Pipeline markers - PML-T109 (52X560)R CUS - 1014266

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Pipeline markers, can be ordered: by line, brown/black, labeled according to customer specifications: Non-flammable liquids, mounting type: adhesive, diameter: 0 mm, lettering field size: 52 x 560 mm




Your advantages

- Group 9 (non-combustible liquids)



Key Commercial Data

| | |
|--------------|---|
| Packing unit | 1 pc |
| GTIN |  4 046356 784726 |
| GTIN | 4046356784726 |

Technical data

Dimensions

| | |
|------------|---------|
| Length (b) | 52 mm |
| Width (a) | 560 mm |
| Height (c) | 52 mm |
| Diameter | 0.00 mm |

Ambient conditions

| | |
|---------------------------------|---|
| Ambient temperature (operation) | -40 °C ... 150 °C |
| Recommended storage conditions | 23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended. |

General

| | |
|-----------------|-----------------------------|
| Color | brown/black |
| Type | Rectangle |
| Components | Silicone-free |
| Material | Polyester |
| RoHS compliant | Yes |
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |

Pipeline markers - PML-T109 (52X560)R CUS - 1014266

Technical data

General

| | |
|---|-------------------------------------|
| Printing | Non-flammable liquids |
| Number of individual labels per row | 1 |
| Adhesive | Acrylic |
| Test for substances that would hinder coating with paint or varnish | VW PV 3.10.7:2005-02 |
| Result | Test passed |
| Test specification weathering-resistance | Following ISO 4892-2:2013-03 |
| Test duration | 96 h |
| Result of weather resistance test | Test passed |
| Salt spray test specification | DIN EN 60068-2-11:2000-02 |
| Procedure | A |
| Test duration | 96 h |
| Salt spray testing result | Test passed |
| Wipe resistance of test specification inscriptions | DIN EN 61010-1 (VDE 0411-1):2011-07 |
| Result of wipe resistance test | Test passed |
| Foil strength | 50 µm |
| Adhesive strength | 46 µm |
| Marking mounting type | adhesive |

Standards and Regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

Classifications

eCl@ss

| | |
|---------------|----------|
| eCl@ss 10.0.1 | 40200202 |
| eCl@ss 4.0 | 40200100 |
| eCl@ss 4.1 | 40200100 |
| eCl@ss 5.0 | 40200100 |
| eCl@ss 5.1 | 27371300 |
| eCl@ss 6.0 | 40200100 |
| eCl@ss 7.0 | 40200103 |
| eCl@ss 8.0 | 40200202 |
| eCl@ss 9.0 | 40200202 |

ETIM

| | |
|----------|----------|
| ETIM 3.0 | EC000712 |
| ETIM 4.0 | EC002498 |
| ETIM 5.0 | EC001777 |
| ETIM 6.0 | EC001777 |
| ETIM 7.0 | EC001777 |

Pipeline markers - PML-T109 (52X560)R CUS - 1014266

Classifications

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 43172501 |
| UNSPSC 7.0901 | 43212107 |
| UNSPSC 11 | 43172501 |
| UNSPSC 12.01 | 43212107 |
| UNSPSC 13.2 | 55121718 |
| UNSPSC 18.0 | 55121718 |
| UNSPSC 19.0 | 55121718 |
| UNSPSC 20.0 | 55121718 |
| UNSPSC 21.0 | 55121718 |

Accessories

Accessories

Ink ribbon

Ink ribbon - TM-RIBBON 110 WH 101 - 1099966



Ink ribbon, For THERMOMARK roll printers for printing the product group material off the roll: PML-T..., width: 110 mm, color: white

Warning label printed

Hazardous substances label - PML-GHS102 (25X25) - 1014272



Hazardous substances label, Sheet, red/white, labeled: Flammable, mounting type: adhesive, diameter: 0 mm, lettering field size: 25 x 25 mm, Number of individual labels: 4

Hazardous substances label - PML-GHS103 (25X25) - 1014274



Hazardous substances label, Sheet, red/white, labeled: Oxidizing, mounting type: adhesive, diameter: 0 mm, lettering field size: 25 x 25 mm, Number of individual labels: 4

Pipeline markers - PML-T109 (52X560)R CUS - 1014266

Accessories

Hazardous substances label - PML-GHS105 (13X13) - 1014277



Hazardous substances label, Sheet, red/white, labeled: Corrosive, mounting type: adhesive, diameter: 0 mm, lettering field size: 13 x 13 mm, Number of individual labels: 35

Hazardous substances label - PML-GHS105 (25X25) - 1014278



Hazardous substances label, Sheet, red/white, labeled: Corrosive, mounting type: adhesive, diameter: 0 mm, lettering field size: 25 x 25 mm, Number of individual labels: 4

Hazardous substances label - PML-GHS106 (25X25) - 1014280



Hazardous substances label, Sheet, red/white, labeled: Toxic, mounting type: adhesive, diameter: 0 mm, lettering field size: 25 x 25 mm, Number of individual labels: 9

Hazardous substances label - PML-GHS107 (25X25) - 1014282



Hazardous substances label, Sheet, red/white, labeled: Irritant, mounting type: adhesive, diameter: 0 mm, lettering field size: 25 x 25 mm, Number of individual labels: 9

Hazardous substances label - PML-GHS109 (13X13) - 1014285



Hazardous substances label, Sheet, red/white, labeled: Hazardous to the environment, mounting type: adhesive, diameter: 0 mm, lettering field size: 13 x 13 mm, Number of individual labels: 35

Pipeline markers - PML-T109 (52X560)R CUS - 1014266

Accessories

Hazardous substances label - PML-GHS109 (25X25) - 1014286



Hazardous substances label, Sheet, red/white, labeled: Hazardous to the environment, mounting type: adhesive, diameter: 0 mm, lettering field size: 25 x 25 mm, Number of individual labels: 9

Warning label unprinted

Hazardous substances label - US-PML-GHS100 (13X13) - 1014287



Hazardous substances label, Card, red/white, pre-printed, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: adhesive, diameter: 0 mm, lettering field size: 13 x 13 mm, Number of individual labels: 50

Hazardous substances label - US-PML-GHS100 (25X25) - 1014288



Hazardous substances label, Card, red/white, pre-printed, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: adhesive, diameter: 0 mm, lettering field size: 25 x 25 mm, Number of individual labels: 9

Hazardous substances label - PML-GHS100 (13X13)R - 1014289



Hazardous substances label, Roll, white/red, pre-printed, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 13 x 13 mm, Number of individual labels: 500

Hazardous substances label - PML-GHS100 (25X25)R - 1014290



Hazardous substances label, Roll, white/red, pre-printed, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 25 x 25 mm, Number of individual labels: 500

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1014266](#)