

# Network cable - VS-OE-OE-94A/300,0 - 1403664

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Network cable, Ethernet CAT5 (1 Gbps), 8-position, PUR, water blue RAL 5021, shielded, free cable end, on free cable end, cable length: 300 m



Ethernet

## Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4046356662857

## Technical data

### Dimensions

Length of cable	300 m
-----------------	-------

### General data

Rated voltage	30 V AC
	30 V DC
Number of positions	8
Signal type/category	Ethernet CAT5 (IEC 11801), 1 Gbps
Transmission characteristics (category)	CAT5

### Cable

Cable type	Ethernet
Cable type (abbreviation)	94A
UL AWM style	20549 (80°C/300 V)
Signal type/category	Ethernet CAT5 (IEC 11801), 1 Gbps
Cable structure	4x2xAWG24/1; SF/UTP
Conductor cross section	4x 2x 0.25 mm <sup>2</sup>
AWG signal line	24
Conductor structure signal line	1x 0.50 mm
Core diameter including insulation	1.1 mm ±0.05 mm

# Network cable - VS-OE-OE-94A/300,0 - 1403664

## Technical data

### Cable

Wire colors	white/blue-blue, white/orange-orange, white/green-green, white/brown-brown
Twisted pairs	2 cores to the pair
Overall twist	4 pairs for core
Shielding	Aluminum-lined polyester foil, tinned copper braided shield
Optical shield covering	85 %
External sheath, color	water blue RAL 5021
Outer sheath thickness	0.4 mm
External cable diameter D	6.4 mm ±0.2 mm
Smallest bending radius, fixed installation	30 mm
Smallest bending radius, movable installation	60 mm (for installation)
Tensile strength GRP	80 N
Outer sheath, material	PUR
Material conductor insulation	PE
Conductor material	Bare Cu wire
Insulation resistance	≥ 5 GΩ*km
Conductor resistance	< 93.8 Ω/km
Cable capacity	< 56 nF/km < 1600 pF/km (Pair-Ground)
Signal speed	0.6 c
Signal runtime	5.7 ns/m
Nominal voltage, cable	72 V DC 300 V AC (in acc. with UL)
Test voltage Core/Core	2500 V DC
Flame resistance	According to FT-2
Halogen-free	According to IEC 60754-2
Resistance to oil	according to IEC 60811-2-1
Ambient temperature (operation)	-40 °C ... 80 °C
Ambient temperature (installation)	0 °C ... 50 °C


### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

### Drawings

# Network cable - VS-OE-OE-94A/300,0 - 1403664

Cable cross section



Ethernet [94A]

## Classifications

eCl@ss

eCl@ss 10.0.1	27060390
eCl@ss 4.0	24010400
eCl@ss 4.1	24010400
eCl@ss 5.0	19030300
eCl@ss 5.1	19030300
eCl@ss 6.0	27061800
eCl@ss 7.0	27061801
eCl@ss 8.0	27061801
eCl@ss 9.0	27061801

# Network cable - VS-OE-OE-94A/300,0 - 1403664

## Classifications

### ETIM

ETIM 3.0	EC000830
ETIM 4.0	EC001855
ETIM 5.0	EC000830
ETIM 6.0	EC000830
ETIM 7.0	EC003249

### UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121413
UNSPSC 11	39121413
UNSPSC 12.01	39121413
UNSPSC 13.2	26121604
UNSPSC 18.0	26121604
UNSPSC 19.0	26121604
UNSPSC 20.0	26121604
UNSPSC 21.0	26121604

## Approvals

### Approvals

---

Approvals

EAC-RoHS

---

Ex Approvals

---

### Approval details

EAC-RoHS		RU D- DE.HB35.B.00385
----------	--	--------------------------

## Accessories

Accessories

## Network cable - VS-OE-OE-94A/300,0 - 1403664

### Accessories

Stripping tool - VS-CABLE-STRIP-VARIO - 1657407



Stripping tool, for the multi-level stripping of shielded cables

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1403664](#)