

Cable feed-through plates - MC-35/37-MULTI-67-PVO-BK - 1415241

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Cable feed-through plates, no. of conductors: 37, length: 222 mm, width: 92 mm, height: 29.5 mm, external cable diameter: 4x 6 mm ... 10 mm , color: black

Your advantages

- Oil-resistant according to UL 157



Key Commercial Data

| | |
|--------------|---|
| Packing unit | 1 pc |
| GTIN |  4 055626 039459 |
| GTIN | 4055626039459 |

Technical data

Dimensions

| | |
|---------------------------------|---------------------|
| Length | 222 mm |
| Width | 92 mm |
| Height | 29.5 mm |
| Drill hole distance, horizontal | 62 mm |
| Drill hole distance, vertical | 194 mm |
| External cable diameter | 4x 6 mm ... 10 mm |
| | 14x 8 mm ... 12 mm |
| | 16x 10 mm ... 14 mm |
| | 2x 12 mm ... 18 mm |
| | 1x 17 mm ... 32 mm |

Ambient conditions

| | |
|---------------------------------|--|
| Degree of protection | IP66 (Minimum sheet thickness \geq 2.5 mm) |
| | IP67 (Minimum sheet thickness \geq 2.5 mm) |
| Ambient temperature (operation) | -40 °C ... 100 °C |

Cable feed-through plates - MC-35/37-MULTI-67-PVO-BK - 1415241

Technical data

General

| | |
|--|---|
| No. of conductors | 37 |
| Material | TPE-SEBS |
| | galvanized sheet steel () |
| Flammability rating according to UL 94 | V0 |
| Color | black |
| Torque | 1.5 Nm ... 2 Nm (Mounting screws) |
| Note | incl. mounting screws |
| | 2 mm thick coated, galvanized sheet steel |
| Installation instructions | M8 mounting screw, torque: 1.5 - 2.0 Nm, SW5 Allen key |
| | The mounting screws included should be used for assembly. Assembly steps: 1) Fix Multigates with the mounting screws provided (observe torque) 2) Make a hole in the membrane (with a screwdriver) or cut off the tip of the cone 3) Guide the cable through the opening (from the outside). Withdraw the cable approximately 20 mm (to improve strain relief). |

Standards and Regulations

| | |
|--|----|
| Flammability rating according to UL 94 | V0 |
|--|----|


Environmental Product Compliance

| | |
|------------|---|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
| | No hazardous substances above threshold values |

Drawings

Cable feed-through plates - MC-35/37-MULTI-67-PVO-BK - 1415241


Dimensional drawing



Dimensional drawing

Cable feed-through plates - MC-35/37-MULTI-67-PVO-BK - 1415241

Dimensional drawing



Wall cutout drawing

Classifications

eCl@ss

| | |
|---------------|----------|
| eCl@ss 10.0.1 | 27400569 |
| eCl@ss 4.0 | 23110100 |
| eCl@ss 4.1 | 23110100 |
| eCl@ss 5.0 | 23110100 |
| eCl@ss 5.1 | 23110100 |
| eCl@ss 6.0 | 27409200 |
| eCl@ss 7.0 | 27409208 |
| eCl@ss 8.0 | 27409208 |
| eCl@ss 9.0 | 27400569 |

ETIM

| | |
|----------|----------|
| ETIM 5.0 | EC001004 |
| ETIM 6.0 | EC001004 |
| ETIM 7.0 | EC001004 |

Approvals

Approvals

Cable feed-through plates - MC-35/37-MULTI-67-PVO-BK - 1415241


Approvals

Approvals

EAC-RoHS

Ex Approvals

Approval details

| | | |
|----------|---|--------------------------|
| EAC-RoHS |  | RU D- DE.HB35.B.00387 |
|----------|---|--------------------------|

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1415241](#)