

FO connecting cable - FOC-HCS-GI-1005/M12-C/SCRJ/5 - 1416651

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



FO connecting cable, degree of protection: IP65/IP67, number of positions: 2, connection method: M12 circular connector

PCF-GI cable, assembled with M12 connector to SC-RJ

Product Description

PCF-GI cable, assembled with M12 connector to SC-RJ

Your advantages

- ✓ 2.2 mm individual wires made from polyvinyl chloride (PVC)
- ✓ Assembled patch cable with test report
- ✓ M12-OPTIC with recessed ferrules to protect against damage
- ✓ optimized polishing for even better attenuation values
- ✓ Rugged installation cable for indoor use
- ✓ Gradient index fiber for maximum performance requirements in terms of transmission bandwidth
- ✓ Rugged polyurethane (PUR) outer sheath
- ✓ Highly tear-resistant aramid strain relief elements
- ✓ Pin connector pattern in accordance with DIN/IEC 61754-27
- ✓ Included in PROFINET planning guideline (v1.14)
- ✓ Robust connector, IP65/IP67
- ✓ Can be used in 10/100/1000 Mbps Ethernet systems
- ✓ Halogen-free, ozone, and UV resistant



Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4046356480741

Technical data

Mechanical characteristics

FO connecting cable - FOC-HCS-GI-1005/M12-C/SCRJ/5 - 1416651

Technical data

Mechanical characteristics

Connection method	M12 circular connector
Weight	346.4 g
Flammability rating according to UL 94	V0

Ambient conditions

Ambient temperature (operation)	-20 °C ... 70 °C
	-20 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Degree of protection	IP65
	IP67

Standards and Regulations

Duty cycle testing	suitable for drag chain
Resistance to UV radiation	yes
Impact strength	2 Nm / 10 x
Flammability rating according to UL 94	V0

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Drawings

Dimensional drawing



Classifications

eCl@ss

eCl@ss 4.0	27260700
eCl@ss 4.1	27260700
eCl@ss 5.0	27260700
eCl@ss 5.1	27061000
eCl@ss 6.0	27061000

FO connecting cable - FOC-HCS-GI-1005/M12-C/SCRJ/5 - 1416651

Classifications

eCl@ss

eCl@ss 7.0	27061090
eCl@ss 8.0	27061003
eCl@ss 9.0	27061003

ETIM

ETIM 3.0	EC000034
ETIM 4.0	EC000034
ETIM 5.0	EC001263
ETIM 6.0	EC001263
ETIM 7.0	EC001263

UNSPSC

UNSPSC 6.01	30211832
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	26121607
UNSPSC 18.0	26121607
UNSPSC 19.0	26121607
UNSPSC 20.0	26121607
UNSPSC 21.0	26121607

Accessories

Accessories

Circular connectors (device side)

FO transceiver - SACFO-T-MNNA-M16-650-S - 1416716



M12 FO transceiver, duplex, wavelength: 650 nm for 125 Mbps, for POF and PCF fiber, for PCB mounting, M16 fastening thread, with sealing cap, including I²C interface for transceiver monitoring and management

Data plug

Fiber optic coupling - SACFO-J-MNNA-2 - 1416677



Fiber optics coupling M12, duplex, suitable for all fibers, with wall bracket, IP65 degree of protection

FO connecting cable - FOC-HCS-GI-1005/M12-C/SCRJ/5 - 1416651

Accessories

Fiber optic contact insert - FOC-M12-RS-HCS - 1406422



Replacement ferrule set (10 pcs.) for M12 PCF fiber optic connector (Order No. 1416619)

Spare parts

Fiber optic contact insert - FOC-M12-RS-HCS - 1406422



Replacement ferrule set (10 pcs.) for M12 PCF fiber optic connector (Order No. 1416619)

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1416651](#)