

# RJ45 connector - VS-V1-C-RJ45-MNNA-PG9-8-I-5-S - 1419182

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



RJ45 connector, degree of protection: IP67, number of positions: 8, CAT5 (IEC 11801:2002), material: Zinc die-cast, connection method: IDC connection, connection cross section: AWG 27- 24, color: silver



## Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4046356539555

## Technical data

### Mechanical characteristics

Connection method	IDC connection
Number of slots	1
Minimum external conductor diameter	5 mm
Maximum external conductor diameter	10 mm
Overvoltage category	I
AWG solid min.	27
AWG solid max.	24
Degree of pollution	2
Conductor cross section	0.11 mm <sup>2</sup> ... 0.23 mm <sup>2</sup>
Weight	128.7 g
Flammability rating according to UL 94	V0

### Ambient conditions

Ambient temperature (operation)	-40 °C ... 70 °C
---------------------------------	------------------

### Material data

Housing material	Zinc die-cast
------------------	---------------

### Electrical characteristics

# RJ45 connector - VS-V1-C-RJ45-MNNA-PG9-8-I-5-S - 1419182

## Technical data

### Electrical characteristics

Number of positions	8
Transmission characteristics (category)	CAT5 (IEC 11801:2002)
GRP transmission properties	CAT5 (IEC 11801:2002) CAT5 (IEC 11801:2002)
Rated current	1.75 A
Overvoltage category	I
Degree of pollution	2
Rated voltage (III/3)	72 V (DC)

### Standards and Regulations


Flammability rating according to UL 94	V0
--	----

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

## Drawings

Dimensional drawing



## Classifications

eCl@ss

eCl@ss 10.0.1	27440101
eCl@ss 4.0	27260700

# RJ45 connector - VS-V1-C-RJ45-MNNA-PG9-8-I-5-S - 1419182

## Classifications

### eCl@ss

eCl@ss 4.1	27260700
eCl@ss 5.0	27260700
eCl@ss 5.1	27260700
eCl@ss 6.0	27260700
eCl@ss 7.0	27440101
eCl@ss 8.0	27440101
eCl@ss 9.0	27440101

### ETIM

ETIM 2.0	EC000764
ETIM 3.0	EC001121
ETIM 4.0	EC001121
ETIM 5.0	EC002636
ETIM 6.0	EC002636
ETIM 7.0	EC002636

### UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	39121409
UNSPSC 18.0	39121409
UNSPSC 19.0	39121409
UNSPSC 20.0	39121409
UNSPSC 21.0	39121409

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

---

### Approval details

## RJ45 connector - VS-V1-C-RJ45-MNNA-PG9-8-I-5-S - 1419182

### Approvals

EAC



B.01687

### Accessories

#### Accessories

#### Panel mounting frame

Panel mounting frame set - VS-V1-F-RJ45-MNNA-1-C-S-JJ-S - 1419184



Panel mounting frame set, type: RJ45, IP67, version 1, degree of protection: IP67, number of positions: 8, 1 Gbps, CAT5 (IEC 11801:2002), material: Zinc die-cast, connection method: Coupling

#### Protective cover

Protective covers - VS-V1-C-PC-POBK - 1419183

Protective cover, IP67, plastic version, to cover the contact insert in the RJ45,LC and SC-RJ connector



Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1419182](#)