

Industrial Ethernet Switch - FL SWITCH 4808E-16FX SM ST-4GC - 2891086

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Rack-mount managed Ethernet switch meets IEC 61850-3 and IEEE 1613. Provides eight RJ45 ports at 10/100 Mbps, 16 ST SM fiber ports at 100 Mbps and four gigabit combo ports (10/100/1000 Mbps RJ45 connection; 1000 Mbps fiber optic connection requires 1000 Mbps SFP module).




Your advantages

- Network structure according to IEC 61850
- IEEE 1613

IEC 61850-3

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 981668
GTIN	4046356981668

Technical data

Dimensions

Width	442 mm
Height	44 mm
Depth	375 mm

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)
Air pressure (operation)	57 kPa ... 108 kPa (up to 4850 m above mean sea level)
Air pressure (storage/transport)	57 kPa ... 108 kPa (up to 4850 m above mean sea level)

Interfaces

Interface	Ethernet (RJ45)
No. of ports	8 (RJ45 ports)
Note on the connection method	Auto negotiation and autocrossing

Industrial Ethernet Switch - FL SWITCH 4808E-16FX SM ST-4GC - 2891086

Technical data

Interfaces

Transmission physics	Ethernet in RJ45 twisted pair
Transmission speed	10/100 Mbps
Transmission length	100 m
No. of ports	16 (Single mode)
Transmission physics	Single-mode fiberglass
Transmission speed	100 Mbps (Full duplex)
Transmission length	40 km (typical)
Interface	Ethernet (RJ45/FO combo)
No. of ports	4
Connection method	Combo
Note on the connection method	Auto negotiation and autocrossing (RJ45 interface)
Transmission physics	Ethernet RJ45 (10/100/1000 Mbps) or SFP (1000 Mbps)
Transmission speed	10/100/1000 Mbps

Function

Basic functions	Store and forward switch, Extended Ring and IEEE redundancy, Multicast control, IGMP snooping, trunking, Port and Tagging VLANs, Port and IEEE 802.1x security, SNMP V3 and Https security, SNTP, web customization, user accounts
Redundancy	ERR (Extended ring redundancy)
Status and diagnostic indicators	LEDs: U _{S1} , U _{S2} (redundant voltage supply), link and activity per port

Network expansion parameters

Cascading depth	Network, linear, and star structure: any
Maximum conductor length (twisted pair)	100 m

Supply voltage

Current consumption	476 mA (115 V AC from FL SWITCH 4800E-P5)
Inrush current	19.2 A (48 V DC from FL SWITCH 4800E-P1)

General

Mounting type	Rack mount, includes brackets
Type AX	Block design
Net weight	4488 g

Standards and Regulations

Type of test	Shock in acc. with EN 60068-2-27/IEC 60068-2-27
Test result	30g, 11 ms half-sine shock pulse
Type of test	Vibration resistance in acc. with EN 60068-2-6/IEC 60068-2-6
Test result	5g, 150 Hz, Criterion 3
Noise emission	EN 61000-6-4
Noise immunity	IEC 61850-3, IEEE 1613, EN 61000-6-2: 2005

Environmental Product Compliance

Industrial Ethernet Switch - FL SWITCH 4808E-16FX SM ST-4GC - 2891086

Technical data

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 10;
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 10.0.1	19170401
eCl@ss 4.0	27250500
eCl@ss 4.1	27250500
eCl@ss 5.0	19030100
eCl@ss 5.1	19030100
eCl@ss 6.0	19170100
eCl@ss 7.0	19170106
eCl@ss 8.0	19170106
eCl@ss 9.0	19170106

ETIM

ETIM 3.0	EC000734
ETIM 4.0	EC000734
ETIM 5.0	EC000734
ETIM 6.0	EC000734
ETIM 7.0	EC000734

UNSPSC

UNSPSC 6.01	43172901
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201410
UNSPSC 13.2	43222612
UNSPSC 18.0	43222612
UNSPSC 19.0	43222612
UNSPSC 20.0	43222612
UNSPSC 21.0	43222612

Accessories

Necessary add-on products

Industrial Ethernet Switch - FL SWITCH 4808E-16FX SM ST-4GC - 2891086

Accessories

Power module - FL SWITCH 4800E-P1 - 2891075



Modular power supply for FL SWITCH 48... managed switches. Wide input voltage range 36 V DC to 75 V DC.

Power module - FL SWITCH 4800E-P5 - 2891076



Modular power supply for FL SWITCH 48... managed switches. Wide input voltage range 90 V,AC to 264 V AC and 88 V DC to 300 V DC.

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2891086](#)