

FO patch cable - FOC-FS:A-SC:A-GZ04/1 - 1409857

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Assembled FO cable, zip cord cable, multi-mode fiberglass 62.5/125 µm, OM1, plug: FSMA/SC duplex, degree of protection: IP20, for installation in cable ducts or control cabinets

Your advantages

- ✓ Multi-mode patch cable for indoor installation
- ✓ Ideal for use in distributor systems and for connecting termination devices
- ✓ All components satisfy UL 94, V0
- ✓ 2.8 mm single elements made from halogen-free and flame-retardant material
- ✓ Interferometer tests at every stage of the certification process
- ✓ Excellent mechanical and optical properties
- ✓ Satisfies optical and mechanical industry standards
- ✓ Comprehensively tested according to IEC 61753-122-2 and IEC 61753-1 Cat. C
- ✓ Temperature fluctuation test according to IEC 61300-2-1
- ✓ Vibration test according to IEC 61300-2-1
- ✓ Tensile strength of the cable connection according to IEC 61300-2-5



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 883627
GTIN	4046356883627

Technical data

Mechanical characteristics

Weight	42.9 g
Flammability rating according to UL 94	V0

Ambient conditions

Ambient temperature (operation)	-10 °C ... 60 °C
Ambient temperature (assembly)	-5 °C ... 50 °C

FO patch cable - FOC-FS:A-SC:A-GZ04/1 - 1409857

Technical data

Ambient conditions

Ambient temperature (storage/transport)	-10 °C ... 60 °C
---	------------------

Electrical characteristics

Lateral strength	60 N/cm
------------------	---------

Standards and Regulations

Flame resistance	yes
Halogen-free	According to IEC 60754-2
Flammability rating according to UL 94	V0

Line characteristics

Type of cable	Zip cord
Cable type	Fiberglass
Cable abbreviation	I-V(ZN)H
External cable diameter	2.8 mm (Zip cord)
Wire colors	-
External sheath, color	orange
Wavelength	850, 1300 nm
Transmission medium	Multi-mode fiberglass
Number of fibers	2
Fiber type	Multimode fiberglass 62.5/125 µm
Fiber	62.5/125 µm
Cable, attenuation	3.2 dB/km (at 850 nm); 0.9 dB/km (at 1300 nm)
Outer sheath, material	LSZH
Cable weight	15.80 kg/km
Smallest bending radius, fixed installation	30 mm
Smallest bending radius, movable installation	60 mm
Tensile strength short-term/long-term	600 N
cable layer type	Indoors
Flame resistance	yes
Halogen-free	According to IEC 60754-2

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 10.0.1	27061003
eCl@ss 4.0	24010700

FO patch cable - FOC-FS:A-SC:A-GZ04/1 - 1409857

Classifications

eCl@ss

eCl@ss 4.1	24010700
eCl@ss 5.0	19030500
eCl@ss 5.1	19030500
eCl@ss 6.0	27069200
eCl@ss 7.0	27069202
eCl@ss 8.0	27061003
eCl@ss 9.0	27061003

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC000034
ETIM 5.0	EC001263
ETIM 6.0	EC001263
ETIM 7.0	EC001263

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	26121607
UNSPSC 18.0	26121607
UNSPSC 19.0	26121607
UNSPSC 20.0	26121607
UNSPSC 21.0	26121607

Approvals

Approvals

Approvals
UL Listed

Ex Approvals

Approval details

UL Listed		http://database.ul.com/cgi-bin/XYVV/template/LISEXT/1FRAME/index.htm E308814-20070105
-----------	--	--

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1409857](#)