

# Patch cable - NBC-R4AC1/3,0-94G/R4AC1-BU - 1413162


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Patch cable, degree of protection: IP20, cable length: 3 m, number of positions: 8, 10 Gbps, CAT6<sub>A</sub>



## Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 989978
GTIN	4046356989978

## Technical data

### Cable type

Fixed cable length	3.00 m
Shielded	yes
Conductor structure signal line	6.00 mm +0.2 mm -0.1 mm
AWG signal line	26
Shielding	S/FTP
Insulation resistance	2000 MΩ*km (500 V)
Coupling resistance	30.00 mΩ/m (30 MHz)
Test voltage	1000 V DC (1 minute)
Material wire insulation	PE

### Ambient conditions

Ambient temperature (operation)	-25 °C ... 60 °C (RJ45 connector)
---------------------------------	-----------------------------------

### External sheath

Outer sheath, material	PUR
External sheath, color	water blue RAL 5021

### General

Conductor length	3.00 m
------------------	--------

## Patch cable - NBC-R4AC1/3,0-94G/R4AC1-BU - 1413162

### Technical data

#### General

Nominal voltage $U_N$	48 V
Transmission characteristics (category)	CAT6 <sub>A</sub>
Transmission speed	10 Gbps
Degree of protection	IP20
Insertion/withdrawal cycles	200


#### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

### Drawings


# Patch cable - NBC-R4AC1/3,0-94G/R4AC1-BU - 1413162

Schematic diagram



Connector pin assignment plug RJ45

Dimensional drawing



# Patch cable - NBC-R4AC1/3,0-94G/R4AC1-BU - 1413162

## Classifications

### eCl@ss

eCl@ss 10.0.1	27060308
eCl@ss 4.0	27260700
eCl@ss 4.1	27260700
eCl@ss 5.0	27260700
eCl@ss 5.1	27260700
eCl@ss 6.0	27189200
eCl@ss 7.0	27060308
eCl@ss 8.0	27060308
eCl@ss 9.0	27060308

### ETIM

ETIM 5.0	EC002599
ETIM 6.0	EC001262
ETIM 7.0	EC001262

### UNSPSC

UNSPSC 13.2	26121604
UNSPSC 18.0	26121604
UNSPSC 19.0	26121604
UNSPSC 20.0	26121604
UNSPSC 21.0	26121604

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

---

### Approval details

EAC		19060508
-----	--	----------

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1413162](#)