

Marker strip - SK 10,0 REEL P10 WH CUS - 0825134

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Marker strip, Card, can be ordered: by card, white, labeled according to customer specifications, mounting type: adhesive, for terminal block width: 10 mm, lettering field size: continuous x 10#mm

Your advantages

- The SK labeling range offers self-adhesive marker strips for labeling products that do not have a marker groove
- The markers that are supplied in roll format can be labeled quickly and cost-effectively using THERMOMARK printers
- Labeling service: Phoenix Contact can custom-label SK markers according to your requirements
- The SK labeling range offers self-adhesive marker strips for labeling products that do not have a marker groove



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 355155
GTIN	4046356355155

Technical data

Dimensions

Height (c)	10 mm
------------	-------

Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
Ambient temperature (assembly)	> 15 °C

General

Note	Marking up to max. 25-pos.
Color	white
Type	Label
Components	free from silicone and halogen
Flammability rating according to UL 94	V2
Material	Polyester

Marker strip - SK 10,0 REEL P10 WH CUS - 0825134

Technical data

General

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of marker strips	7
Marking mounting type	adhesive

Standards and Regulations


Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Flammability rating according to UL 94	V2

Environmental Product Compliance

China RoHS	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"
------------	---

Drawings

Schematic diagram



- ① Horizontal
- ② Vertical

Marker strip - SK 10,0 REEL P10 WH CUS - 0825134

Classifications

eCl@ss

eCl@ss 10.0.1	27141137
eCl@ss 4.0	24190200
eCl@ss 4.1	24190200
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137
eCl@ss 9.0	27141137

ETIM

ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761
ETIM 6.0	EC000761
ETIM 7.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131505
UNSPSC 18.0	39131505
UNSPSC 19.0	39131505
UNSPSC 20.0	39131505
UNSPSC 21.0	39131505

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[0825134](#)