

# Marker for terminal blocks - US-TMF 100 CUS - 0829949

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Marker for terminal blocks, can be ordered: by card, white, labeled according to customer specifications, mounting type: snap into universal marker groove, snap into flat marker groove, lettering field size: 104 x 6.6 mm, Number of individual labels: 20




## Your advantages

- The markers, which are supplied as uniform cards, can be labeled quickly, easily, and precisely using the THERMOMARK CARD
- The cards provide space for including function texts
- The perforated marking strips are easy to separate and can be easily fitted
- The US-TMF 100 UniSheet markers are suitable for products with a flat marker groove
- Labeling service: Phoenix Contact can custom-label all UniSheet markers according to your requirements



## Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 609999
GTIN	4046356609999

## Technical data

### Dimensions

Length (b)	6.3 mm
Width (a)	104 mm
Height (c)	0.5 mm

### Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
---------------------------------	------------------

### General

Color	white
Type	flat
Components	Silicone-free
Flammability rating according to UL 94	V0
Material	PVC

# Marker for terminal blocks - US-TMF 100 CUS - 0829949

## Technical data

### General


	PVC
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	20
Number of individual labels per row	1
Marking mounting type	snap into universal marker groove

### Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Flammability rating according to UL 94	V0

## Drawings

Schematic diagram



- ① Horizontal
- ② Vertical

## Marker for terminal blocks - US-TMF 100 CUS - 0829949

### Classifications

#### eCl@ss

eCl@ss 10.0.1	27141137
eCl@ss 4.0	24190200
eCl@ss 4.1	24190200
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137
eCl@ss 9.0	27141137

#### ETIM

ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761
ETIM 6.0	EC000761
ETIM 7.0	EC000761

#### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131505
UNSPSC 18.0	39131505
UNSPSC 19.0	39131505
UNSPSC 20.0	39131505
UNSPSC 21.0	39131505

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[0829949](#)