

Marker for terminal blocks - UC-TMF 16 OG - 0817811

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Marker for terminal blocks, Sheet, orange, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: snap into flat marker groove, for terminal block width: 16 mm, lettering field size: 15.45 x 5.1 mm, Number of individual labels: 32

Your advantages

- Labeling service: Phoenix Contact can custom-label all UniCard markers according to your requirements
- The UC-TMF ... UniCard labeling range includes markers for products with tall and flat marker grooves



Key Commercial Data

| | |
|------------------------|---|
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| GTIN |  4 046356 108133 |
| GTIN | 4046356108133 |

Technical data

Dimensions

| | |
|-----------|-------|
| Width (a) | 16 mm |
|-----------|-------|

Ambient conditions

| | |
|---------------------------------|---|
| Ambient temperature (operation) | -40 °C ... 120 °C |
| Recommended storage conditions | 23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended. |

General

| | |
|--|--------------------------------|
| Color | orange |
| Type | flat |
| Components | free from silicone and halogen |
| Flammability rating according to UL 94 | V2 |
| Material | PA |
| RoHS compliant | Yes |
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |

Marker for terminal blocks - UC-TMF 16 OG - 0817811

Technical data

General

| | |
|---|-------------------------------------|
| Number of individual labels | 32 |
| Number of individual labels per row | 4 |
| Printability | UV LED technology |
| Device | 5147999 BLUEMARK CLED |
| Test for substances that would hinder coating with paint or varnish | VW PV 3.10.7:2005-02 |
| Result | Test passed |
| Salt spray test specification | DIN EN 60068-2-11:2000-02 |
| Test duration | 96 h |
| Salt spray testing result | Test passed |
| Wipe resistance of test specification inscriptions | DIN EN 61010-1 (VDE 0411-1):2011-07 |
| Result of wipe resistance test | Test passed |
| Marking mounting type | snap into flat marker groove |
| Result | Test passed |
| Oxygen index (DIN EN ISO 4589-2) | 28,2% |
| Class I | 3 |
| Class F | 2 |
| R22 | HL 1 - HL 2 |
| R23 | HL 1 - HL 2 |
| R24 | HL 1 - HL 2 |

Standards and Regulations

| | |
|--|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
| Flammability rating according to UL 94 | V2 |

Classifications

eCl@ss

| | |
|---------------|----------|
| eCl@ss 10.0.1 | 27141137 |
| eCl@ss 4.0 | 24190200 |
| eCl@ss 4.1 | 24190200 |
| eCl@ss 5.0 | 27141100 |
| eCl@ss 5.1 | 27141100 |
| eCl@ss 6.0 | 27141100 |
| eCl@ss 7.0 | 27141137 |
| eCl@ss 8.0 | 27141137 |
| eCl@ss 9.0 | 27141137 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000761 |
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |

Marker for terminal blocks - UC-TMF 16 OG - 0817811

Classifications

ETIM

| | |
|----------|----------|
| ETIM 5.0 | EC000761 |
| ETIM 6.0 | EC000761 |
| ETIM 7.0 | EC000761 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11 | 39121410 |
| UNSPSC 12.01 | 39121410 |
| UNSPSC 13.2 | 39131505 |
| UNSPSC 18.0 | 39131505 |
| UNSPSC 19.0 | 39131505 |
| UNSPSC 20.0 | 39131505 |
| UNSPSC 21.0 | 39131505 |

Accessories

Accessories

Magazine

Magazine - P1 UC-MAG 4 - 5146105



Magazine, for CMS-P1-PLOTTER and PLOTMARK, for accommodating UC-TMF..., UC1-TMF..., UC-WMT...

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[0817811](#)