

Printed-circuit board connector - PTF 0,3/ 4-WB-10-H PC1234L150 - 1714995

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Assembled PCB connectors

The figure shows version

Your advantages

- Tool-free fast connection for flexible PCBs
- Small component size for applications where space is at a premium
- Reliable contacting of flexible PCBs, thanks to fixing pin
- Designed and tested according to IEC 60838-2-2
- Approval in accordance with UL 1977 demonstrates electrical safety for use in the North American market



Key Commercial Data

Packing unit	20 pc
GTIN	
GTIN	4055626380827

Technical data

Dimensions

Length [1]	9.00 mm
Pitch	2.40 mm

General

Range of articles	PTF 0,3/...-WB-H
Number of positions	4
Rated voltage (III/2)	24 V
Nominal cross section	0.34 mm ²
Flammability rating according to UL 94	V0

Standards and Regulations

Printed-circuit board connector - PTF 0,3/ 4-WB-10-H PC1234L150 - 1714995

Technical data

Standards and Regulations


Flammability rating according to UL 94	V0
--	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Drawings

Diagram



Type: PTF 0,3/ 2-WB-10-H

Classifications

eCl@ss

eCl@ss 10.0.1	27440309
eCl@ss 4.0	27260700
eCl@ss 4.1	27260700
eCl@ss 5.0	27260700
eCl@ss 5.1	27260700
eCl@ss 6.0	27260700
eCl@ss 7.0	27440309
eCl@ss 8.0	27440309
eCl@ss 9.0	27440309

Printed-circuit board connector - PTF 0,3/ 4-WB-10-H PC1234L150 - 1714995

Classifications

ETIM

ETIM 5.0	EC002638
ETIM 6.0	EC002638
ETIM 7.0	EC002638

Approvals


Approvals


Approvals

UL Recognized / EAC

Ex Approvals

Approval details

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm E118976-20130430
Nominal voltage UN	60 V	
Nominal current IN	5 A	
mm ² /AWG/kcmil	22	

EAC		B.01687
-----	---	---------

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1714995](#)