

Corner inlay - UCS CC 5018 - 2203398

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Corner inlay for UCS housings, material: polyamide, color: turquoise blue, similar to RAL 5018




Your advantages

- Flexible mounting options for the control cabinet and use in the field
- Can be adapted to suit the application, thanks to identical receptacles in the housing
- Different colors for high recognition value inside and outside the control cabinet

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 427942
GTIN	4055626427942

Technical data

Item properties

Type	UCS CC 5018
Order No.	2203398
Housing type	Universal housings
Type	including screws, flat

Measurements

Width [w]	16.2 mm
Height [h]	16.2 mm
Depth [d]	13.5 mm

Material specifications

Color (RAL)	turquoise blue (5018)
Insulating material	PA
CTI according to IEC 60112	0

Corner inlay - UCS CC 5018 - 2203398

Technical data

Material specifications

Flammability rating according to UL 94	V0
Housing material	PA

Ambient conditions

Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Ambient temperature (operation)	-40 °C ... 100 °C (depending on power dissipation)

PCB data

Type of PCB mount	Bolt mounting
-------------------	---------------

Note on mounting

Tightening torque / rotational speed	Screw connection between housing halves: 1.2 Nm-1.4 Nm / 500 rpm-1000 rpm
--------------------------------------	---------------------------------------------------------------------------

Packaging information

Pieces per package	1
Denomination packing units	Pcs.

Standards and regulations

Flammability rating according to UL 94	V0
----------------------------------------	----

Classifications

eCl@ss

eCl@ss 10.0.1	27182702
eCl@ss 5.1	27180506
eCl@ss 6.0	27180800
eCl@ss 7.0	27182702
eCl@ss 8.0	27182702
eCl@ss 9.0	27182702

ETIM

ETIM 5.0	EC001031
ETIM 6.0	EC001031
ETIM 7.0	EC001031

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2203398](#)