

## Cable - FLK 50/EZ-DR/ 900/KONFEK - 2289667

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Round cable set; connection 1: IDC/FLK socket strip (1x 50-position); connection 2: IDC/FLK socket strip (1x 50-position); cable length: 9 m



COMPLIANT

### Key Commercial Data

|              |   |
|--------------|---|
| Packing unit | 1 pc  |
| GTIN         | <br>4 017918 057725 |
| GTIN         | 4017918057725   |

### Technical data

#### Ambient conditions

|   |  |
|---|--|
| Ambient temperature (operation)         | -40 °C ... 70 °C (fixed installation)    |
|   | -10 °C ... 70 °C (flexible installation) |
| Ambient temperature (storage/transport) | -40 °C ... 80 °C                         |
| Maximum altitude                        | ≤ 2000 m                                 |
| Degree of protection                    | IP00                                     |
|   | ≥ IP54 (Installation location)           |

#### General

|   |                      |
|---|----------------------|
| Max. permissible operating voltage      | 25 V AC              |
|   | 60 V DC              |
| Max. current carrying capacity per path | 1 A (50 °C)          |
|   | 0.6 A (70 °C)        |
| Length of cable                         | 9 m                  |
| External cable diameter                 | 10.3 mm ±0.4 mm      |
| Single wire, cross section              | 0.14 mm <sup>2</sup> |
| Single wire, cross section [AWG]        | 26                   |
| Single wire, number of litz wires       | 7                    |
| Single wire, material                   | Cu tin-plated        |

# Cable - FLK 50/EZ-DR/ 900/KONFEK - 2289667

## Technical data

### General

|   |   |
|---|---|
| Wire diameter incl. insulation                | 1 mm ±0.03 mm                                       |
| Smallest bending radius, fixed installation   | 86 mm   |
| Smallest bending radius, movable installation | 161 mm  |
| Bending cycles                                | 5000 (at a radius of ≥ 15x outside diameter)        |
| Cable, preassembly                            | Insulation displacement, IEC 60352-4/DIN EN 60352-4 |
| Shielding                                     | no  |
| Cable insulation resistance                   | ≥ 20 MΩ/km (20 °C)                                  |
| Cable resistance                              | ≤ 145 Ω/km (20 °C)                                  |
| Outer sheath, material                        | Semi-rigid PVC                                      |
| External sheath, color                        | gray  |
| Nominal operating mode                        | 100% operating factor                               |

### Connection data

|                                  |                      |
|----------------------------------|----------------------|
| Connection name                  | Field level          |
| Connection in acc. with standard | IEC 60603-13         |
| Connection method                | IDC/FLK socket strip |
| Number of connections            | 1                    |
| Number of positions              | 50                   |
| Insertion/withdrawal cycles      | > 50                 |
| Pitch                            | 2.54 mm              |

### Connection data 2

|                                  |                      |
|----------------------------------|----------------------|
| Connection name                  | Controller level     |
| Connection in acc. with standard | IEC 60603-13         |
| Connection method                | IDC/FLK socket strip |
| Number of connections            | 1                    |
| Number of positions              | 50                   |
| Insertion/withdrawal cycles      | > 50                 |
| Pitch                            | 2.54 mm              |

### Standards and Regulations

|                                  |                                       |
|----------------------------------|---------------------------------------|
| Flame resistance                 | UL VW-1                               |
|                                  | CSA FT-1                              |
|                                  | IEC 60332-1-2                         |
|                                  | VDE 0842, Part 332-1-2                |
|                                  | IEC 60332-3-22                        |
| Resistance to oil                | against occasional splashes           |
| Gasoline resistance              | against occasional splashes           |
| Connection in acc. with standard | CUL                                   |
| Designation                      | Air clearances and creepage distances |
| Standards/regulations            | DIN EN 50178                          |
| Rated insulation voltage         | 63 V                                  |

# Cable - FLK 50/EZ-DR/ 900/KONFEK - 2289667

## Technical data

### Standards and Regulations

|                      |                       |
|----------------------|-----------------------|
| Rated surge voltage  | 0.6 kV                |
| Insulation           | Functional insulation |
| Pollution degree     | 2                     |
| Overvoltage category | II                    |

### Supported controller

|                     |                           |
|---------------------|---------------------------|
| Controller          | SIEMENS S7-1500           |
| - suitable I/O card | 6ES7 521-1BL00-0AB0       |
|                     | 6ES7 522-1BL00-0AB0       |
|                     | 6ES7 522-1BL01-0AB0       |
|                     | 6ES7 531-7KF00-0AB0       |
|                     | 6ES7 531-7NF00-0AB0       |
|                     | 6ES7 531-7NF10-0AB0       |
|                     | 6ES7 531-7PF00-0AB0       |
|                     | 6ES7 532-5HF00-0AB0       |
| Controller          | SIEMENS S7-300 / ET 200 M |
| - suitable I/O card | CPU 313C                  |
|                     | CPU 313C-2DP              |
|                     | CPU 313C-2PtP             |
|                     | CPU 314C-2DP              |
|                     | CPU 314C-2PtP             |
|                     | 6ES7 321-1BL00-0AA0       |
|                     | 6ES7 322-1BL00-0AA0       |
|                     | 6ES7 322-8BH01-0AB0       |
|                     | 6ES7 323-1BL00-0AA0       |
|                     | 6ES7 331-1KF01-0AB0       |
|                     | 6ES7 331-7NF00-0AB0       |
|                     | 6ES7 331-7NF10-0AB0       |
|                     | 6ES7 331-7PF01-0AB0       |
|                     | 6ES7 331-7PF11-0AB0       |
|                     | 6ES7 332-5HF00-0AB0       |
|                     | 6ES7 350-2AH01-0AE0       |
|                     | 6ES7 357-4AH01-0AE0       |
| Controller          | SIEMENS S7-400            |
| - suitable I/O card | 6ES7 421-1BL01-0AA0       |
|                     | 6ES7 421-7BH01-0AB0       |
|                     | 6ES7 421-7DH00-0AA0       |
|                     | 6ES7 422-1BL00-0AA0       |
|                     | 6ES7 422-7BL00-0AB0       |
|                     | 6ES7 431-0HH0-0AB0        |
|                     | 6ES7 431-1KF00-0AB0       |

## Cable - FLK 50/EZ-DR/ 900/KONFEK - 2289667

### Technical data

#### Supported controller

|                     |  |
|---------------------|--|
|                     | 6ES7 431-1KF10-0AB0                    |
|                     | 6ES7 431-1KF20-0AB0                    |
|                     | 6ES7 431-7KF00-0AB0                    |
|                     | 6ES7 431-7KF10-0AB0                    |
|                     | 6ES7 431-7QH00-0AB0                    |
|                     | 6ES7 432-1HF00-0AB0                    |
| Controller          | Schneider Electric Modicon TSX QUANTUM |
| - suitable I/O card | DDI 353                                |
|                     | DDI 841                                |
|                     | DDI 853                                |
|                     | DAI 340                                |
|                     | DAI 440                                |
|                     | DAI 453                                |
|                     | DDO 353                                |
|                     | DDM 390                                |
|                     | ACI 030                                |
|                     | ACI 040                                |
|                     | ATI 030                                |
|                     | ARI 030                                |
|                     | AVI 030                                |
|                     | ACO 020                                |
|                     | ACO 130                                |
|                     | AVO 020                                |
|                     | EHC 105                                |
|                     | EHC 202                                |
| Controller          | ALLEN-BRADLEY ControlLogix             |
| - suitable I/O card | 1756-IA16I                             |
|                     | 1756-IB16D                             |
|                     | 1756-IB16I                             |
|                     | 1756-IB32                              |
|                     | 1756-IH16I                             |
|                     | 1756-OB32                              |
|                     | 1756-IF8                               |
|                     | 1756-IF16                              |
|                     | 1756-HSC                               |
|                     | 1756-M02AE                             |
| Controller          | ALLEN-BRADLEY PLC 5                    |
| - suitable I/O card | 1771 IBN                               |
|                     | 1771 OBN                               |
| Controller          | HONEYWELL Experion PKS C200            |

# Cable - FLK 50/EZ-DR/ 900/KONFEK - 2289667

## Technical data

### Supported controller

|                     |            |
|---------------------|------------|
| - suitable I/O card | TC-IDK 161 |
|                     | TC-IDX 161 |
|                     | TC-IDJ 161 |
|                     | TC-IDD 321 |
|                     | TC-ODD 321 |
|                     | TC-IAH 161 |

### Color code

|   |  |
|---|--|
| Connector 1 = connector 2 (optional) = wire color | IDC/FLK50 (1) = IDC/FLK50 (1) = black          |
|   | IDC/FLK50 (2) = IDC/FLK50 (2) = brown          |
|   | IDC/FLK50 (3) = IDC/FLK50 (3) = red            |
|   | IDC/FLK50 (4) = IDC/FLK50 (4) = orange         |
|   | IDC/FLK50 (5) = IDC/FLK50 (5) = yellow         |
|   | IDC/FLK50 (6) = IDC/FLK50 (6) = green          |
|   | IDC/FLK50 (7) = IDC/FLK50 (7) = blue           |
|   | IDC/FLK50 (8) = IDC/FLK50 (8) = violet         |
|   | IDC/FLK50 (9) = IDC/FLK50 (9) = gray           |
|   | IDC/FLK50 (10) = IDC/FLK50 (10) = white        |
|   | IDC/FLK50 (11) = IDC/FLK50 (11) = white-black  |
|   | IDC/FLK50 (12) = IDC/FLK50 (12) = white-brown  |
|   | IDC/FLK50 (13) = IDC/FLK50 (13) = white-red    |
|   | IDC/FLK50 (14) = IDC/FLK50 (14) = white-orange |
|   | IDC/FLK50 (15) = IDC/FLK50 (15) = white-yellow |
|   | IDC/FLK50 (16) = IDC/FLK50 (16) = white-green  |
|   | IDC/FLK50 (17) = IDC/FLK50 (17) = white-blue   |
|   | IDC/FLK50 (18) = IDC/FLK50 (18) = white-violet |
|   | IDC/FLK50 (19) = IDC/FLK50 (19) = white-gray   |
|   | IDC/FLK50 (20) = IDC/FLK50 (20) = brown-black  |
|   | IDC/FLK50 (21) = IDC/FLK50 (21) = brown-red    |
|   | IDC/FLK50 (22) = IDC/FLK50 (22) = brown-orange |
|   | IDC/FLK50 (23) = IDC/FLK50 (23) = brown-yellow |
|   | IDC/FLK50 (24) = IDC/FLK50 (24) = brown-green  |
|   | IDC/FLK50 (25) = IDC/FLK50 (25) = brown-blue   |
|   | IDC/FLK50 (26) = IDC/FLK50 (26) = brown-violet |
|   | IDC/FLK50 (27) = IDC/FLK50 (27) = brown-gray   |
|   | IDC/FLK50 (28) = IDC/FLK50 (28) = brown-white  |
|   | IDC/FLK50 (29) = IDC/FLK50 (29) = green-black  |
|   | IDC/FLK50 (30) = IDC/FLK50 (30) = green-brown  |
|   | IDC/FLK50 (31) = IDC/FLK50 (31) = green-red    |
|   | IDC/FLK50 (32) = IDC/FLK50 (32) = green-orange |
|   | IDC/FLK50 (33) = IDC/FLK50 (33) = green-blue   |

## Cable - FLK 50/EZ-DR/ 900/KONFEK - 2289667

### Technical data

#### Color code

|  |   |
|--|---|
|  | IDC/FLK50 (34) = IDC/FLK50 (34) = green-violet  |
|  | IDC/FLK50 (35) = IDC/FLK50 (35) = green-gray    |
|  | IDC/FLK50 (36) = IDC/FLK50 (36) = green-white   |
|  | IDC/FLK50 (37) = IDC/FLK50 (37) = yellow-black  |
|  | IDC/FLK50 (38) = IDC/FLK50 (38) = yellow-brown  |
|  | IDC/FLK50 (39) = IDC/FLK50 (39) = yellow-red    |
|  | IDC/FLK50 (40) = IDC/FLK50 (40) = yellow-orange |
|  | IDC/FLK50 (41) = IDC/FLK50 (41) = yellow-blue   |
|  | IDC/FLK50 (42) = IDC/FLK50 (42) = yellow-violet |
|  | IDC/FLK50 (43) = IDC/FLK50 (43) = yellow-gray   |
|  | IDC/FLK50 (44) = IDC/FLK50 (44) = yellow-white  |
|  | IDC/FLK50 (45) = IDC/FLK50 (45) = gray-black    |
|  | IDC/FLK50 (46) = IDC/FLK50 (46) = gray-brown    |
|  | IDC/FLK50 (47) = IDC/FLK50 (47) = gray-red      |
|  | IDC/FLK50 (48) = IDC/FLK50 (48) = gray-orange   |
|  | IDC/FLK50 (49) = IDC/FLK50 (49) = gray-yellow   |
|  | IDC/FLK50 (50) = IDC/FLK50 (50) = gray-green    |


#### Environmental Product Compliance

|            |   |
|------------|---|
| China RoHS | Environmentally Friendly Use Period = 50 years  |
|            | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |

### Drawings

## Cable - FLK 50/EZ-DR/ 900/KONFEK - 2289667

Diagram



Maximum permissible current per path in uncoiled state

### Classifications

#### eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27242220 |
| eCl@ss 4.0    | 27060300 |
| eCl@ss 4.1    | 27060300 |
| eCl@ss 5.0    | 27242200 |
| eCl@ss 5.1    | 27242200 |
| eCl@ss 6.0    | 27249200 |
| eCl@ss 7.0    | 27249205 |
| eCl@ss 8.0    | 27249205 |
| eCl@ss 9.0    | 27242220 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000237 |
| ETIM 3.0 | EC000237 |
| ETIM 4.0 | EC000237 |
| ETIM 5.0 | EC000237 |
| ETIM 6.0 | EC000237 |
| ETIM 7.0 | EC000237 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 26121620 |
| UNSPSC 7.0901 | 26121620 |
| UNSPSC 11     | 26121620 |

# Cable - FLK 50/EZ-DR/ 900/KONFEK - 2289667

## Classifications

### UNSPSC

|              |          |
|--------------|----------|
| UNSPSC 12.01 | 26121620 |
| UNSPSC 13.2  | 26121620 |
| UNSPSC 18.0  | 26121620 |
| UNSPSC 19.0  | 26121620 |
| UNSPSC 20.0  | 26121620 |
| UNSPSC 21.0  | 26121620 |

## Approvals

### Approvals

#### Approvals

UL Listed / cUL Listed / EAC / cULus Listed

#### Ex Approvals

### Approval details

|                    |  |   |               |
|--------------------|--|---|---------------|
| UL Listed          |  | <a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> | FILE E 238705 |
| Nominal voltage UN |  | 125 V   |               |
| Nominal current IN |  | 1 A   |               |

|                    |  |   |               |
|--------------------|--|---|---------------|
| cUL Listed         |  | <a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> | FILE E 238705 |
| Nominal voltage UN |  | 125 V   |               |
| Nominal current IN |  | 1 A   |               |

|     |  |                        |
|-----|--|------------------------|
| EAC |  | RU*<br>DE.HB*35.B00385 |
|-----|--|------------------------|

|              |  |
|--------------|--|
| cULus Listed |  |
|--------------|--|



## Cable - FLK 50/EZ-DR/ 900/KONFEK - 2289667

### Accessories

#### Accessories

#### Marker carrier cable

#### Cable marker carrier - KME - 0807083



Cable marker carrier, white, unlabeled, mounting type: Assembly with cable binders, cable diameter: > 5 mm, lettering field size: 20 mm x 8 mm

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2289667](#)