

## Pin strip - PST 1,3/ 5-5,0 - 1933215

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



The figure shows a 6-position version

Pin strip, nominal current: 12 A, rated voltage (III/2): 320 V, nominal cross section: 1.5 mm<sup>2</sup>, number of positions: 5, pitch: 5 mm, color: black, contact surface: Tin, mounting: THR soldering, pin layout: Linear pinning, solder pin [P]: 3.5 mm, The maximum current depends on the plug used. The lower of the two current values apply for plug and pin strip. The pin strip is made of highly temperature resistant plastic and is thus suitable for the reflow process.

### Your advantages

- Suitable for wave and reflow soldering processes
- Optimum pin geometry for all COMBICON pin strip connectors



### Key Commercial Data

|                        |               |
|------------------------|---------------|
| Packing unit           | 250 pc        |
| Minimum order quantity | 250 pc        |
| GTIN                   |               |
| GTIN                   | 4017918918705 |

### Technical data

#### Dimensions

|                          |          |
|--------------------------|----------|
| Length [ l ]             | 2.8 mm   |
| Width                    | 24.6 mm  |
| Pitch                    | 5 mm     |
| Dimension a              | 20 mm    |
| Width [ w ]              | 24.6 mm  |
| Height [ h ]             | 13 mm    |
| Installed height         | 9.5 mm   |
| Length of the solder pin | 3.5 mm   |
| Pin dimensions           | ø 1.3 mm |
| Length                   | 2.8 mm   |

#### General

## Pin strip - PST 1,3/ 5-5,0 - 1933215

### Technical data

#### General

|  |                                 |
|--|---------------------------------|
| Range of articles                      | PST 1,3/..-V                    |
| Insulating material group              | IIIa                            |
| Rated surge voltage (III/3)            | 4 kV                            |
| Rated surge voltage (III/2)            | 4 kV                            |
| Rated surge voltage (II/2)             | 4 kV                            |
| Rated voltage (III/3)                  | 250 V                           |
| Rated voltage (III/2)                  | 320 V                           |
| Rated voltage (II/2)                   | 400 V                           |
| Connection in acc. with standard       | EN-VDE                          |
| Nominal current $I_N$                  | 12 A (depends on the plug used) |
| Maximum load current                   | 12 A (depends on the plug used) |
| Insulating material                    | PA                              |
| Flammability rating according to UL 94 | V0                              |
| Color                                  | black                           |
| Number of positions                    | 5                               |

#### Standards and Regulations

|  |        |
|--|--------|
| Connection in acc. with standard       | EN-VDE |
|  | CSA    |
| Flammability rating according to UL 94 | V0     |


#### Environmental Product Compliance

|            |   |
|------------|---|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
|            | No hazardous substances above threshold values          |


### Drawings

# Pin strip - PST 1,3/ 5-5,0 - 1933215

Diagram




Diagram



# Pin strip - PST 1,3/ 5-5,0 - 1933215

Diagram



Type: PTS 1,5/...-PH-5,0 with PST 1,3/...-5,0

## Classifications

eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27440402 |
| eCl@ss 4.0    | 27260700 |
| eCl@ss 4.1    | 27260700 |
| eCl@ss 5.0    | 27260700 |
| eCl@ss 5.1    | 27260700 |
| eCl@ss 6.0    | 27260700 |
| eCl@ss 7.0    | 27440402 |
| eCl@ss 8.0    | 27440402 |
| eCl@ss 9.0    | 27440402 |

ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC001121 |
| ETIM 4.0 | EC002637 |
| ETIM 5.0 | EC002637 |
| ETIM 6.0 | EC002637 |
| ETIM 7.0 | EC002637 |

UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211801 |
| UNSPSC 7.0901 | 39121432 |
| UNSPSC 11     | 34131203 |
| UNSPSC 12.01  | 39121432 |

# Pin strip - PST 1,3/ 5-5,0 - 1933215

## Classifications

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 13.2 | 39121409 |
| UNSPSC 18.0 | 39121409 |
| UNSPSC 19.0 | 39121409 |
| UNSPSC 20.0 | 39121409 |
| UNSPSC 21.0 | 39121409 |

## Approvals

### Approvals

#### Approvals

SEV / EAC / cULus Recognized / IECCEB CB Scheme / IECCEB CB Scheme / VDE Gutachten mit Fertigungsüberwachung

#### Ex Approvals

### Approval details

|                    |  |   |         |
|--------------------|--|---|---------|
| SEV                |  | <a href="https://www.eurofins.ch/de/">https://www.eurofins.ch/de/</a> | IK-4496 |
| Nominal voltage UN |  | 250 V   |         |
| Nominal current IN |  | 12 A  |         |

|     |  |         |
|-----|--|---------|
| EAC |  | B.01687 |
|-----|--|---------|

|                    |       |   |                 |
|--------------------|-------|---|-----------------|
| cULus Recognized   |       | <a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> | E60425-20030211 |
|                    | B     | D   |                 |
| Nominal voltage UN | 300 V | 300 V   |                 |
| Nominal current IN | 16 A  | 10 A  |                 |

|                    |  |   |           |
|--------------------|--|---|-----------|
| IECEE CB Scheme    |  | <a href="http://www.iecee.org/">http://www.iecee.org/</a> | DE1-58429 |
| Nominal voltage UN |  | 320 V   |           |

# Pin strip - PST 1,3/ 5-5,0 - 1933215

## Approvals

|                                |      |
|--------------------------------|------|
| Nominal current I <sub>N</sub> | 10 A |
|--------------------------------|------|

|                 |  |   |          |
|-----------------|--|---|----------|
| IECEE CB Scheme |  | <a href="http://www.iecee.org/">http://www.iecee.org/</a> | CH-10786 |
|-----------------|--|---|----------|

|   |       |   |          |
|---|-------|---|----------|
| VDE Gutachten mit Fertigungsüberwachung |       | <a href="http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx">http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx</a> | 40040542 |
| Nominal voltage U <sub>N</sub>          | 320 V |   |          |
| Nominal current I <sub>N</sub>          | 10 A  |   |          |

## Accessories

### Additional products

Plug - PTDA 2,5/ 5-PH-5,0 - 1725536



PCB connector, nominal current: 14 A, rated voltage (III/2): 400 V, nominal cross section: 2.5 mm<sup>2</sup>, number of positions: 5, pitch: 5 mm, connection method: Push-in spring connection, color: green, contact surface: Tin

PCB terminal block - PT 1,5/ 5-PH-5,0 - 1755619



PCB connector, nominal current: 10 A, rated voltage (III/2): 400 V, nominal cross section: 1.5 mm<sup>2</sup>, number of positions: 5, pitch: 5 mm, connection method: Screw connection with tension sleeve, color: green, contact surface: Tin

PCB terminal block - PT 1,5/ 5-PH-5,0 CLIP - 1755761



PCB connector, nominal current: 10 A, rated voltage (III/2): 400 V, nominal cross section: 1.5 mm<sup>2</sup>, number of positions: 5, pitch: 5 mm, connection method: Screw connection with tension sleeve, color: green, contact surface: Tin

## Pin strip - PST 1,3/ 5-5,0 - 1933215

### Accessories

Plug - PT 1,5/ 5-PVH-5,0 - 1934890

PCB connector, nominal current: 12 A, rated voltage (III/2): 400 V, nominal cross section: 1.5 mm<sup>2</sup>, number of positions: 5, pitch: 5 mm, connection method: Screw connection with wire protector, color: green, contact surface: Tin



---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1933215](#)