

Remote bus cable - IBS RBC METER/E-T - 2723149


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



By the meter, Remote bus cable, INTERBUS, shielded, PVC, black RAL 9005, 6-wire (3 x 2 x 0.22 mm²), color single wire: Green-yellow, white-brown, gray-pink, for underground runs



Key Commercial Data

| | |
|--------------|---|
| Packing unit | 1 M |
| GTIN |  4 017918 141271 |
| GTIN | 4017918141271 |

Technical data

General data

| | |
|---------------------------------------|------------------|
| Number of positions | 6 |
| Alternative short product description | Remote bus cable |

Cable

| | |
|---|--------------------------------------|
| Signal type/category | INTERBUS |
| Cable structure | 3 x 2 x 0.22 mm ² |
| Conductor cross section | 3x 2x 0.22 mm ² |
| Conductor structure signal line | 7x 0.20 mm |
| Wire colors | Green-yellow, white-brown, gray-pink |
| Twisted pairs | 2 cores to the pair |
| Overall twist | 3 pairs to the core |
| Shielding | Braided copper wires |
| External sheath, color | black RAL 9005 |
| External cable diameter D | 9 mm |
| Minimum bending radius, fixed installation | 7.5 x D |
| Minimum bending radius, flexible installation | 15 x D |
| Outer sheath, material | PVC |
| Material conductor insulation | PE |

Remote bus cable - IBS RBC METER/E-T - 2723149

Technical data

Cable

| | |
|---------------------------------------|---|
| Conductor material | Bare Cu litz wires |
| Insulation resistance | ≥ 5 GΩ*km |
| Loop resistance | ≤ 186.00 Ω/km |
| Cable capacity | ≤ 60 nF/km (At 800 Hz) |
| Wave impedance | 120 Ω ±20 % (at 64 kHz) |
| | 100 Ω ±15 % (with 1 MHz) |
| Near end crosstalk attenuation (NEXT) | ≥ 61 dB (at 772 kHz) |
| | ≥ 59 dB (with 1 MHz) |
| | ≥ 55 dB (at 2 MHz) |
| | ≥ 50 dB (at 4 MHz) |
| | ≥ 46 dB (at 8 MHz) |
| | ≥ 44 dB (at 10 MHz) |
| | ≥ 41 dB (at 16 MHz) |
| | ≥ 40 dB (at 20 MHz) |
| Attenuation | ≤ 15 dB/km (at 256 kHz) |
| | ≤ 24 dB/km (at 772 kHz) |
| | ≤ 27 dB/km (with 1 MHz) |
| | ≤ 52 dB/km (at 4 MHz) |
| | ≤ 84 dB/km (at 10 MHz) |
| | ≤ 112 dB/km (at 16 MHz) |
| | ≤ 119 dB/km (at 20 MHz) |
| Signal speed | 0.66 c |
| Coupling resistance | < 250.00 mΩ/m (at 30 MHz) |
| Nominal voltage, cable | 250 V (Peak value, not for high-power applications) |
| Test voltage Core/Core | 1500 V _{rms} |
| Test voltage Core/Shield | 1000 V _{rms} |
| Ambient temperature (operation) | -30 °C ... 70 °C (cable, fixed installation) |
| | -5 °C ... 70 °C (cable, flexible installation) |

Environmental Product Compliance

| | |
|------------|---|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
| | No hazardous substances above threshold values |

Classifications

eCl@ss

| | |
|---------------|----------|
| eCl@ss 10.0.1 | 27060390 |
| eCl@ss 4.0 | 24010400 |
| eCl@ss 4.1 | 24010400 |
| eCl@ss 5.0 | 19030300 |
| eCl@ss 5.1 | 19030300 |

Remote bus cable - IBS RBC METER/E-T - 2723149

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 6.0 | 27061800 |
| eCl@ss 7.0 | 27061801 |
| eCl@ss 8.0 | 27061801 |
| eCl@ss 9.0 | 27061801 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000304 |
| ETIM 3.0 | EC000830 |
| ETIM 4.0 | EC000830 |
| ETIM 5.0 | EC000830 |
| ETIM 6.0 | EC000830 |
| ETIM 7.0 | EC003249 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 43172015 |
| UNSPSC 7.0901 | 43201404 |
| UNSPSC 11 | 39121311 |
| UNSPSC 12.01 | 39121311 |
| UNSPSC 13.2 | 26121604 |
| UNSPSC 18.0 | 26121604 |
| UNSPSC 19.0 | 26121604 |
| UNSPSC 20.0 | 26121604 |
| UNSPSC 21.0 | 26121604 |

Approvals

Approvals


Approvals

INTERBUS CLUB / EAC-RoHS

Ex Approvals

Approval details

| | |
|---------------|--------------|
| INTERBUS CLUB | 116/27.05.97 |
|---------------|--------------|

| | | |
|----------|---|--------------------------|
| EAC-RoHS |  | RU D- DE.HB35.B.00371 |
|----------|---|--------------------------|

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2723149](#)