

Cable - CABLE-D37-M2,5/4X14/ 50/Y81P-O - 2302476


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Round cable set; controller: Mitsubishi Electric MELSEC Q (Y81P); connection 1: D-SUB socket strip (1x 37-position); connection 2: IDC/FLK socket strip (4x 14-position); cable length: 0.5 m

RoHS

Key Commercial Data

| | |
|--------------|---|
| Packing unit | 1 pc |
| GTIN |  4 017918 907945 |
| GTIN | 4017918907945 |

Technical data

Ambient conditions

| | |
|---|--|
| Ambient temperature (operation) | -40 °C ... 70 °C (fixed installation) |
| | -10 °C ... 70 °C (flexible installation) |
| Ambient temperature (storage/transport) | -40 °C ... 80 °C |
| Maximum altitude | ≤ 2000 m |
| Degree of protection | IP00 |
| | ≥ IP54 (Installation location) |

General

| | |
|---|----------------------|
| Max. permissible operating voltage | 25 V AC |
| | 60 V DC |
| Max. current carrying capacity per path | 1 A (50 °C) |
| | 0.6 A (70 °C) |
| Length of cable | 0.5 m |
| External cable diameter | 4x 6.4 mm ±0.4 mm |
| Single wire, cross section | 0.14 mm ² |
| Single wire, cross section [AWG] | 26 |
| Single wire, number of litz wires | 7 |
| Single wire, material | Cu tin-plated |

Cable - CABLE-D37-M2,5/4X14/ 50/Y81P-O - 2302476

Technical data

General

| | |
|---|--|
| Wire diameter incl. insulation | 1 mm ±0.03 mm |
| Smallest bending radius, fixed installation | 55 mm |
| Smallest bending radius, movable installation | 104 mm |
| Bending cycles | 5000 (at a radius of ≥ 15x outside diameter) |
| Shielding | no |
| Cable insulation resistance | ≥ 20 MΩ/km (20 °C) |
| Cable resistance | ≤ 145 Ω/km (20 °C) |
| External sheath, color | gray |
| Nominal operating mode | 100% operating factor |

Connection data

| | |
|----------------------------------|----------------------|
| Connection name | Field level |
| Connection in acc. with standard | IEC 60603-13 |
| Connection method | IDC/FLK socket strip |
| Number of connections | 4 |
| Number of positions | 14 |
| Insertion/withdrawal cycles | > 50 |
| Pitch | 2.54 mm |

Connection data 2

| | |
|----------------------------------|--------------------|
| Connection name | Controller level |
| Connection in acc. with standard | IEC 60807-2 |
| | DIN 41652 |
| Connection method | D-SUB socket strip |
| Screw thread | M2,5 |
| Number of connections | 1 |
| Number of positions | 37 |
| Torque | 0.2 Nm |
| Insertion/withdrawal cycles | > 200 |

Standards and Regulations

| | |
|----------------------------------|---------------------------------------|
| Flame resistance | UL VW-1 |
| | CSA FT-1 |
| | IEC 60332-1-2 |
| | VDE 0842, Part 332-1-2 |
| | IEC 60332-3-22 |
| Resistance to oil | against occasional splashes |
| Gasoline resistance | against occasional splashes |
| Connection in acc. with standard | CUL |
| Designation | Air clearances and creepage distances |
| Standards/regulations | DIN EN 50178 |
| Rated insulation voltage | 63 V |

Cable - CABLE-D37-M2,5/4X14/ 50/Y81P-O - 2302476

Technical data

Standards and Regulations

| | |
|----------------------|-----------------------|
| Rated surge voltage | 0.6 kV |
| Insulation | Functional insulation |
| Pollution degree | 2 |
| Overvoltage category | II |

Supported controller

| | |
|---------------------|---------------------|
| Controller | MITSUBISHI MELSEC Q |
| - suitable I/O card | QY81P |

Color code

| | |
|---|---|
| Connector 1 = connector 2 (optional) = wire color | D-SUB37 (1) = IDC/FLK14-1 (1) = black |
| | D-SUB37 (20) = IDC/FLK14-1 (2) = brown |
| | D-SUB37 (2) = IDC/FLK14-1 (3) = red |
| | D-SUB37 (21) = IDC/FLK14-1 (4) = orange |
| | D-SUB37 (3) = IDC/FLK14-1 (5) = yellow |
| | D-SUB37 (22) = IDC/FLK14-1 (6) = green |
| | D-SUB37 (4) = IDC/FLK14-1 (7) = blue |
| | D-SUB37 (23) = IDC/FLK14-1 (8) = violet |
| | D-SUB37 (17) = IDC/FLK14-1 (9) = gray |
| | D-SUB37 (19) = IDC/FLK14-1 (10) = white |
| | D-SUB37 (18) = IDC/FLK14-1 (11) = white-black |
| | D-SUB37 (36) = IDC/FLK14-1 (13) = white-brown |
| | D-SUB37 (5) = IDC/FLK14-2 (1) = black |
| | D-SUB37 (24) = IDC/FLK14-2 (2) = brown |
| | D-SUB37 (6) = IDC/FLK14-2 (3) = red |
| | D-SUB37 (25) = IDC/FLK14-2 (4) = orange |
| | D-SUB37 (7) = IDC/FLK14-2 (5) = yellow |
| | D-SUB37 (26) = IDC/FLK14-2 (6) = green |
| | D-SUB37 (8) = IDC/FLK14-2 (7) = blue |
| | D-SUB37 (27) = IDC/FLK14-2 (8) = violet |
| | D-SUB37 (17) = IDC/FLK14-2 (9) = gray |
| | D-SUB37 (19) = IDC/FLK14-2 (10) = white |
| | D-SUB37 (18) = IDC/FLK14-2 (11) = white-black |
| | D-SUB37 (36) = IDC/FLK14-2 (13) = white-brown |
| | D-SUB37 (9) = IDC/FLK14-3 (1) = black |
| | D-SUB37 (28) = IDC/FLK14-3 (2) = brown |
| | D-SUB37 (10) = IDC/FLK14-3 (3) = red |
| | D-SUB37 (29) = IDC/FLK14-3 (4) = orange |
| | D-SUB37 (11) = IDC/FLK14-3 (5) = yellow |
| | D-SUB37 (30) = IDC/FLK14-3 (6) = green |
| | D-SUB37 (12) = IDC/FLK14-3 (7) = blue |
| | D-SUB37 (31) = IDC/FLK14-3 (8) = violet |

Cable - CABLE-D37-M2,5/4X14/ 50/Y81P-O - 2302476

Technical data

Color code

| | |
|--|---|
| | D-SUB37 (17) = IDC/FLK14-3 (9) = gray |
| | D-SUB37 (37) = IDC/FLK14-3 (10) = white |
| | D-SUB37 (18) = IDC/FLK14-3 (11) = white-black |
| | D-SUB37 (36) = IDC/FLK14-3 (13) = white-brown |
| | D-SUB37 (13) = IDC/FLK14-4 (1) = black |
| | D-SUB37 (32) = IDC/FLK14-4 (2) = brown |
| | D-SUB37 (14) = IDC/FLK14-4 (3) = red |
| | D-SUB37 (33) = IDC/FLK14-4 (4) = orange |
| | D-SUB37 (15) = IDC/FLK14-4 (5) = yellow |
| | D-SUB37 (34) = IDC/FLK14-4 (6) = green |
| | D-SUB37 (16) = IDC/FLK14-4 (7) = blue |
| | D-SUB37 (35) = IDC/FLK14-4 (8) = violet |
| | D-SUB37 (17) = IDC/FLK14-4 (9) = gray |
| | D-SUB37 (37) = IDC/FLK14-4 (10) = white |
| | D-SUB37 (18) = IDC/FLK14-4 (11) = white-black |
| | D-SUB37 (36) = IDC/FLK14-4 (13) = white-brown |


Environmental Product Compliance

| | |
|------------|---|
| REACH SVHC | Lead 7439-92-1 |
| China RoHS | Environmentally Friendly Use Period = 50 years |
| | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |

Drawings


Cable - CABLE-D37-M2,5/4X14/ 50/Y81P-O - 2302476

Diagram



Maximum permissible current per path in uncoiled state

Dimensional drawing



Cable - CABLE-D37-M2,5/4X14/ 50/Y81P-O - 2302476

Classifications

eCl@ss

| | |
|---------------|----------|
| eCl@ss 10.0.1 | 27242220 |
| eCl@ss 4.0 | 27060300 |
| eCl@ss 4.1 | 27060300 |
| eCl@ss 5.0 | 27242200 |
| eCl@ss 5.1 | 27242200 |
| eCl@ss 6.0 | 27249200 |
| eCl@ss 7.0 | 27249205 |
| eCl@ss 8.0 | 27249205 |
| eCl@ss 9.0 | 27242220 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000237 |
| ETIM 3.0 | EC000237 |
| ETIM 4.0 | EC000237 |
| ETIM 5.0 | EC000237 |
| ETIM 6.0 | EC000237 |
| ETIM 7.0 | EC000237 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 26121620 |
| UNSPSC 7.0901 | 26121620 |
| UNSPSC 11 | 26121620 |
| UNSPSC 12.01 | 26121620 |
| UNSPSC 13.2 | 26121620 |
| UNSPSC 18.0 | 26121620 |
| UNSPSC 19.0 | 26121620 |
| UNSPSC 20.0 | 26121620 |
| UNSPSC 21.0 | 26121620 |

Approvals

Approvals

Approvals

UL Listed / cUL Listed / EAC / cULus Listed

Ex Approvals

Approval details

Cable - CABLE-D37-M2,5/4X14/ 50/Y81P-O - 2302476

Approvals

| | | | |
|--------------------|--|---|---------------|
| UL Listed | | http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm | FILE E 238705 |
| Nominal voltage UN | | 125 V | |
| Nominal current IN | | 1 A | |

| | | | |
|--------------------|--|---|---------------|
| cUL Listed | | http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm | FILE E 238705 |
| Nominal voltage UN | | 125 V | |
| Nominal current IN | | 1 A | |

| | | |
|-----|--|-------------------------|
| EAC | | RU*- DE.HB*35.B00385 |
|-----|--|-------------------------|

| | |
|--------------|--|
| cULus Listed | |
|--------------|--|

Accessories

Accessories

Marker carrier cable

Cable marker carrier - KME - 0807083



Cable marker carrier, white, unlabeled, mounting type: Assembly with cable binders, cable diameter: > 5 mm, lettering field size: 20 mm x 8 mm

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2302476](#)