

Cable - CABLE-FLK50/0,14/HF/ 3,0M - 2314189

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Assembled, halogen-free round cable; connection 1: IDC/FLK socket strip (1x 50-position); connection 2: IDC/FLK socket strip (1x 50-position); cable length: 3 m



COMPLETE RoHS

Key Commercial Data

| | |
|--------------|---------------|
| Packing unit | 1 pc |
| GTIN | |
| GTIN | 4046356099745 |

Technical data

Ambient conditions

| | |
|---|--|
| Ambient temperature (operation) | -40 °C ... 70 °C (fixed installation) |
| | -10 °C ... 70 °C (flexible installation) |
| Ambient temperature (storage/transport) | -40 °C ... 80 °C |
| Maximum altitude | ≤ 2000 m |
| Degree of protection | IP00 |
| | ≥ IP54 (Installation location) |

General

| | |
|---|----------------------|
| Max. permissible operating voltage | 25 V AC |
| | 60 V DC |
| Max. current carrying capacity per path | 1 A (50 °C) |
| | 0.6 A (70 °C) |
| Length of cable | 3 m |
| External cable diameter | 10.3 mm ±0.4 mm |
| Single wire, cross section | 0.14 mm ² |
| Single wire, cross section [AWG] | 26 |
| Single wire, number of litz wires | 7 |
| Single wire, material | Cu tin-plated |

Cable - CABLE-FLK50/0,14/HF/ 3,0M - 2314189

Technical data

General

| | |
|---|---|
| Wire diameter incl. insulation | 1 mm ±0.03 mm |
| Smallest bending radius, fixed installation | 86 mm |
| Smallest bending radius, movable installation | 161 mm |
| Bending cycles | 5000 (at a radius of ≥ 15x outside diameter) |
| Cable, preassembly | Insulation displacement, IEC 60352-4/DIN EN 60352-4 |
| Shielding | no |
| Cable insulation resistance | ≥ 20 MΩ/km (20 °C) |
| Cable resistance | ≤ 145 Ω/km (20 °C) |
| Outer sheath, material | halogen-free (type 2) |
| External sheath, color | gray |
| Nominal operating mode | 100% operating factor |

Connection data

| | |
|----------------------------------|----------------------|
| Connection name | Field level |
| Connection in acc. with standard | IEC 60603-13 |
| Connection method | IDC/FLK socket strip |
| Number of connections | 1 |
| Number of positions | 50 |
| Insertion/withdrawal cycles | > 50 |
| Pitch | 2.54 mm |

Connection data 2

| | |
|----------------------------------|----------------------|
| Connection name | Controller level |
| Connection in acc. with standard | IEC 60603-13 |
| Connection method | IDC/FLK socket strip |
| Number of connections | 1 |
| Number of positions | 50 |
| Insertion/withdrawal cycles | > 50 |
| Pitch | 2.54 mm |

Standards and Regulations

| | |
|--------------------------|---------------------------------------|
| Flame resistance | IEC 60332-1-2 |
| | VDE 0842, Part 332-1-2 |
| | IEC 60332-3-22 |
| Resistance to oil | against occasional splashes |
| Gasoline resistance | against occasional splashes |
| Designation | Air clearances and creepage distances |
| Standards/regulations | DIN EN 50178 |
| Rated insulation voltage | 63 V |
| Rated surge voltage | 0.6 kV |
| Insulation | Functional insulation |
| Pollution degree | 2 |

Cable - CABLE-FLK50/0,14/HF/ 3,0M - 2314189

Technical data

Standards and Regulations

| | |
|----------------------|----|
| Overvoltage category | II |
|----------------------|----|

Supported controller

| | |
|---------------------|--|
| Controller | SIEMENS S7-300 / ET 200 M |
| - suitable I/O card | CPU 313C-2DP |
| | CPU 314C-2PtP |
| | 6ES7 321-1BL00-0AA0 |
| | 6ES7 322-1BL00-0AA0 |
| | 6ES7 323-1BL00-0AA0 |
| | 6ES7 331-7NF00-0AB0 |
| | 6ES7 331-7PF01-0AB0 |
| | 6ES7 331-7PF11-0AB0 |
| | 6ES7 350-2AH01-0AE0 |
| | 6ES7 357-4AH01-0AE0 |
| | CPU 314C-2DP |
| | 6ES7 332-5HF00-0AB0 |
| | 6ES7 331-7NF10-0AB0 |
| | 6ES7 331-1KF01-0AB0 |
| | CPU 313C |
| | CPU 313C-2PtP |
| Controller | SIEMENS S7-400 |
| - suitable I/O card | 6ES7 421-1BL01-0AA0 |
| | 6ES7 421-7BH01-0AB0 |
| | 6ES7 421-7DH00-0AA0 |
| | 6ES7 422-1BL00-0AA0 |
| | 6ES7 422-7BL00-0AB0 |
| | 6ES7 431-0HH0-0AB0 |
| | 6ES7 431-1KF00-0AB0 |
| | 6ES7 431-1KF10-0AB0 |
| | 6ES7 431-1KF20-0AB0 |
| | 6ES7 431-7KF00-0AB0 |
| | 6ES7 431-7KF10-0AB0 |
| | 6ES7 431-7QH00-0AB0 |
| | 6ES7 432-1HF00-0AB0 |
| Controller | Schneider Electric Modicon TSX QUANTUM |
| - suitable I/O card | DDI 353 |
| | DDI 841 |
| | DDI 853 |
| | DAI 340 |
| | DAI 353 |
| | DAI 440 |

Cable - CABLE-FLK50/0,14/HF/ 3,0M - 2314189

Technical data

Supported controller

| | |
|---------------------|-----------------------------|
| | DAI 453 |
| | DDO 353 |
| | DDM 390 |
| | ACI 030 |
| | ACI 040 |
| | ATI 030 |
| | ARI 030 |
| | AVI 030 |
| | ACO 020 |
| | ACO 130 |
| | AVO 020 |
| | EHC 105 |
| | EHC 202 |
| Controller | ALLEN-BRADLEY ControlLogix |
| - suitable I/O card | 1756-IA16I |
| | 1756-IB16D |
| | 1756-IB16I |
| | 1756-IB32 |
| | 1756-IH16I |
| | 1756-OB32 |
| | 1756-IF8 |
| | 1756-IF16 |
| | 1756-HSC |
| | 1756-M02AE |
| Controller | ALLEN-BRADLEY PLC 5 |
| - suitable I/O card | 1771 IBN |
| | 1771 OBN |
| Controller | HONEYWELL Experion PKS C200 |
| - suitable I/O card | TC-IDK 161 |
| | TC-IDX 161 |
| | TC-IDJ 161 |
| | TC-IDD 321 |
| | TC-ODD 321 |
| | TC-IAH 161 |
| Controller | ALLEN-BRADLEY SLC 500 |
| - suitable I/O card | 1746 OA16 |
| | 1746 OW16 |

Color code

| | |
|---|---------------------------------------|
| Connector 1 = connector 2 (optional) = wire color | IDC/FLK50 (1) = IDC/FLK50 (1) = black |
| | IDC/FLK50 (2) = IDC/FLK50 (2) = brown |

Cable - CABLE-FLK50/0,14/HF/ 3,0M - 2314189

Technical data

Color code

| | |
|--|---|
| | IDC/FLK50 (3) = IDC/FLK50 (3) = red |
| | IDC/FLK50 (4) = IDC/FLK50 (4) = orange |
| | IDC/FLK50 (5) = IDC/FLK50 (5) = yellow |
| | IDC/FLK50 (6) = IDC/FLK50 (6) = green |
| | IDC/FLK50 (7) = IDC/FLK50 (7) = blue |
| | IDC/FLK50 (8) = IDC/FLK50 (8) = violet |
| | IDC/FLK50 (9) = IDC/FLK50 (9) = gray |
| | IDC/FLK50 (10) = IDC/FLK50 (10) = white |
| | IDC/FLK50 (11) = IDC/FLK50 (11) = white-black |
| | IDC/FLK50 (12) = IDC/FLK50 (12) = white-brown |
| | IDC/FLK50 (13) = IDC/FLK50 (13) = white-red |
| | IDC/FLK50 (14) = IDC/FLK50 (14) = white-orange |
| | IDC/FLK50 (15) = IDC/FLK50 (15) = white-yellow |
| | IDC/FLK50 (16) = IDC/FLK50 (16) = white-green |
| | IDC/FLK50 (17) = IDC/FLK50 (17) = white-blue |
| | IDC/FLK50 (18) = IDC/FLK50 (18) = white-violet |
| | IDC/FLK50 (19) = IDC/FLK50 (19) = white-gray |
| | IDC/FLK50 (20) = IDC/FLK50 (20) = brown-black |
| | IDC/FLK50 (21) = IDC/FLK50 (21) = brown-red |
| | IDC/FLK50 (22) = IDC/FLK50 (22) = brown-orange |
| | IDC/FLK50 (23) = IDC/FLK50 (23) = brown-yellow |
| | IDC/FLK50 (24) = IDC/FLK50 (24) = brown-green |
| | IDC/FLK50 (25) = IDC/FLK50 (25) = brown-blue |
| | IDC/FLK50 (26) = IDC/FLK50 (26) = brown-violet |
| | IDC/FLK50 (27) = IDC/FLK50 (27) = brown-gray |
| | IDC/FLK50 (28) = IDC/FLK50 (28) = brown-white |
| | IDC/FLK50 (29) = IDC/FLK50 (29) = green-black |
| | IDC/FLK50 (30) = IDC/FLK50 (30) = green-brown |
| | IDC/FLK50 (31) = IDC/FLK50 (31) = green-red |
| | IDC/FLK50 (32) = IDC/FLK50 (32) = green-orange |
| | IDC/FLK50 (33) = IDC/FLK50 (33) = green-blue |
| | IDC/FLK50 (34) = IDC/FLK50 (34) = green-violet |
| | IDC/FLK50 (35) = IDC/FLK50 (35) = green-gray |
| | IDC/FLK50 (36) = IDC/FLK50 (36) = green-white |
| | IDC/FLK50 (37) = IDC/FLK50 (37) = yellow-black |
| | IDC/FLK50 (38) = IDC/FLK50 (38) = yellow-brown |
| | IDC/FLK50 (39) = IDC/FLK50 (39) = yellow-red |
| | IDC/FLK50 (40) = IDC/FLK50 (40) = yellow-orange |
| | IDC/FLK50 (41) = IDC/FLK50 (41) = yellow-blue |
| | IDC/FLK50 (42) = IDC/FLK50 (42) = yellow-violet |

Cable - CABLE-FLK50/0,14/HF/ 3,0M - 2314189

Technical data

Color code


| | |
|--|--|
| | IDC/FLK50 (43) = IDC/FLK50 (43) = yellow-gray |
| | IDC/FLK50 (44) = IDC/FLK50 (44) = yellow-white |
| | IDC/FLK50 (45) = IDC/FLK50 (45) = gray-black |
| | IDC/FLK50 (46) = IDC/FLK50 (46) = gray-brown |
| | IDC/FLK50 (47) = IDC/FLK50 (47) = gray-red |
| | IDC/FLK50 (48) = IDC/FLK50 (48) = gray-orange |
| | IDC/FLK50 (49) = IDC/FLK50 (49) = gray-yellow |
| | IDC/FLK50 (50) = IDC/FLK50 (50) = gray-green |

Environmental Product Compliance

| | |
|------------|---|
| China RoHS | Environmentally Friendly Use Period = 50 years |
| | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |

Drawings

Diagram



Maximum permissible current per path in uncoiled state

Classifications

eCl@ss

| | |
|---------------|----------|
| eCl@ss 10.0.1 | 27242220 |
| eCl@ss 4.0 | 27060300 |
| eCl@ss 4.1 | 27060300 |
| eCl@ss 5.0 | 27242200 |

Cable - CABLE-FLK50/0,14/HF/ 3,0M - 2314189

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 5.1 | 27242200 |
| eCl@ss 6.0 | 27249200 |
| eCl@ss 7.0 | 27249205 |
| eCl@ss 8.0 | 27249205 |
| eCl@ss 9.0 | 27242220 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000237 |
| ETIM 3.0 | EC000237 |
| ETIM 4.0 | EC000237 |
| ETIM 5.0 | EC000237 |
| ETIM 6.0 | EC000237 |
| ETIM 7.0 | EC000237 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 26121620 |
| UNSPSC 7.0901 | 26121620 |
| UNSPSC 11 | 26121620 |
| UNSPSC 12.01 | 26121620 |
| UNSPSC 13.2 | 26121620 |
| UNSPSC 18.0 | 26121620 |
| UNSPSC 19.0 | 26121620 |
| UNSPSC 20.0 | 26121620 |
| UNSPSC 21.0 | 26121620 |

Approvals

Approvals

Approvals

UL Listed / cUL Listed / EAC / cULus Listed

Ex Approvals

Approval details

Cable - CABLE-FLK50/0,14/HF/ 3,0M - 2314189

Approvals

| | | | |
|--------------------|--|---|---------------|
| UL Listed | | http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm | FILE E 238705 |
| Nominal voltage UN | | 125 V | |
| Nominal current IN | | 1 A | |

| | | | |
|--------------------|--|---|---------------|
| cUL Listed | | http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm | FILE E 238705 |
| Nominal voltage UN | | 125 V | |
| Nominal current IN | | 1 A | |

| | | |
|-----|--|-------------------------|
| EAC | | RU*- DE.HB*35.B00385 |
|-----|--|-------------------------|

| | |
|--------------|--|
| cULus Listed | |
|--------------|--|

Accessories

Accessories

Marker carrier cable

Cable marker carrier - KME - 0807083



Cable marker carrier, white, unlabeled, mounting type: Assembly with cable binders, cable diameter: > 5 mm, lettering field size: 20 mm x 8 mm

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2314189](#)