

# I/O module - IBS IP CDIO/R 24-8/SF - 2719564

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Digital input/output module, for use on robots, IP65 protection, 8 inputs, 24 V DC, 4-wire connection technology or 8 outputs, 24 V DC, 0.5 A, 3-wire connection technology, connection of additional signals on the back of the module

The figure shows version IBS IP CDIO/R 24-8

## Product Description

The IBS IP CDIO/R 24... modules are available as an input/output unit for the robot concept. The metal housing allows them to be used in welding applications. The module can be used directly on the welding transformer if it is mounted on a terminal box. The modules are connected via a 17-pin circular connector. In addition to the INTERBUS and power supply lines, this connector also carries two further signal lines for constant current regulation (CCR) and for secondary circuit monitoring (SCM). These signals are looped in on the underside of the .../SF devices and are needed at the welding current controller for control and monitoring tasks.

Two module types are available:

The IBS IP CDIO 24-8 ... module has 8 channels that can be used either as inputs or as outputs.

The IBS IP CDIO 24-12/4/8 .. module has 12 inputs and 8 outputs.

## Your advantages

- IP65 degree of protection
- Electrical isolation of I/O and bus logic



## Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4017918241650

## Technical data

### Dimensions

Width	54 mm
Height	150 mm
Depth	62 mm

### Ambient conditions

Degree of protection	IP65
----------------------	------

# I/O module - IBS IP CDIO/R 24-8/SF - 2719564

## Technical data

### Interfaces

Interface	Installation remote bus
-----------	-------------------------

### Power supply

Residual ripple	3.6 V <sub>pp</sub>
-----------------	---------------------

### Inputs

Number of inputs	8
Connection technology	4-wire
Input voltage	24 V DC
Input voltage range "0" signal	-30 V ... 5 V
Input voltage range "1" signal	13 V ... 30 V

### Outputs

Number of outputs	7
Connection technology	3-conductor (shielded)
Type of protection	Short-circuit protection, polarity reversal protection

### General

Weight	800 g
--------	-------

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

## Classifications

### eCl@ss

eCl@ss 10.0.1	27242604
eCl@ss 4.0	27250300
eCl@ss 4.1	27250300
eCl@ss 5.0	27250300
eCl@ss 5.1	27242600
eCl@ss 6.0	27242600
eCl@ss 7.0	27242604
eCl@ss 8.0	27242604
eCl@ss 9.0	27242604

### ETIM

ETIM 2.0	EC001430
ETIM 3.0	EC001599
ETIM 4.0	EC001599
ETIM 5.0	EC001599
ETIM 6.0	EC001599
ETIM 7.0	EC001599

# I/O module - IBS IP CDIO/R 24-8/SF - 2719564

## Classifications

### UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	32151602
UNSPSC 18.0	32151602
UNSPSC 19.0	32151602
UNSPSC 20.0	32151602
UNSPSC 21.0	32151602

## Accessories

### Accessories

#### Circular connector (cable-side)

Cable connector - TGGM/CDIO/17-ST - 1667895



INTERBUS remote bus connectors, straight, with contacts 12x 1597862, 5x 1602996, with IP68 cable gland Pg16, pin contact insert

Cable connector - TGGM/CDIO/17-BU - 1667905



INTERBUS remote bus connector, straight, with contacts 12x 1599600, 5x 1602998, with IP68 cable gland Pg16, socket contact insert

Cable connector - TWGM/CDIO/17-ST - 1667950



INTERBUS remote bus connector, angled, with contacts, male contact insert

## I/O module - IBS IP CDIO/R 24-8/SF - 2719564

### Accessories

Cable connector - TWGM/CDIO/17-BU - 1667963



INTERBUS remote bus connector, angled, with contacts, female contact insert

---

### Protective cap

Protective cap - MSK 2 - 1665907



M23 metal sealing cap, for unoccupied M23 connectors, with steel wire

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2719564](#)