

Printed-circuit board connector - VIP/S/FRONT-MC/KIT 9-16 - 2907270

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)


Pair of screw-clamp plugs to connect to VIP base module labeled 9-16



Your advantages

- Screw-clamp terminal wire connection
- Pre-printed channel and shield labeling

Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 257037
GTIN	4055626257037

Technical data

Dimensions

Width	44.68 mm
Height	12.3 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C

General

Nominal voltage U_N	300 V (maximum continuous operating voltage)
Max. permissible current	8 A

Connection data

Connection name	Controller level
Connection method	Screw connection
Stripping length	9 mm
Number of positions	9

Printed-circuit board connector - VIP/S/FRONT-MC/KIT 9-16 - 2907270

Technical data

Connection data

Conductor cross section solid	0.14 mm ² ... 1.5 mm ²
Conductor cross section flexible	0.14 mm ² ... 1.5 mm ²
Conductor cross section AWG	28 ... 16
Torque	0.22 Nm ... 0.25 Nm

Classifications

eCl@ss

eCl@ss 10.0.1	27371392
eCl@ss 4.0	27378000
eCl@ss 4.1	27378000
eCl@ss 5.0	27379100
eCl@ss 5.1	27379100
eCl@ss 6.0	27379200
eCl@ss 7.0	27379201
eCl@ss 8.0	27379201
eCl@ss 9.0	27379201

ETIM

ETIM 4.0	EC002498
ETIM 5.0	EC002498
ETIM 6.0	EC002498
ETIM 7.0	EC002498

UNSPSC

UNSPSC 13.2	39121409
UNSPSC 18.0	39121421
UNSPSC 19.0	39121421
UNSPSC 20.0	39121421
UNSPSC 21.0	39121421

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2907270](#)