

# Industrial Ethernet Switch - FL SWITCH SMCS 8TX-PN - 2989103

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Ethernet Smart Managed Compact Switch with eight 10/100 Mbps RJ45 ports, PROFINET mode (default)

## Product Description


The Smart Managed Compact Switch (SMCS) is an Ethernet switch suitable for industrial applications with eight Fast Ethernet ports in RJ45 format. The switch has "PROFINET" mode activated by default.

## Your advantages

- Web-based management, SNMP
- SNMP
- MRP (client and master)
- RSTP
- VLANs



## Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 320757
GTIN	4046356320757

## Technical data

### Dimensions

Width	128 mm
Height	110 mm
Depth	69 mm

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	0 °C ... 60 °C (non-condensing)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)

# Industrial Ethernet Switch - FL SWITCH SMCS 8TX-PN - 2989103

## Technical data

### Ambient conditions

Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)
Air pressure (operation)	86 kPa ... 108 kPa (2000 m above sea level)
Air pressure (storage/transport)	66 kPa ... 108 kPa (3500 m above sea level)

### Interfaces

Interface	Ethernet (RJ45)
No. of ports	8 (RJ45 ports)
Note on the connection method	Auto negotiation and autocrossing
Transmission physics	Copper
Transmission speed	10/100 Mbps
Transmission length	100 m (per segment)
Signal LEDs	Supply voltage, data transmission, error, link, activity
Interface	Serial (RS-232)
Connection method	RS-232-C, 6-pos. MINI-DIN socket (PS/2)

### Function

Basic functions	Store-and-forward switch complies with IEEE 802.3 4 priority classes in acc. with IEEE 802.1 P TCP/IP protocol, BootP-capable, port-mirroring, integrated web server function, multicast filtering, IGMP snooping, VLAN, Rapid Spanning Tree (RSTP), PROFINET Device, Media Redundancy Protocol (MRP).	
Management	Web-based management (HTTP)	
	SNMP v1/v2	
	Serial interface (V.24)	
Diagnostic functions	RMON History	
	N:1-Portmirroring	
	LLDP (Link Layer Discovery Protocol)	
	SNMP-Traps	
	ACD (Address Conflict Detection)	
	Filter functions	Quality of Service (4 priority classes)
Filter functions	Port-Priorisierung	
	VLAN	
	IGMP Snooping (128 groups)	
	IGMP Query	
	Auto-Query-Port	
	Extended Multicast Filtering	
	Static Multicast Filtering	
	Redundancy	MRP (Media Redundancy Protocol)
	Redundancy	RSTP (Rapid Spanning Tree Protocol)
FRD (Fast Ring Detection)		
Large Tree Support		
Additional functions	BootP	
	DHCP-Client	

# Industrial Ethernet Switch - FL SWITCH SMCS 8TX-PN - 2989103

## Technical data

### Function

Supported browsers	Internet Explorer 5.5 or higher
MAC address table	4000
PROFINET device function	PROFINET device
	Fast Startup
PROFINET conformance class	Conformance-Class B
Time synchronization	SNTP
Status and diagnostic indicators	LEDs: US1, US2 (power supply), Fail (alarm contact), 2 LEDs per Ethernet port (Link and switchable Activity/Speed/Duplex)
Signal contact control voltage	24 V (typical)
Signal contact control current	600 mA

### Security functions

Link Layer Discovery Protocol (LLDP)	As per protocol 802.2
--------------------------------------	-----------------------

### Network expansion parameters

Cascading depth	Network, linear, and star structure: any
Maximum conductor length (twisted pair)	100 m

### Supply voltage

Supply voltage	24 V DC (redundant)
Residual ripple	3.6 V <sub>PP</sub> (within the permitted voltage range)
Supply voltage range	18 V DC ... 32 V DC
Typical current consumption	240 mA (at U <sub>S</sub> = 24 V DC)
Current consumption	600 mA

### General

Mounting type	DIN rail
Type AX	Block design
Net weight	650 g

### Connection data

Connection method	Screw connection
Conductor cross section solid min.	0.2 mm <sup>2</sup>
Conductor cross section solid max.	2.5 mm <sup>2</sup>
Conductor cross section flexible min.	0.2 mm <sup>2</sup>
Conductor cross section flexible max.	2.5 mm <sup>2</sup>
Conductor cross section AWG min.	24
Conductor cross section AWG max.	12
Stripping length	7 mm

### Standards and Regulations

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Noise emission	EN 61000-6-3 +A11
Noise immunity	EN 61000-6-2:2005

# Industrial Ethernet Switch - FL SWITCH SMCS 8TX-PN - 2989103

## Technical data

### Standards and Regulations

Vibration (storage/transport)	5g, 10 Hz ... 150 Hz, in accordance with IEC 60068-2-6
Free from substances that could impair the application of coating	Yes
Vibration (operation)	in accordance with IEC 60068-2-6: 5g, 10 Hz ... 150 Hz

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

## Classifications

### eCl@ss

eCl@ss 10.0.1	19170401
eCl@ss 4.0	27250500
eCl@ss 4.1	27250500
eCl@ss 5.0	19030100
eCl@ss 5.1	19030100
eCl@ss 6.0	19170100
eCl@ss 7.0	19170106
eCl@ss 8.0	19170106
eCl@ss 9.0	19170106

### ETIM

ETIM 2.0	EC000734
ETIM 3.0	EC000734
ETIM 4.0	EC000734
ETIM 5.0	EC000734
ETIM 6.0	EC000734
ETIM 7.0	EC000734

### UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201410
UNSPSC 13.2	43222612
UNSPSC 18.0	43222612
UNSPSC 19.0	43222612
UNSPSC 20.0	43222612
UNSPSC 21.0	43222612

# Industrial Ethernet Switch - FL SWITCH SMCS 8TX-PN - 2989103

## Approvals

Approvals

---

Approvals

UL Listed / cUL Listed / EAC / EAC / EAC / cULus Listed

---

Ex Approvals

---

## Approval details

UL Listed		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 140324
-----------	--	---	---------------

cUL Listed		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 140324
------------	--	---	---------------

EAC			EAC-Zulassung
-----	--	--	---------------

EAC			RU *- DE.A*30.B.01735
-----	--	--	--------------------------

EAC			RU* - DE.*.B.00741/19
-----	--	--	--------------------------

cULus Listed			
--------------	--	--	--

## Accessories

Accessories

Configuration memory

# Industrial Ethernet Switch - FL SWITCH SMCS 8TX-PN - 2989103

## Accessories

Configuration memory - FL MEM PLUG - 2891259



Exchangeable configuration memory of the device settings for simple device exchange and set-up

---

Configuration memory - FL MEM PLUG/MRM - 2891275



Exchangeable configuration memory of the device settings for simple device exchange and set-up In addition, the Media Redundancy Manager (MRM) license for use is stored within the Media Redundancy protocol (MRP).

---

## Drivers and interfaces

Software - FL SNMP OPC SERVER V3 - 2701139



SNMP-OPC server, German and English, for monitoring and configuration of SNMP-capable equipment in HMI and SCADA systems

---

## Patch cable

Patch cable - FL CAT6 PATCH 0,3 - 2891181



Patch cable, CAT6, pre-assembled, 0.3 m

---

Patch cable - FL CAT6 PATCH 0,5 - 2891288



Patch cable, CAT6, pre-assembled, 0.5 m

---

## Industrial Ethernet Switch - FL SWITCH SMCS 8TX-PN - 2989103

### Accessories

Patch cable - FL CAT6 PATCH 1,0 - 2891385



Patch cable, CAT6, pre-assembled, 1.0 m

---

Patch cable - FL CAT6 PATCH 1,5 - 2891482



Patch cable, CAT6, pre-assembled, 1.5 m

---

Patch cable - FL CAT6 PATCH 2,0 - 2891589



Patch cable, CAT6, pre-assembled, 2.0 m

---

Patch cable - FL CAT6 PATCH 3,0 - 2891686



Patch cable, CAT6, pre-assembled, 3.0 m

---

Patch cable - FL CAT6 PATCH 5,0 - 2891783



Patch cable, CAT6, pre-assembled, 5.0 m

---

# Industrial Ethernet Switch - FL SWITCH SMCS 8TX-PN - 2989103

## Accessories

Patch cable - FL CAT6 PATCH 7,5 - 2891880



Patch cable, CAT6, pre-assembled, 7.5 m

---

Patch cable - FL CAT6 PATCH 10 - 2891877



Patch cable, CAT6, pre-assembled, 10 m

---

Patch cable - FL CAT6 PATCH 12,5 - 2891369



Patch cable, CAT6, pre-assembled, 12.5 m

---

Patch cable - FL CAT6 PATCH 15,0 - 2891372



Patch cable, CAT6, pre-assembled, 15.0 m

---

Patch cable - FL CAT6 PATCH 20,0 - 2891576



Patch cable, CAT6, pre-assembled, 20.0 m

---

## Programming cable



## Industrial Ethernet Switch - FL SWITCH SMCS 8TX-PN - 2989103

### Accessories

Connecting cable - COM CAB MINI DIN - 2400127



Connecting cable, for connecting the controller to a PC (RS-232) for PC WORX with flow control, 3 m in length

Software - IPASSIGN - 2701094



IPAssign is an easy to use tool for setting the IP address of devices which rely on BOOTP. No installation or administrative rights are required to use IPAssign.

This product is free and only available from the "Downloads" tab.

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2989103](#)