

Flange cover - DFS-SPB 2,5 - 3061444

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Flange cover, length: 35.8 mm, width: 4.5 mm, height: 24.7 mm, color: gray

Can be snapped on

Product Description


Flange cover, can be snapped onto SPB 2,5/... connectors

Your advantages

- Same shape and pitch as the basic terminal blocks
- Automatic latching in self-locking flange



Key Commercial Data

| | |
|--------------|---|
| Packing unit | 50 pc |
| GTIN |  4 046356 556484 |
| GTIN | 4046356556484 |

Technical data

General

| | |
|--|------|
| Color | gray |
| Material | PA |
| Flammability rating according to UL 94 | V0 |

Dimensions

| | |
|--------|---------|
| Width | 4.5 mm |
| Length | 35.8 mm |
| Height | 24.7 mm |

General

| | |
|--|--|
| Ambient temperature (operation) | -60 °C ... 85 °C |
| Ambient temperature (storage/transport) | -25 °C ... 55 °C (For a short time, not exceeding 24 h, -60 to +70 °C) |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

Flange cover - DFS-SPB 2,5 - 3061444

Technical data

General

| | |
|---|-----------------|
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Ambient temperature (actuation) | -5 °C ... 70 °C |
| Relative insulation material temperature index (Elec., UL 746 B) | 130 °C |
| Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21)) | 130 °C |
| Static insulating material application in cold | -60 °C |
| Surface flammability NFPA 130 (ASTM E 162) | passed |
| Specific optical density of smoke NFPA 130 (ASTM E 662) | passed |
| Calorimetric heat release NFPA 130 (ASTM E 1354) | 28 MJ/kg |
| Smoke gas toxicity NFPA 130 (SMP 800C) | passed |
| Fire protection for rail vehicles (DIN EN 45545-2) R22 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R23 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R24 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R26 | HL 1 - HL 3 |

Standards and Regulations

| | |
|--|----|
| Flammability rating according to UL 94 | V0 |
|--|----|

Environmental Product Compliance

| | |
|------------|---|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
| | No hazardous substances above threshold values |

Classifications

eCl@ss

| | |
|---------------|----------|
| eCl@ss 10.0.1 | 27141133 |
| eCl@ss 4.0 | 21011300 |
| eCl@ss 4.1 | 21011300 |
| eCl@ss 5.0 | 27141100 |
| eCl@ss 5.1 | 27141100 |
| eCl@ss 6.0 | 27141100 |
| eCl@ss 7.0 | 27141133 |
| eCl@ss 8.0 | 27141133 |
| eCl@ss 9.0 | 27141133 |

ETIM

| | |
|----------|----------|
| ETIM 4.0 | EC000886 |
| ETIM 5.0 | EC000886 |
| ETIM 6.0 | EC000886 |
| ETIM 7.0 | EC000886 |

UNSPSC

| | |
|-------------|----------|
| UNSPSC 6.01 | 30211812 |
|-------------|----------|

Flange cover - DFS-SPB 2,5 - 3061444

Classifications

UNSPSC

| | |
|---------------|----------|
| UNSPSC 7.0901 | 39121411 |
| UNSPSC 11 | 39121411 |
| UNSPSC 12.01 | 39121411 |
| UNSPSC 13.2 | 39121425 |
| UNSPSC 18.0 | 39121425 |
| UNSPSC 19.0 | 39121425 |
| UNSPSC 20.0 | 39121425 |
| UNSPSC 21.0 | 39121425 |

Accessories

Additional products

Latching flange - ST 2,5/1P-FS - 3061376



Latching flange, width: 5.2 mm, height: 35.3 mm, color: gray, mounting type: NS 35/7,5, NS 35/15

Latching flange - ST 2,5-TWIN/1P-FS - 3061389



Latching flange, width: 5.2 mm, height: 35.3 mm, color: gray, mounting type: NS 35/7,5, NS 35/15

Latching flange - ST 2,5-QUATTRO/2P-FS - 3061392



Latching flange, width: 5.2 mm, height: 35.3 mm, color: gray, mounting type: NS 35/7,5, NS 35/15

Latching flange - ST 2,5-QUATTRO/4P-FS - 3061402



Latching flange, width: 5.2 mm, height: 35.3 mm, color: gray, mounting type: NS 35/7,5, NS 35/15

Flange cover - DFS-SPB 2,5 - 3061444

Accessories

Latching flange - ST 2,5/2P-FS - 3061415



Latching flange, width: 5.2 mm, height: 35.3 mm, color: gray, mounting type: NS 35/7,5, NS 35/15

Latching flange - STTB 2,5/2P-FS - 3061428



Latching flange, width: 5.2 mm, height: 40 mm, color: gray, mounting type: NS 35/7,5, NS 35/15

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[3061444](#)