

## Fuse modular terminal block - UK 10,3 HESILED 1000V - 3211249

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Fuse terminal block with light indicator, for cartridge fuse insert 10.3 x 38 mm, cross section: 1.5 - 25 mm<sup>2</sup>, AWG: 16 - 4, width: 18 mm, color: Black

### Your advantages

- ✓ Quick identification of faulty fuses regardless of the current direction, thanks to LED status indicator
- ✓ For 10 x 38 gPV fuse-links in accordance with IEC 60269-6
- ✓ Easy to bridge
- ✓ For 10 x 38 gPV fuse-links in accordance with IEC 60269-6
- ✓ Fuse holder for fusing 400 V – 1000 V DC PV strings

### Key Commercial Data

Packing unit	10 pc
GTIN	 4 046356 482400
GTIN	4046356482400

### Technical data

#### General

Number of levels	1
Number of connections	2
Nominal cross section	16 mm <sup>2</sup>
Color	black
Insulating material	PA
Flammability rating according to UL 94	V0
Maximum power dissipation for nominal condition	2.43 W
Fuse	10:3 x 38 mm
Fuse type	Glass / ceramics / ...
Rated surge voltage	6 kV
Degree of pollution	3

# Fuse modular terminal block - UK 10,3 HESILED 1000V - 3211249

## Technical data

### General

Overvoltage category	II
Insulating material group	IIIb
Connection in acc. with standard	IEC 60269-1 / -2
Maximum load current	30 A (the current and voltage are determined by the fuse)
Nominal current $I_N$	30 A (the current and voltage are determined by the fuse)
Nominal voltage $U_N$	1000 V (the current and voltage are determined by the fuse)
Open side panel	No

### Dimensions

Width	18 mm
Length	81 mm
Height NS 35/7,5	65.5 mm
Height NS 35/15	73 mm

### Ambient conditions

Ambient temperature (operation)	-60 °C ... 85 °C
Ambient temperature (storage/transport)	-25 °C ... 55 °C (For a short time, not exceeding 24 h, -60 to +70 °C)
Permissible humidity (storage/transport)	30 % ... 70 %
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C

### Connection data

Conductor cross section solid min.	0.75 mm <sup>2</sup>
Conductor cross section solid max.	25 mm <sup>2</sup>
Conductor cross section flexible min.	0.75 mm <sup>2</sup>
Conductor cross section flexible max.	25 mm <sup>2</sup>
Conductor cross section AWG min.	16
Conductor cross section AWG max.	3
Conductor cross section flexible, with ferrule without plastic sleeve min.	0.75 mm <sup>2</sup>
Conductor cross section flexible, with ferrule without plastic sleeve max.	16 mm <sup>2</sup>
Conductor cross section flexible, with ferrule with plastic sleeve min.	0.75 mm <sup>2</sup>
Conductor cross section flexible, with ferrule with plastic sleeve max.	16 mm <sup>2</sup>
Cross section with insertion bridge, solid max.	10 mm <sup>2</sup>
Cross section with insertion bridge, stranded max.	10 mm <sup>2</sup>
2 conductors with same cross section, solid min.	0.75 mm <sup>2</sup>
2 conductors with same cross section, solid max.	4 mm <sup>2</sup>
2 conductors with same cross section, stranded min.	0.75 mm <sup>2</sup>
2 conductors with same cross section, stranded max.	4 mm <sup>2</sup>
Two conductors with the same cross section stranded, with ferrule and without plastic sleeve, minimum	0.75 mm <sup>2</sup>
Two conductors with the same cross section stranded, with ferrule and without plastic sleeve, maximum	4 mm <sup>2</sup>

# Fuse modular terminal block - UK 10,3 HESILED 1000V - 3211249

## Technical data

### Connection data

Two conductors with the same cross section, flexible, with TWIN ferrules, with plastic sleeve, minimum	0.75 mm <sup>2</sup>
Two conductors with the same cross section, flexible, with TWIN ferrules, with plastic sleeve, maximum	10 mm <sup>2</sup>
Cross section with insertion bridge, solid max.	10 mm <sup>2</sup>
Cross section with insertion bridge, stranded max.	10 mm <sup>2</sup>
Connection method	Screw connection
Stripping length	12 mm
Internal cylindrical gage	B6
Screw thread	M5
Tightening torque, min	2.5 Nm
Tightening torque max	3 Nm

### Standards and Regulations


Connection in acc. with standard	IEC 60269-1 / -2
Flammability rating according to UL 94	V0

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Drawings

Circuit diagram



# Fuse modular terminal block - UK 10,3 HESILED 1000V - 3211249

## Classifications

### eCl@ss

eCl@ss 10.0.1	27141116
eCl@ss 4.0	27141100
eCl@ss 4.1	27141100
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27141116
eCl@ss 8.0	27141116
eCl@ss 9.0	27141116

### ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000899
ETIM 4.0	EC000899
ETIM 5.0	EC000899
ETIM 6.0	EC000899
ETIM 7.0	EC000899

### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410
UNSPSC 18.0	39121410
UNSPSC 19.0	39121410
UNSPSC 20.0	39121410
UNSPSC 21.0	39121410

## Approvals

### Approvals

---

Approvals

UL Listed / EAC / EAC

---


Ex Approvals

---

### Approval details

# Fuse modular terminal block - UK 10,3 HESILED 1000V - 3211249

## Approvals

UL Listed		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 353282
Nominal voltage UN		1000 V	
Nominal current IN		30 A	
mm <sup>2</sup> /AWG/kcmil		18-8	

EAC		RU C- DE.AI30.B.01102
-----	---	--------------------------

EAC		RU C- DE.BL08.B.00534
-----	---	--------------------------

## Accessories

### Accessories

#### Connector

Connection pin - VS-UK 10,3-HESI N 2POL - 3048532



Connection pin, plastic, for coupling two fuse terminal blocks, color: black, diameter: 3 mm

Connection pin - VS-UK 10,3-HESI N 3POL - 3048409



Connection pin, plastic, for coupling three fuse terminal blocks, color: black, diameter: 3 mm

#### DIN rail

DIN rail perforated - NS 35/ 7,5 PERF 2000MM - 0801733



DIN rail perforated, Standard profile, width: 35 mm, height: 7.5 mm, acc. to EN 60715, material: Steel, galvanized, passivated with a thick layer, length: 2000 mm, color: silver

## Fuse modular terminal block - UK 10,3 HESILED 1000V - 3211249

### Accessories

---

DIN rail, unperforated - NS 35/ 7,5 UNPERF 2000MM - 0801681



DIN rail, unperforated, Standard profile, width: 35 mm, height: 7.5 mm, acc. to EN 60715, material: Steel, galvanized, passivated with a thick layer, length: 2000 mm, color: silver

---

DIN rail perforated - NS 35/ 7,5 WH PERF 2000MM - 1204119



DIN rail perforated, Standard profile, width: 35 mm, height: 7.5 mm, acc. to EN 60715, material: Steel, Galvanized, white passivated, length: 2000 mm, color: silver

---

DIN rail, unperforated - NS 35/ 7,5 WH UNPERF 2000MM - 1204122



DIN rail, unperforated, Standard profile, width: 35 mm, height: 7.5 mm, acc. to EN 60715, material: Steel, Galvanized, white passivated, length: 2000 mm, color: silver

---

DIN rail, unperforated - NS 35/ 7,5 AL UNPERF 2000MM - 0801704



DIN rail, unperforated, Standard profile, width: 35 mm, height: 7.5 mm, acc. to EN 60715, material: Aluminum, uncoated, length: 2000 mm, color: silver

---

DIN rail perforated - NS 35/ 7,5 ZN PERF 2000MM - 1206421



DIN rail perforated, Standard profile, width: 35 mm, height: 7.5 mm, acc. to EN 60715, material: Steel, galvanized, length: 2000 mm, color: silver

---

## Fuse modular terminal block - UK 10,3 HESILED 1000V - 3211249

### Accessories

DIN rail, unperforated - NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



DIN rail, unperforated, Standard profile, width: 35 mm, height: 7.5 mm, acc. to EN 60715, material: Steel, galvanized, length: 2000 mm, color: silver

---

DIN rail, unperforated - NS 35/ 7,5 CU UNPERF 2000MM - 0801762



DIN rail, unperforated, Standard profile, width: 35 mm, height: 7.5 mm, acc. to EN 60715, material: Copper, uncoated, length: 2000 mm, color: copper-colored

---

End cap - NS 35/ 7,5 CAP - 1206560



DIN rail end piece, for DIN rail NS 35/7.5

---

DIN rail perforated - NS 35/15 PERF 2000MM - 1201730



DIN rail perforated, Standard profile, width: 35 mm, height: 15 mm, similar to EN 60715, material: Steel, galvanized, passivated with a thick layer, length: 2000 mm, color: silver

---

DIN rail, unperforated - NS 35/15 UNPERF 2000MM - 1201714



DIN rail, unperforated, Standard profile, width: 35 mm, height: 15 mm, similar to EN 60715, material: Steel, galvanized, passivated with a thick layer, length: 2000 mm, color: silver

---

## Fuse modular terminal block - UK 10,3 HESILED 1000V - 3211249

### Accessories

DIN rail perforated - NS 35/15 WH PERF 2000MM - 0806602



DIN rail perforated, Standard profile, width: 35 mm, height: 15 mm, similar to EN 60715, material: Steel, Galvanized, white passivated, length: 2000 mm, color: silver

---

DIN rail, unperforated - NS 35/15 WH UNPERF 2000MM - 1204135



DIN rail, unperforated, Standard profile, width: 35 mm, height: 15 mm, similar to EN 60715, material: Steel, Galvanized, white passivated, length: 2000 mm, color: silver

---

DIN rail, unperforated - NS 35/15 AL UNPERF 2000MM - 1201756



DIN rail, unperforated, Standard profile, width: 35 mm, height: 15 mm, similar to EN 60715, material: Aluminum, uncoated, length: 2000 mm, color: silver

---

DIN rail perforated - NS 35/15 ZN PERF 2000MM - 1206599



DIN rail perforated, Standard profile, width: 35 mm, height: 15 mm, similar to EN 60715, material: Steel, galvanized, length: 2000 mm, color: silver

---

DIN rail, unperforated - NS 35/15 ZN UNPERF 2000MM - 1206586



DIN rail, unperforated, Standard profile, width: 35 mm, height: 15 mm, similar to EN 60715, material: Steel, galvanized, length: 2000 mm, color: silver

---



## Fuse modular terminal block - UK 10,3 HESILED 1000V - 3211249

### Accessories

DIN rail, unperforated - NS 35/15 CU UNPERF 2000MM - 1201895



DIN rail, unperforated, Standard profile, width: 35 mm, height: 15 mm, similar to EN 60715, material: Copper, uncoated, length: 2000 mm, color: copper-colored

---

End cap - NS 35/15 CAP - 1206573



DIN rail end piece, for DIN rail NS 35/15

---

DIN rail, unperforated - NS 35/15-2,3 UNPERF 2000MM - 1201798



DIN rail, unperforated, Standard profile 2.3 mm, width: 35 mm, height: 15 mm, acc. to EN 60715, material: Steel, galvanized, passivated with a thick layer, length: 2000 mm, color: silver

---

End block

End clamp - CLIPFIX 35 - 3022218



Quick mounting end clamp for NS 35/7,5 DIN rail or NS 35/15 DIN rail, with marking option, width: 9.5 mm, color: gray

---

End clamp - CLIPFIX 35-5 - 3022276



Quick mounting end clamp for NS 35/7,5 DIN rail or NS 35/15 DIN rail, with marking option, with parking option for FBS...5, FBS...6, KSS 5, KSS 6, width: 5.15 mm, color: gray

---

## Fuse modular terminal block - UK 10,3 HESILED 1000V - 3211249

### Accessories

End clamp - E/NS 35 N - 0800886



End clamp, width: 9.5 mm, color: gray

---

### Fuse

Fuse - FUSE 10,3X38 2A PV - 3061295



Fuse, 10.3x38 mm, up to 1000 V DC, gPV characteristics

---

Fuse - FUSE 10,3X38 4A PV - 3061305



Fuse, 10.3x38 mm, up to 1000 V DC, gPV characteristics

---

Fuse - FUSE 10,3X38 6A PV - 3061318



Fuse, 10.3x38 mm, up to 1000 V DC, gPV characteristics

---

Fuse - FUSE 10,3X38 8A PV - 3061321



Fuse, 10.3x38 mm, up to 1000 V DC, gPV characteristics

---

## Fuse modular terminal block - UK 10,3 HESILED 1000V - 3211249

### Accessories

Fuse - FUSE 10,3X38 10A PV - 3061334



Fuse, 10.3x38 mm, up to 1000 V DC, gPV characteristics

---

Fuse - FUSE 10,3X38 12A PV - 3061347



Fuse, 10.3x38 mm, up to 1000 V DC, gPV characteristics

---

Fuse - FUSE 10,3X38 16A PV - 3061350



Fuse, 10.3x38 mm, up to 1000 V DC, gPV characteristics

---

Fuse - FUSE 10,3X38 20A PV - 3061363



Fuse, 10.3x38 mm, up to 1000 V DC, gPV characteristics

---

Fuse - FUSE 10,3X38 25A PV - 3061364



Fuse, 10.3x38 mm, up to 1000 V DC, gPV characteristics

---

## Fuse modular terminal block - UK 10,3 HESILED 1000V - 3211249

### Accessories

Fuse - FUSE 10,3X38 15A PV - 3061348



Fuse, 10.3x38 mm, up to 1000 V DC, gPV characteristics

---

Fuse - FUSE 10,3X38 2A PV - 3061295



Fuse, 10.3x38 mm, up to 1000 V DC, gPV characteristics

---

Fuse - FUSE 10,3X38 4A PV - 3061305



Fuse, 10.3x38 mm, up to 1000 V DC, gPV characteristics

---

Fuse - FUSE 10,3X38 6A PV - 3061318



Fuse, 10.3x38 mm, up to 1000 V DC, gPV characteristics

---

Fuse - FUSE 10,3X38 8A PV - 3061321



Fuse, 10.3x38 mm, up to 1000 V DC, gPV characteristics

---

## Fuse modular terminal block - UK 10,3 HESILED 1000V - 3211249

### Accessories

Fuse - FUSE 10,3X38 10A PV - 3061334



Fuse, 10.3x38 mm, up to 1000 V DC, gPV characteristics

---

Fuse - FUSE 10,3X38 12A PV - 3061347



Fuse, 10.3x38 mm, up to 1000 V DC, gPV characteristics

---

Fuse - FUSE 10,3X38 15A PV - 3061348



Fuse, 10.3x38 mm, up to 1000 V DC, gPV characteristics

---

Fuse - FUSE 10,3X38 16A PV - 3061350



Fuse, 10.3x38 mm, up to 1000 V DC, gPV characteristics

---

Fuse - FUSE 10,3X38 20A PV - 3061363



Fuse, 10.3x38 mm, up to 1000 V DC, gPV characteristics

---

## Fuse modular terminal block - UK 10,3 HESILED 1000V - 3211249

### Accessories

Fuse - FUSE 10,3X38 25A PV - 3061364



Fuse, 10.3x38 mm, up to 1000 V DC, gPV characteristics

---

Fuse - FUSE 10,3X38 25A PV 900V - 3061365



Fuse, 10.3 mm x 38 mm, up to 900 V DC, gPV characteristic

---

Fuse - FUSE 10,3X38 6A PV A - 3062778



Fuse, for the photovoltaics industry according to UL 2579, length: 38 mm, diameter: 10.3 mm, color: white

---

Fuse - FUSE 10,3X38 8A PV A - 3062779



Fuse, for the photovoltaics industry according to UL 2579, length: 38 mm, diameter: 10.3 mm, color: white

---

Fuse - FUSE 10,3X38 10A PV A - 3062780



Fuse, for the photovoltaics industry according to UL 2579, length: 38 mm, diameter: 10.3 mm, color: white

---

## Fuse modular terminal block - UK 10,3 HESILED 1000V - 3211249

### Accessories

Fuse - FUSE 10,3X38 12A PV A - 3062781



Fuse, for the photovoltaics industry according to UL 2579, length: 38 mm, diameter: 10.3 mm, color: white

---

Fuse - FUSE 10,3X38 16A PV A - 3062782



Fuse, for the photovoltaics industry according to UL 2579, length: 38 mm, diameter: 10.3 mm, color: white

---

Fuse - FUSE 10,3X38 15A PV A - 3062784



Fuse, for the photovoltaics industry according to UL 2579, length: 38 mm, diameter: 10.3 mm, color: white

---

Fuse - FUSE 10,3X38 25A PV A - 3062785



Fuse, for the photovoltaics industry according to UL 2579, nominal current: 25 A, length: 38 mm, diameter: 10.3 mm, color: white

---

### Insertion bridge

Insertion bridge - EB 56-18/L1-L2-L3 - 3009367



Insertion bridge, pitch: 18 mm, number of positions: 56, color: gray

---

## Fuse modular terminal block - UK 10,3 HESILED 1000V - 3211249

### Accessories

Insertion bridge - EB 56-18 - 3009299



Insertion bridge, pitch: 18 mm, number of positions: 56, color: gray

Insertion bridge - EB 2-18 - 3009300



Insertion bridge, pitch: 17.8 mm, number of positions: 2, color: light gray

Insertion bridge - EB 3-18 - 3009305



Insertion bridge, pitch: 17.8 mm, number of positions: 3, color: light gray

### Labeled terminal marker

Zack Marker strip, flat - ZBF 16 CUS - 0827465



Zack Marker strip, flat, can be ordered: Strip, white, labeled according to customer specifications, mounting type: snap into flat marker groove, for terminal block width: 16 mm, lettering field size: 5.15 x 16 mm, Number of individual labels: 5

Marker for terminal blocks - UC-TMF 16 CUS - 0824678



Marker for terminal blocks, can be ordered: by sheet, white, labeled according to customer specifications, mounting type: snap into flat marker groove, for terminal block width: 16 mm, lettering field size: 15.45 x 5.1 mm, Number of individual labels: 32



## Fuse modular terminal block - UK 10,3 HESILED 1000V - 3211249

### Accessories

Marker for terminal blocks - UCT-TMF 16 CUS - 0829693



Marker for terminal blocks, can be ordered: by sheet, white, labeled according to customer specifications, mounting type: snap into flat marker groove, for terminal block width: 16 mm, lettering field size: 15.2 x 4.7 mm, Number of individual labels: 24

---

### Screwdriver tools

Screwdriver - SF-SL 0,6X3,5-100 S-VDE - 1212587



Actuation tool, for ST terminal blocks, VDE insulated, with slimmer insulation integrated in the blade, also suitable for use as a bladed screwdriver, size: 0.6 x 3.5 x 100 mm, 2-component grip, with non-slip grip

---

Philips screwdriver - SZK PZ2 VDE - 1206463



Screwdriver, PZ crosshead, VDE insulated, size: PZ 2 x 100 mm, 2-component grip, with non-slip grip

---

Screwdriver - SZS 1,0X4,0 VDE - 1205066



Screwdriver, slot-headed, VDE insulated, size: 1.0 x 4.0 x 100 mm, 2-component grip, with non-slip grip

---

### Terminal marking

Zack Marker strip, flat - ZBF 16:UNPRINTED - 0827464



Zack Marker strip, flat, Strip, white, unlabeled, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, mounting type: snap into flat marker groove, for terminal block width: 16 mm, lettering field size: 16.25 x 10.5 mm, Number of individual labels: 50

## Fuse modular terminal block - UK 10,3 HESILED 1000V - 3211249

### Accessories

#### Marker for terminal blocks - UC-TMF 16 - 0819262



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: snap into flat marker groove, for terminal block width: 16 mm, lettering field size: 15.45 x 5.1 mm, Number of individual labels: 32

---

#### Marker for terminal blocks - UCT-TMF 16 - 0829218



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snap into flat marker groove, for terminal block width: 16 mm, lettering field size: 15.2 x 4.7 mm, Number of individual labels: 24

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[3211249](#)