

Cable binder base - WT-BASE LS HF 6 - 3240708


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Cable binder base, for cable binders up to 6 mm wide, self-adhesive (rubber) and screwable, 4.8 mm fixing hole, 4-sided cable binder feed-through



RoHS

Key Commercial Data

| | |
|------------------------|---|
| Packing unit | 100 pc |
| Minimum order quantity | 100 pc |
| GTIN |  4 046356 703956 |
| GTIN | 4046356703956 |

Technical data

Dimensions

| | |
|---------------|--------|
| Length (b) | 27 mm |
| Width (a) | 27 mm |
| Height (c) | 6.5 mm |
| Hole diameter | 4.8 mm |

Ambient conditions

| | |
|---------------------------------|------------------|
| Ambient temperature (operation) | -40 °C ... 60 °C |
| Ambient temperature (assembly) | -15 °C ... 40 °C |

General

| | |
|--|--------------------------------|
| Color | transparent |
| Type | Fixing |
| Components | free from silicone and halogen |
| Flammability rating according to UL 94 | HB |
| Material | ABS |
| Tensile strength | 0 N |

Standards and Regulations

Cable binder base - WT-BASE LS HF 6 - 3240708

Technical data

Standards and Regulations

| | |
|--|----|
| Flammability rating according to UL 94 | HB |
|--|----|

Environmental Product Compliance

| | |
|------------|---|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
| | No hazardous substances above threshold values |

Classifications

eCl@ss

| | |
|---------------|----------|
| eCl@ss 10.0.1 | 23159007 |
| eCl@ss 4.0 | 27140700 |
| eCl@ss 4.1 | 27140700 |
| eCl@ss 5.0 | 27140700 |
| eCl@ss 5.1 | 27140700 |
| eCl@ss 6.0 | 27140700 |
| eCl@ss 7.0 | 23159007 |
| eCl@ss 8.0 | 23159007 |
| eCl@ss 9.0 | 23159007 |

ETIM

| | |
|----------|----------|
| ETIM 3.0 | EC000046 |
| ETIM 4.0 | EC000046 |
| ETIM 5.0 | EC000046 |
| ETIM 6.0 | EC000449 |
| ETIM 7.0 | EC000449 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30212109 |
| UNSPSC 7.0901 | 27121703 |
| UNSPSC 11 | 27121703 |
| UNSPSC 12.01 | 27121703 |
| UNSPSC 13.2 | 27121703 |
| UNSPSC 19.0 | 39121731 |

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[3240708](#)