

Ferrule - A 120 -40 - 1090640

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Ferrule, length: 40 mm, color: silver

Your advantages

- The ferrules without plastic sleeve are made from soft tin-plated electrolytic copper



Key Commercial Data

Packing unit	50 pc
Minimum order quantity	50 pc
GTIN	 4 055626 901091
GTIN	4055626901091

Technical data

Dimensions

Length (b)	40 mm
Maximum stripping length	40 mm
Inner dimension of the insulating collar (d)	19 mm
Ferrule diameter	17.7 mm
Sleeve wall thickness	0.5 mm

Ambient conditions

Short-term temperature	120 °C
Max. permanent temperature	105 °C

General

Note	These ferrules are not included in DIN 46228-1: 1992-08
Color	silver
Material	CU-DHP
Coating	tin-plated (galvanic)

Ferrule - A 120 -40 - 1090640

Technical data

General

Conductor category	Stranded conductors, class 2, 5, 6 / B, C, K, M
--------------------	---

Classifications

eCl@ss

eCl@ss 10.0.1	27400201
eCl@ss 11.0	27400201
eCl@ss 9.0	27400201

ETIM

ETIM 6.0	EC000005
ETIM 7.0	EC000005

Accessories

Accessories

Crimping tool

Crimping pliers - CRIMPFOX-C120 - 1212318



Basic pliers, for accommodating dies for a wide range of type of contacts up to 120 mm²

Die

Replacement die - CRIMPFOX-C120 AI 120/DIE - 1209910



Die (pair), for CRIMPFOX-C120, for ferrules (DIN 46228) 120 mm², trapezoid crimp

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1090640](#)