


Sensor/actuator cable - SAC-5P-M12MS/ 2,0-927 VA - 1402938

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

5-pos. cable, black PVC, shielded, shielded plug, straight M12, A-coded, on free cable end with VA knurl, length: 2 m



Key Commercial Data

| | |
|------------------------|---|
| Packing unit | 1 pc |
| Minimum order quantity | 50 pc |
| GTIN |  4 046356 637589 |
| GTIN | 4046356637589 |

Technical data

General

| | |
|---------------------|---------|
| Rated voltage | 48 V AC |
| | 60 V DC |
| Number of positions | 5 |

Cable

| | |
|-------------------------------------|---|
| Cable type | DeviceNet™ |
| Cable type (abbreviation) | 927 |
| UL AWM style | 2464 (80°C/300 V) |
| Conductor cross section | 2x 0.34 mm² (Signal line) |
| | 2x 0.34 mm² (Power supply) |
| | 1x 0.38 mm² (Drain wire) |
| AWG signal line | 22 |
| AWG power supply | 22 |
| Conductor structure signal line | 44x 0.10 mm |
| Conductor structure, voltage supply | 44x 0.10 mm |
| Core diameter including insulation | 2.55 mm (Signal line) |
| | 1.37 mm (Power supply) |
| Thickness, insulation | ≥ 0.3 mm (Wire insulation power supply) |
| Wire colors | Red-black, blue-white |
| Twisted pairs | 2 cores to the pair |
| Type of pair shielding | Aluminum-lined polyester foil |
| Overall twist | 2 pairs with filler elements, around a drain wire in the center to the core |

Sensor/actuator cable - SAC-5P-M12MS/ 2,0-927 VA - 1402938

Technical data

Cable

| | |
|---|--|
| Shielding | Tinned copper braided shield |
| Optical shield covering | 85 % |
| External sheath, color | black |
| Outer sheath thickness | ≥ 1 mm |
| External cable diameter D | 8.3 mm ±0,3 mm |
| Minimum bending radius, fixed installation | 4 x D |
| Minimum bending radius, flexible installation | 8 x D |
| Cable weight | 83 kg/km |
| Outer sheath, material | PVC |
| Material conductor insulation | Foamed PP (Signal line) |
| | PVC (Power supply) |
| Conductor material | Tin-plated Cu litz wires |
| Insulation resistance | ≥ 20 MΩ*km |
| Conductor resistance | ≤ 56 Ω/km |
| Working capacitance | approx. 39.8 nF (Signal line, Core-Core) |
| | ≤ 4000 pF (Signal line, Core-Shield) |
| Wave impedance | 120 Ω ±12 Ω (f = 1 MHz) |
| Signal runtime | 4.46 ns/m |
| Nominal voltage, cable | ≤ 300 V |
| Test voltage, cable | 2000 V (50 Hz, 1 min.) |
| Flame resistance | in acc. with UL 1581, section 1061 |
| Ambient temperature (operation) | -30 °C ... 80 °C |

Approvals


Approvals

Approvals

EAC

Ex Approvals

Approval details

| | | |
|-----|---|---------------|
| EAC |  | EAC-Zulassung |
|-----|---|---------------|

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1402938](#)