




PUI audio



Data Sheet

AS02208MO

The **AS02208MO** is designed for applications such as hand-held devices, portable devices, and devices that value compact design.

Features:


- 76dB SPL: $P_{DRIVE} = 1W$, distance = 0.5m
- 1.0W continuous dissipation
- 1050Hz free-air resonance
- 22mm x 9mm x 3.5mm dimensions

Specifications


(Specifications measured with following conditions: ambient temperature; $15^{\circ}C \leq T_A \leq 35^{\circ}C$, relative humidity; $25\% \leq RH_A \leq 75\%$, according to standard GB/T9396-1996, unless otherwise stated. Judgement Condition: ambient temperature; $20 \pm 2^{\circ}C$; relative humidity; $63\% \leq RH_A \leq 67\%$. Product shelf life valid for 12 months.

Parameters	Values	Units
Rated Input Power	1.0	Watts
Maximum Input Power	1.2	Watts
Impedance	$8 \pm 15\%$	Ohms
Sensitivity (SPL) $P_{DRIVE} = 1.0W$, distance = 0.5m f = ave. 1.0kHz, 1.2kHz, 1.5kHz, 1.8kHz	81 ± 3	dB
Resonant Frequency (f_0)	$1050 \pm 20\%$	Hz
Frequency Range (-10 dB)	$f_0 \leq f \leq 20,000$	Hz
Total Harmonic Distortion (THD) f = 1 kHz, $P_{DRIVE} = 1.0W$	<5 %	-
Frame Material	ABS	-
Magnet Material	NdFeB	-
Diaphragm Material	PEN	-
Weight	1.15	gm
Buzz, Rattle, etc.	Not audible with $P_{DRIVE} = 1.0W$, sine wave	-
Polarity	Applying positive dc current to "+" terminal moves diaphragm forward	-
Operating Temperature Range	$-25 \leq T_o \leq 50$	$^{\circ}C$
Storage Temperature Range	$-25 \leq T_s \leq 60$	$^{\circ}C$
Environmental Compliance	RoHS/REACH	-


Measurement Method (measured with $P_{DRIVE} = 1.0W$, distance = 0.5m) Standard test condition of speaker




Typical Frequency Response ($P_{DRIVE} = 1.0W$, distance = 0.5m)



Typical THD vs. Frequency ($P_{DRIVE} = 1.0W$)




Impedance Response



Mounting Precautions

To ensure normal operation of the speaker, allow enough free space for diaphragm movement. The minimum distance required, "X," is the dimensioned drawing below is




1.15mm.



Reliability Testing

Type of Test	Test Specifications	Judgement
High Temperature Test GB2423.2-81	96 hours at +85°C ± 2°C followed by one hour in normal room temperature	SPL shall not deviate by ±3dB. Resonant frequency shall not deviate by ±50Hz. (compared with pre-test measurement)
Low Temperature Test GB2423.1-81	96 hours at -40°C ± 2°C followed by one hour in normal room temperature	
Humidity Test GB5170.18-87	96 hours at +40°C ± 2°C with relative humidity between 90% and 95% followed by 6 hours in normal room temperature	
Temperature Cycle Testing GB5170.18-87	<p>The graph shows a temperature cycle starting at Room Temperature +25°C. It ramps up in 10 seconds to +85°C, where it stays for 1 hour. It then ramps down in 10 seconds to -40°C, where it stays for 1 hour. The cycle then ramps back up to Room Temperature +25°C. This cycle is repeated 4 times.</p>	SPL shall not deviate by ±4dB. Resonant frequency shall not deviate by ±80Hz. (compared with pre-test measurement)
Vibration Test GB11606.8-89	Frequency 30±15 Hz, Amplitude 1.5 mm for 3 Hours	SPL shall not deviate by ±3dB. (compared with pre-test measurement)
Drop Test GB2423.8-81	75 cm free falling on concrete floor, 10 times.	
Load Test GB/T12060.5-2011	Speaker should not fail after applying 20Hz ~ 20kHz pink noise with HPF rated power input (RMS), 96 hours.	



Dimensions (Measured in mm. Tolerance = ±0.2mm.)



Packaging



NOTE
 120 PCS per Layer
 Total 14 Layer per box
 Total 1680 PCS per box
 41.5*38.5*38.5 cm
 HF+ROHS 2



Measurement & Standard Reference

Abstract from GB/T 9396-1996 and IEC 268-5:1989: methods of measurement for main characteristics of loudspeakers.

5.1 Rated sine voltage.

A sinusoidal signal voltage specified by the manufacturer which makes the speaker work continuously in the rated frequency range, without causing electrical or mechanical damage to the speaker. The continuous voltage time is 1 hour.

5.2 Rated sine power.

The rated sine power corresponding with the rated sine voltage defined by: U_s^2/R , where U_s indicates the rated sin voltage and R indicates the rated impedance of the speaker.

5.3 Rated noise power.

The rated sine power corresponding with the rated sine voltage defined by: U_n^2/R , where U_n indicates the rated sin voltage and R indicates the rated impedance of the speaker.

Specifications Revisions

Revision	Description	Date	Approved
A	Released by Engineering	03/24/2024	KH
B	Changes made to the front-page device picture and to the Dimensions drawing	09/10/2024	KH
C	Frame material under Specifications update to ABS	09/11/2024	KH
D	Updated Packaging information	12/23/2024	KH

Notes:

- Unless otherwise specified:
 - All dimensions are in millimeters.
 - Default tolerances are $\pm 0.2\text{mm}$ and angles are $\pm 3^\circ$.
- Specifications subject to change or withdrawal without notice.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PUI Audio:](#)

[AS02208MO](#)