



PUIaudio



Data Sheet

AS02308MR-T

The **AS02308MR-T** is designed for applications such as hand-held devices, portable devices, and devices that value compact design.


Features:

- 97dB SPL: $P_{DRIVE} = 1.0W$, distance = 0.1m
- 1.0W continuous dissipation
- 660Hz free-air resonance
- 22.5mm diameter x 7.0mm dimensions


Specifications (Specifications measured with following conditions: ambient temperature; $15^{\circ}C \leq T_A \leq 35^{\circ}C$, relative humidity; $25\% \leq RH_A \leq 75\%$, according to standard GB/T9396-1996, unless otherwise stated. Judgement Condition: ambient temperature; $20 \pm 2^{\circ}C$; relative humidity; $63\% \leq RH_A \leq 67\%$. Product shelf life valid for 12 months.

Parameters	Values	Units
Rated Input Power	1	Watts
Maximum Input Power	1.5	Watts
Impedance (f = 2.5 kHz)	$8 \pm 15\%$	Ohms
Sensitivity (SPL) $P_{DRIVE} = 1.0W$, distance = 0.1m f = ave. 0.8kHz, 1.0kHz, 1.2kHz, 1.5kHz	97 ± 3	dB
Resonant Frequency (f_0)	$660 \pm 20\%$	Hz
Frequency Range (-10 dB)	$f_0 \leq f \leq 20,000$	Hz
Total Harmonic Distortion (THD) $660Hz \leq f \leq 1kHz$, $P_{DRIVE} = 1.0W$ $1kHz \leq f \leq 6kHz$, $P_{DRIVE} = 1.0W$	≤ 15 ≤ 10	%
Frame Material	PBT + 15% GF	-
Magnet Material	NdFeB	-
Diaphragm Material	PEN	-
Weight	5.46	gm
Buzz, Rattle, etc.	Not audible with $P_{DRIVE} = 1.0W$, sine wave	-
Polarity	Applying positive dc current to "+" terminal moves diaphragm forward	-
Operating Temperature	$-25 \leq T_O \leq 50$	$^{\circ}C$
Storage Temperature	$-40 \leq T_S \leq 85$	$^{\circ}C$
Environmental Compliances	RoHS/REACH	


Measurement Method (1W input power with microphone spaced at 10cm)




Typical Frequency Response ($P_{DRIVE} = 1W$, distance = 0.1m)



Typical THD vs. Frequency ($P_{DRIVE} = 1W$)




Typical Impedance Response




Reliability Testing

Type of Test	Test Specifications	Judgement
High Temperature Test GB2423.2-81	96 hours at +85°C ± 2°C followed by one hour in normal room temperature	SPL shall not deviate by ±3dB. Resonant frequency shall not deviate by ±50Hz. (compared with pre-test measurement)
Low Temperature Test GB2423.1-81	96 hours at -40°C ± 2°C followed by one hour in normal room temperature	
Humidity Test GB5170.18-87	96 hours at +40°C ± 2°C with relative humidity between 90% and 95% followed by 6 hours in normal room temperature	
Temperature Cycle Testing GB5170.18-87		SPL shall not deviate by ±4dB. Resonant frequency shall not deviate by ±80Hz. (compared with pre-test measurement)
Vibration Test GB11606.8-89	Frequency 30±15 Hz, Amplitude 1.5 mm for 3 Hours	SPL shall not deviate by ±3dB. (compared with pre-test measurement)
Drop Test GB2423.8-81	75 cm free falling on concrete floor, 10 times.	
Load Test GB/T12060.5-2011	Speaker should not fail after applying 20Hz ~ 20kHz pink noise with HPF rated power input (RMS), 96 hours.	



Dimensions (All dimensions in mm; tolerance is +0.5mm, unless otherwise stated.)



Packaging



NOTE
50 PCS per Layer
Total 14 Layer per box
Total 900 PCS per box
38.5*32.5*36.5 cm
HF+ROHS 2



Notes

Measurement & Standard Reference

Abstract from GB/T 9396-1996 and IEC 268-5:1989: methods of measurement for main characteristics of loudspeakers.

Rated sine voltage.

A sinusoidal signal voltage specified by the manufacturer which makes the speaker work continuously in the rated frequency range, without causing electrical or mechanical damage to the speaker. The continuous voltage time is 1 hour.

Rated sine power.

The rated sine power corresponding with the rated sine voltage defined by: V_s^2/R , where V_s indicates the rated sin voltage and R indicates the rated impedance of the speaker.

Rated noise power.

The rated sine power corresponding with the rated sine voltage defined by: V_n^2/R , where V_n indicates the rated sin voltage and R indicates the rated impedance of the speaker.

Specifications Revisions

Revision	Description	Date	Approved
A	Datasheet released by Engineering	03-07-2024	KH

Note:

- Unless otherwise specified:
 - All dimensions are in millimeters.
 - Default tolerances are $\pm 0.5\text{mm}$ and angles are $\pm 3^\circ$.
- Specifications subject to change or withdrawal without notice.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PUI Audio:](#)

[AS02308MR-T](#)