



PUIaudio



Datasheet

AS02504AR

The **AS02504AR** is designed for applications that require robust low-frequency response in compact designs.

Features:


- 81dB SPL: 1 P_{DRIVE} = 1W, distance = 0.5m
- 3W continuous dissipation
- 320Hz free-air resonance
- 25mm diameter x 9.4mm dimensions

Specifications


(Specifications measured with following conditions: ambient temperature; 15°C ≤ T_A ≤ 35°C, relative humidity; 25% ≤ RH_A ≤ 75%, according to standard GB/T9396-1996, unless otherwise stated. Judgement Condition: ambient temperature; 20 ± 2°C; relative humidity; 63% ≤ RH_A ≤ 67%. Product shelf life valid for 12 months.

Parameters	Values	Units
Rated Input Power	3.0	Watts
Max Input Power	3.5	Watts
Impedance	4 ± 15%	Ohms
Sensitivity P _{DRIVE} = 1.0W, distance = 0.5m f = ave. 0.8kHz, 1.0kHz, 1.2kHz, 1.5kHz	81 ± 3	dB
Resonant Frequency (f ₀)	320 ± 20%	Hz
Frequency Range (-10dB SPL)	f ₀ ≤ f ≤ 20,000	Hz
Total Harmonic Distortion f = 1kHz, P _{DRIVE} = 1.0W	≤ 5	%
Frame Material	PBT + 15% GF	-
Magnet Material	NdFeB	-
Diaphragm Material	Aluminum	-
Weight	10.8	gm
Buzz, Rattle, etc.	Not audible with P _{DRIVE} = 2W sine wave	-
Polarity	Applying positive dc current to "+" terminal moves diaphragm forward	-
Storage Temperature	-25 ≤ T _S ≤ 60	°C
Operating Temperature	-25 ≤ T _O ≤ 50	°C
Environmental Compliances	ROHS/REACH	-


Measurement Method (Measured with $P_{DRIVE} = 1.0W$, distance = 0.5m, Temperature: 23 ~ 25°C, Relative Humidity: 55% (max).)




Typical Frequency Response (Measured with $P_{DRIVE} = 1.0W$, distance = 0.5m)




Typical THD vs. Frequency ($P_{DRIVE} = 1.0W$)



Impedance Curve




Reliability Testing


Type of Test	Test Specifications	Judgement
High Temperature Test GB2423.2-81	96 hours at +60°C ± 2°C followed by one hour in normal room temperature	SPL shall not deviate by ±3dB. Resonant frequency shall not deviate by ±50Hz. (compared with pre-test measurement)
Low Temperature Test GB2423.1-81	96 hours at -25°C ± 2°C followed by one hour in normal room temperature	
Humidity Test GB5170.18-87	96 hours at +40°C ± 2°C with relative humidity between 90% and 95% followed by 6 hours in normal room temperature	
Temperature Cycle Testing GB5170.18-87	 <p>The graph shows a temperature cycle starting at Room Temperature +25°C. It ramps up to +60°C in 10 seconds, holds at +60°C for 1 hour, ramps down to -25°C in 10 seconds, and holds at -25°C for 1 hour. This cycle repeats 4 times before returning to the start.</p>	SPL shall not deviate by ±4dB. Resonant frequency shall not deviate by ±80Hz. (compared with pre-test measurement)
Vibration Test GB11606.8-89	Frequency 30±15 Hz, Amplitude 1.5 mm for 3 Hours	SPL shall not deviate by ±3dB. (compared with pre-test measurement)
Drop Test GB2423.8-81	75 cm free falling on concrete floor, 10 times.	
Load Test GB/T12060.5-2011	Speaker should not fail after applying 20Hz ~ 20kHz pink noise with HPF rated power input (RMS), 96 hours.	

Dimensions (Tolerance: ±0.5mm, unless otherwise specified.)

MOUNTING NOTICE





Packaging



NOTE

45 PCS per Layer
Total 10 Layer per box
Total 450 PCS per box
38.5*32.5*27.5 cm
HF+ROHS 2



Measurement & Standard Reference

Abstract from GB/T 9396-1996 and IEC 268-5:1989: methods of measurement for main characteristics of loudspeakers.

5.1 Rated sine voltage.

A sinusoidal signal voltage specified by the manufacturer which makes the speaker work continuously in the rated frequency range, without causing electrical or mechanical damage to the speaker. The continuous voltage time is 1 hour.

5.2 Rated sine power.

The rated sine power corresponding with the rated sine voltage defined by: U_s^2/R , where U_s indicates the rated sin voltage and R indicates the rated impedance of the speaker.

5.3 Rated noise power.

The rated sine power corresponding with the rated sine voltage defined by: U_n^2/R , where U_n indicates the rated sin voltage and R indicates the rated impedance of the speaker.

Specifications Revisions

Revision	Description	Date	Approved
A	Released from Engineering	03/25/2024	KH

Notes:

- Unless otherwise specified:
 - All dimensions are in millimeters.
 - Default tolerances are $\pm 0.5\text{mm}$ and angles are $\pm 3^\circ$.
- Specifications subject to change or withdrawal without notice.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PUI Audio:](#)

[AS02504AR](#)