

Product data sheet

Characteristics

BR1500G

APC Power-Saving Back-UPS Pro 1500,
1500VA, 120V, LCD, 10 NEMA outlets (5
surge)



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Kw Rating	865 W
Rated power in VA	1500 VA
Nb of power socket outlets	5 NEMA 5-15R 5 NEMA 5-15R surge
Main Output Voltage	120 V
Main Input Voltage	120 V
Plug standard	NEMA 5-15P
Cable length	6 ft (1.83 m)

General

Provided equipment	User Manual USB cable
Number of power module free slots	0
Number of power module filled slots	0
Redundant	No

Physical

Depth	15.04 in (38.2 cm)
Height	11.85 in (30.1 cm)
Mounting preference	No preference
Net Weight	26.68 lb(US) (12.1 kg)
Mounting Mode	Not rack-mountable
Two post mountable	0
USB compatible	Yes
Width	4.41 in (11.2 cm)

Input

Input Frequency	50/60 Hz +/- 3 Hz auto-sensing
-----------------	--------------------------------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Output

Max Configurable Power (Watts)	865 W
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains
Topology	Line Interactive
Waveform Type	Stepped approximation to a sine wave
Maximum configurable power in VA	1500 VA
Transfer Time	8ms typical : 12ms maximum

Conformance

Product Certifications	NOM TÜV ENERGY STAR V2.0 (USA)
Standards	FCC Part 15 class B UL 1778
Equipment protection policy	Lifetime : \$150000

Environmental

Ambient air temperature for operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...30000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)
Acoustic level	45 dBA

Batteries & Runtime

Battery Type	Lead-Acid battery
Included Battery Modules	1
Battery Slots Empty	0
Typical recharge time	8 h
RBC Quantity	1
Battery Voltage	24 V
Battery Capacity	9.0 Ah
Battery Charge Power (Watts)	23 W rated
Battery power in VAh	187 VAh capacity 187 VAh runtime
Battery life	3...5 year(s)
Battery option	BR24BP 1 518 VAh BR24BPG 1 518 VAh
Battery graph comments	This graph is based on actual measured runtime data. All measurements were taken with new, fully charged batteries and a balanced resistive load (PF = 1.0). Actual runtimes may vary from the values of this graph. Actual runtimes are dependent on several variables including battery age, battery charge level, environmental conditions and characteristics of the connected load.
Extendable Run Time	0

Communications & Management

Control panel	Multi-function LCD status and control console
Audible Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm

Surge Protection and Filtering

Surge energy rating	354 J
Filtering	Full time multi-pole noise filtering :5% of IEEE surge let-through : zero clamping response time: in
Data line protection	Cable modem/video protection Network line - 10/100/1000 Base-T Ethernet (RJ45 connector)
Let Through Voltage Rating	300 V

Ordering and shipping details

Category	11309 - APC RESALE PRODUCTS
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	PH

Packing Units

Package 1 Height	15.24 in (38.7 cm)
Package 1 width	9.37 in (23.8 cm)
Package 1 Length	19.21 in (48.8 cm)
SCC14	10731304268779
Number of Units in Package 2	1
Number of Units in Package 3	20

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
Energy Star	ENERGY STAR UPS V2.0 (USA)
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	3 years repair or replace
----------	---------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[BR1500G](#)