



Main

Range of Product	Harmony Relay
Product or Component Type	Plug-in relay
Device short name	RHN
Contacts type and composition	4 C/O
Contact operation	Instantaneous Standard
[Uc] control circuit voltage	24 V AC 50 Hz
[Ithe] conventional enclosed thermal current	5 A 104 °F (40 °C)
Status LED	Without
Control Type	Manual control
Coil interference suppression	Without

Complementary

[Ui] rated insulation voltage	250 V
Test levels	Level A
Operating position	Any position
Minimum switching capacity	150 mVA 10 mA 150 mVA, 1 V
Contact bounce time	<= 10 ms
Maximum voltage drop	<100 V for 3 A at 24 V
Average resistance	30 mOhm 68 °F (20 °C)
Average coil consumption in VA	2.5 holding)68 °F (20 °C) 4.5 inrush)68 °F (20 °C)
Control circuit voltage limits	0.8...1.1 Uc IEC 60255
Drop-out voltage threshold	0.15...0.5 Uc
Cos phi	0.6 (inrush) 0.7 (holding)
Mechanical durability	20000000 cycles
Maximum operating rate	6 cyc/mn
Operating time	2...15 ms between energisation of coil and closing of NO contact 68 °F (20 °C) 1.2...12 ms between de-energisation of coil and closing of NC contact 68 °F (20 °C) 1...3 ms energisation/de-energisation 0.5...6 ms de-energisation/energisation
CAD overall width	1.30 in (33 mm)
CAD overall height	1.69 in (43 mm)
CAD overall depth	2.13 in (54 mm)
Terminals description ISO n°1	(11-12-14)OC (41-42-44)OC (21-22-24)OC (A1-A2)CO (31-32-34)OC
Net Weight	0.20 lb(US) (0.09 kg)
Compatibility code	RHN

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Standards	IEC 60255 VDE 0435 NF C 45-250 BS 4794
Product Certifications	CSA EDF USSR BV UR ASE
Protective treatment	TC
Dielectric strength	2500 V
Ambient air temperature for operation	23...104 °F (-5...40 °C) IEC 60255
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Vibration resistance	6 gn 10...55 Hz)IEC 60068-2-6 6 gn 10...55 Hz)NF C 20-616
Shock resistance	50 gn 11 ms NF C 20-608

Ordering and shipping details

Category	18073 - SPARE PARTS DISCOUNT I
Discount Schedule	CP2
GTIN	3389110162806
Nbr. of units in pkg.	1
Package weight(Lbs)	3.46 oz (98 g)
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.05 in (5.2 cm)
Package 1 width	2.13 in (5.4 cm)
Package 1 Length	3.03 in (7.7 cm)
Unit Type of Package 2	S02
Number of Units in Package 2	55
Package 2 Weight	12.49 lb(US) (5.665 kg)
Package 2 Height	5.91 in (15 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[RHN411B](#)