

SM657A66400

Hyde Park, Ultrasonic sensor, small target sensing, 18 mm barrel, 12 24 V DC



Main

| | |
|-------------------------------|--|
| Range of Product | Hyde Park |
| Sensor Type | Ultrasonic sensor |
| Series name | Superprox 600 |
| Device short name | SM657 |
| Sensor design | Cylindrical M18 |
| [Sn] nominal sensing distance | 6.00 in (152.4 mm) |
| Type of sensing window | Fixed |
| Material | Plastic |
| Enclosure Material | ULTEM |
| Front material | Silicone rubber |
| Type of output signal | Discrete |
| Discrete output function | 1 NO |
| ISO thread | M18 x 1 |
| Wiring Technique | 4-wire |
| [Us] rated supply voltage | 12...24 V DC overload and short-circuit protection |
| Supply voltage limits | 10...28 V DC |
| Discrete output type | PNP/NPN |
| Electrical connection | 1 male connector M12 4 pins |
| Product Specific Application | Small target sensing |

Complementary

| | |
|---------------------------------|--|
| [Sd] sensing range | 2.00...6.00 in (50.8...152.4 mm) |
| Blind zone | 1.50 in (38.1 mm) |
| Transmission frequency | 500 kHz |
| Repeat accuracy | 0.69 % |
| Beam angle | 7 ° |
| Minimum size of detected object | Width of 0.076 mm - up to 51 mm sensing distance |
| Current Consumption | 70 mA |
| Maximum switching current | 100 mA reverse polarity protection |
| Height | 0.71 in (18 mm) |
| Width | 0.71 in (18 mm) |
| Depth | 0.71 in (18 mm) |
| Length | 2.91 in (73.91 mm) |
| Net Weight | 0.07 lb(US) (0.033 kg) |

Environment

| | |
|---------------------------------------|--|
| Product Certifications | UL |
| Marking | CE |
| NEMA degree of protection | NEMA 4X indoor use only) |
| IP degree of protection | IP67 |
| Ambient air temperature for operation | 32...140 °F (0...60 °C) |
| Ambient Air Temperature for Storage | -40...212 °F (-40...100 °C) |
| Relative humidity | 100 % without condensation |
| Vibration resistance | +/-1 mm 10...55 Hz)IEC 60068-2-6 |
| Shock resistance | 30 gn in all 3 axes 11 ms IEC 60068-2-27 |

| | |
|--------------------------------------|---|
| Resistance to electromagnetic fields | 9.14 V/m (10 V/m) level 3 IEC 61000-4-3 |
| Resistance to fast transients | 1 kV level 3 IEC 61000-4-4 |

Ordering and shipping details

| | |
|-----------------------|------------------------------------|
| Category | 22490 - SENSORS-ULTRASONIC (XX5,6) |
| Discount Schedule | DS2 |
| GTIN | 03389119109871 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 0.13 lb(US) (0.06 kg) |
| Returnability | No |
| Country of origin | US |

Offer Sustainability

| | |
|---------------------------|---|
| California proposition 65 | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| EU RoHS Directive | Not applicable, out of EU RoHS legal scope |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SM657A66400](#)