



# PUI audio



Data Sheet

AS02204CR

The **AS02204CR** is designed for applications such as hand-held devices, portable devices, and devices that value compact design.

## Features:


- 83dB SPL:  $P_{DRIVE} = 1.0W$ , distance = 0.1m
- 3.0W continuous dissipation
- 850Hz free-air resonance
- 22.0mm diameter x 6.4mm dimensions

## Specifications


(Specifications measured with following conditions: ambient temperature;  $15^{\circ}C \leq T_A \leq 35^{\circ}C$ , relative humidity;  $25\% \leq RH_A \leq 75\%$ , according to standard GB/T9396-1996, unless otherwise stated. Judgement Condition: ambient temperature;  $20 \pm 2^{\circ}C$ ; relative humidity;  $63\% \leq RH_A \leq 67\%$ . Product shelf life valid for 12 months.

| Parameters   | Values   | Units       |
|--|--|-------------|
| Rated Input Power  | 3.0  | Watts       |
| Max Input Power  | 3.5  | Watts       |
| Impedance  | $4 \pm 15\%$   | Ohms        |
| Sensitivity (SPL)<br>$P_{DRIVE} = 1.0W$ , distance = 0.1m<br>f = ave. 0.8kHz, 1.0kHz, 1.2kHz, 1.5kHz | $83 \pm 3$   | dB          |
| Resonant Frequency ( $f_0$ )   | $850 \pm 20\%$   | Hz          |
| Frequency Range (-10 dB)   | $850 \leq f \leq 20,000$   | Hz          |
| Total Harmonic Distortion (THD)<br>f = 1kHz, $P_{DRIVE} = 1.0W$                                      | $\leq 10$  | %           |
| Frame Material   | PBT + 15% GF   | -           |
| Magnet Material  | NdFeB  | -           |
| Diaphragm Material   | Cloth + Aluminum   | -           |
| Weight   | 4.8  | gm          |
| Buzz, Rattle, etc.   | Not audible with $P_{DRIVE} = 3.0W$ , sine wave,<br>$680 \leq f \leq 20,000$ | -           |
| Polarity   | Applying positive dc current to "+" terminal<br>moves diaphragm forward      | -           |
| Operating Temperature  | $-25 \leq T_O \leq 50$   | $^{\circ}C$ |
| Storage Temperature  | $-25 \leq T_S \leq 60$   | $^{\circ}C$ |
| Environmental Compliances  | ROHS/REACH   | -           |


### Measurement Method (measured with $P_{DRIVE} = 1.0$ , distance = 0.5m)




### Typical Frequency Response ( $P_{DRIVE} = 1W$ , distance = 0.5m)




### Typical THD vs. Frequency ( $P_{DRIVE} = 1W$ )




### Typical Impedance Response



## Reliability Testing

| Type of Test                              | Test Specifications   | Judgement  |
|---|---|--|
| High Temperature Test<br>GB2423.2-81      | 96 hours at +85°C ± 2°C followed by one hour in normal room temperature   | SPL shall not deviate by ±3dB. Resonant frequency shall not deviate by ±50Hz. (compared with pre-test measurement) |
| Low Temperature Test<br>GB2423.1-81       | 96 hours at -40°C ± 2°C followed by one hour in normal room temperature   |  |
| Humidity Test<br>GB5170.18-87             | 96 hours at +40°C ± 2°C with relative humidity between 90% and 95% followed by 6 hours in normal room temperature |  |
| Temperature Cycle Testing<br>GB5170.18-87 |                                 |  |
| Vibration Test<br>GB11606.8-89            | Frequency 30±15 Hz, Amplitude 1.5 mm for 3 Hours  | SPL shall not deviate by ±3dB. (compared with pre-test measurement)  |
| Drop Test<br>GB2423.8-81                  | 75 cm free falling on concrete floor, 10 times.   |  |
| Load Test<br>GB/T12060.5-2011             | Speaker should not fail after applying 20Hz ~ 20kHz pink noise with HPF rated power input (RMS), 96 hours.        |  |



## Dimensions



## Packaging

42pcs per tray

15 trays/630pcs master carton



## Measurement & Standard Reference

Abstract from GB/T 9396-1996 and IEC 268-5:1989: methods of measurement for main characteristics of loudspeakers.

### 5.1 Rated sine voltage.

A sinusoidal signal voltage specified by the manufacturer which makes the speaker work continuously in the rated frequency range, without causing electrical or mechanical damage to the speaker. The continuous voltage time is 1 hour.

### 5.2 Rated sine power.

The rated sine power corresponding with the rated sine voltage defined by:  $U_s^2/R$ , where  $U_s$  indicates the rated sin voltage and  $R$  indicates the rated impedance of the speaker.

### 5.3 Rated noise power.

The rated sine power corresponding with the rated sine voltage defined by:  $U_n^2/R$ , where  $U_n$  indicates the rated sin voltage and  $R$  indicates the rated impedance of the speaker.

**Specifications Revisions**

| <b>Revision</b> | <b>Description</b>                  | <b>Date</b> | <b>Approved</b> |
|-----------------|-------------------------------------|-------------|-----------------|
| A               | Datasheet released from Engineering | 3/11/2024   | KH              |

Note:

- 1. Unless otherwise specified:
  - A. All dimensions are in millimeters.
  - B. Default tolerances are  $\pm 0.5\text{mm}$  and angles are  $\pm 3^\circ$ , unless otherwise specified.
- 2. Specifications subject to change or withdrawal without notice.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PUI Audio:](#)

[AS02204CR](#)