



NOTES:

1. Material: Corrosion resistant steel (CRES) per ASTM A582/A582M, type 303 (UN S30330) or 303SE (UNS S30323) or XM-1 (UMS S20300), condition A
2. Finish: Passivate per AMS2700, Method 1, Class 4
3. All Drawing Dimensions are in Inches [mm]
4. Unless otherwise specified, Edge Breaks, Radii or Countersinks 0.005-0.015
5. All features in accordance with NAS1831
6. Parts may be Drilled and/or Tapped thru



95 Silvermine Rd., Seymour CT 06483
Tel: 203-888-2133, Fax: 203-888-9860

This Drawing is the Property of RAF.
It contains confidential, proprietary information that is RAF property. Do not disclose to or duplicate for others except as authorized by RAF.

TOLERANCES
ALL DIMENSIONS ARE INCHES (UNLESS OTHERWISE SPECIFIED)
METALLIC
LENGTHS < 6 INCHES ± 0.005
LENGTH > 6 INCHES ± 0.010
DIAMETERS: ± 0.005
NON-METALLIC
LENGTH: ± 0.010 DIAMETERS: ± 0.010
INTERNAL THREADS:
MINIMUM THREAD DEPTH

COMPONENT	FEMALE FEMALE STANDOFF	
NAS1831C6D40	SCALE	REV
	2.81	04
3/8 Female Female Standoff	SHEET	
	1 of 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[RAF Electronic Hardware:](#)

[NAS1831C6D40](#)