Product data sheet Characteristics

RXM4AB2FD

Harmony, Miniature plug-in relay, 6 A, 4 CO, with LED, with lockable test button, 110 V DC





Main

Range of Product	Harmony Electromechanical Relays
Series name	Miniature
Product or Component Type	Plug-in relay
Device short name	RXM
Contacts type and composition	4 C/O
[Uc] control circuit voltage	110 V DC
Status LED	With
Control Type	Lockable test button
Utilisation coefficient	20 %

Complementary

Flat
250 V IEC
300 V CSA 300 V UL
2.5 kV 1.2/50 μs
AgNi
3 A 28 V DC) NC IEC
3 A 250 V AC) NC IEC 6 A 28 V DC) NO IEC
6 A 250 V AC) NO IEC
6 A 277 V AC) UL
8 A 30 V DC) UL
5 A
250 V IEC
6 A 250 V AC
6 A 28 V DC
1500 VA/168 W
170 mW 10 mA, 17 V
<= 1200 cycles/hour under load
<= 18000 cycles/hour no-load
10000000 cycles
100000 cycles resistive
0.9 W
>= 0.1 Uc
20 ms
20 ms
13440 Ohm 20 °C +/- 10 %
88121 V DC
B10d = 100000
RTI
Level A
Any position
3.11 in (79 mm)
3.09 in (78.45 mm)
0.08 lb(US) (0.037 kg)
Complete product

Environment

Dielectric strength	1300 V AC between contacts with micro disconnection 2000 V AC between coil and contact with basic insulation	
	2000 V AC between coll and contact with basic insulation	
	·	
Product Certifications	GOST	
	CE	
	UL	
	Lloyd's	
	CSA	
Standards	CSA C22.2 No 14	
	UL 508	
	EN/IEC 61810-1	
Ambient Air Temperature for Storage	-40185 °F (-4085 °C)	
Ambient air temperature for operation	-40131 °F (-4055 °C)	
Vibration resistance	3 gn +/- 1 mm 10150 Hz)5 cycles in operation	
	5 gn +/- 1 mm 10150 Hz)5 cycles not operating	
IP degree of protection	IP40 conforming to EN/IEC 60529	
Shock resistance	10 gnin operation	
	30 gnnot operating	
Pollution degree	2	
<u> </u>		

Ordering and shipping details

Category	21127-ZELIO ICE CUBE RELAYS
Discount Schedule	CP2
GTIN	3389119403856
Nbr. of units in pkg.	1
Package weight(Lbs)	1.31 oz (37.0 g)
Returnability	No
Country of origin	ID

Packing Units

Packing Units	
Unit Type of Package 1	PCE
Package 1 Height	4.29 in (10.9 cm)
Package 1 width	0.83 in (2.1 cm)
Package 1 Length	1.07 in (2.72 cm)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	14.11 oz (400.0 g)
Package 2 Height	1.18 in (3 cm)
Package 2 width	4.02 in (10.2 cm)
Package 2 Length	4.92 in (12.5 cm)
Unit Type of Package 3	S02
Number of Units in Package 3	240
Package 3 Weight	22.28 lb(US) (10.108 kg)
Package 3 Height	5.91 in (15 cm)
Package 3 width	11.81 in (30 cm)
Package 3 Length	15.75 in (40 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACh Regulation	☑ REACh Declaration
REACh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EV RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	₫Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.


Contractual warranty

Warranty	18 months	


Product data sheet Dimensions Drawings

RXM4AB2FD


Dimensions




Pin Side View



Wiring Diagram





Symbols shown in blue correspond to Nema marking.


Product data sheet Performance Curves

RXM4AB2FD

Electrical Durability of Contacts

Durability (inductive load) = durability (resistive load) x reduction coefficient.

Resistive AC load



X Switching capacity (kVA)

Y Durability (Number of operating cycles)


A RXM2AB•••

B RXM3AB•••

C RXM4AB•••


D RXM4GB•••

Reduction coefficient for inductive AC load (depending on power factor $\cos \phi$)



Y Reduction coefficient (A)

Maximum switching capacity on resistive DC load



X Voltage DC

Y Current DC

A RXM2AB•••

B RXM3AB•••

C RXM4AB•••

D RXM4GB•••

Note: These are typical curves, actual durability depends on load, environment, duty cycle, etc.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Schneider Electric: RXM4AB2FD