



## Overview

|           |                              |
|-----------|------------------------------|
| Lead time | Usually Ships within 2 Weeks |
|-----------|------------------------------|

## General

|                                     |  |
|-------------------------------------|--|
| Provided equipment                  | CD with software<br>Documentation CD<br>Smart UPS signalling RS-232 cable<br>USB cable<br>Web/SNMP management card |
| Number of tare power                | 30 W   |
| Number of power module free slots   | 0  |
| Number of power module filled slots | 0  |
| Redundant                           | No   |
| Variant option                      | Web/SNMP card AP9631 preinstalled  |

## Physical

|                     |                         |
|---------------------|-------------------------|
| Cable length        | 6 Ft (1.83 m)           |
| Color               | Black                   |
| Depth               | 17.28 In (43.9 cm)      |
| Height              | 8.62 In (21.9 cm)       |
| Mounting Location   | Front                   |
| Mounting preference | No preference           |
| Product Weight      | 53.11 Lb(US) (24.09 kg) |
| Mounting Mode       | Not rack-mountable      |
| Two post mountable  | 0                       |
| USB compatible      | Yes                     |
| Width               | 6.73 In (17.1 cm)       |

## Input

|                         |                                     |
|-------------------------|-------------------------------------|
| Input Frequency         | 50/60 Hz +/- 3 Hz auto-sensing      |
| Plug standard           | NEMA 5-15P                          |
| Efficiency at full load | 75...154 V adjustable<br>82...144 V |
| Number of cables        | 1                                   |
| Nominal Input Voltage   | 120 V                               |

## Output

|                                  |                                 |
|----------------------------------|---------------------------------|
| Kw Rating                        | 1000 W                          |
| Max Configurable Power (Watts)   | 1000 W                          |
| Harmonic distortion              | Less than 5%                    |
| Output frequency                 | 50/60 Hz +/- 3 Hz sync to mains |
| Topology                         | Line Interactive                |
| Waveform Type                    | Sine wave                       |
| Nb of power socket outlets       | 8 NEMA 5-15R                    |
| Output voltage                   | 120 V                           |
| Maximum configurable power in VA | 1440 VA                         |
| Rated power in VA                | 1440 VA                         |
| Transfer Time                    | 4ms typical : 8ms maximum       |

## Conformance

|                             |                     |
|-----------------------------|---------------------|
| Product Certifications      | CUL Listed          |
| Standards                   | UL 1778             |
| Equipment protection policy | Lifetime : \$150000 |

## Environmental

|                                       |                                  |
|---------------------------------------|----------------------------------|
| Ambient Air Temperature for Operation | 32...104 °F (0...40 °C)          |
| Relative Humidity                     | 0...95 %                         |
| Operating altitude                    | 0...10000 ft                     |
| Ambient Air Temperature for Storage   | 5...113 °F (-15...45 °C)         |
| Storage Relative Humidity             | 0...95 %                         |
| Storage altitude                      | 0...50000 Ft (0.00...15240.00 m) |
| Acoustic level                        | 45 dBA                           |
| Heat dissipation                      | 135 Btu/H                        |

## Batteries & Runtime

|                              |                   |
|------------------------------|-------------------|
| Battery Type                 | Lead-Acid battery |
| Included Battery Modules     | 0                 |
| Battery Slots Empty          | 0                 |
| Typical recharge time        | 3 H               |
| RBC Quantity                 | 1                 |
| Liquid Electrolyte Value     | 0                 |
| Battery Charge Power (Watts) | 136 W rated       |
| Battery power in VAH         | 408 VAh runtime   |
| Battery life                 | 3...5 Year(S)     |
| Extendable Run Time          | 0                 |

## Communications & Management

|                                      |   |
|--------------------------------------|---|
| Free slots                           | 0   |
| Pre-Installed SmartSlot&trade; Cards | Network management card 2 with environmental monitoring                     |
| Control panel                        | Multi-function LCD status and control console                               |
| Audible Alarm                        | Alarm when on battery : distinctive low battery alarm : configurable delays |
| Emergency Power Off (EPO)            | Optional  |

## Surge Protection and Filtering

|                     |  |
|---------------------|--|
| Surge energy rating | 459 J  |
| Filtering           | Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : m |

## Ordering and shipping details

|                     |                         |
|---------------------|-------------------------|
| GTIN                | 00731304284314          |
| Package weight(Lbs) | 60.03 Lb(US) (27.23 kg) |

## Packing Units

|                              |                    |
|------------------------------|--------------------|
| Package 1 Height             | 14.80 In (37.6 cm) |
| Package 1 width              | 12.91 In (32.8 cm) |
| Package 1 Length             | 23.43 In (59.5 cm) |
| Number of Units in Package 3 | 24                 |

## Offer Sustainability

|                             |   |
|-----------------------------|---|
| Sustainable offer status    | Green Premium product                         |
| REACH Regulation            | <a href="#">REACH Declaration</a>             |
| EU RoHS Directive           | Compliant <a href="#">EU RoHS Declaration</a> |
| Mercury free                | Yes   |
| RoHS exemption information  | <a href="#">Yes</a>                           |
| Environmental Disclosure    | <a href="#">Product Environmental Profile</a> |
| Circularity Profile         | <a href="#">End Of Life Information</a>       |
| Optimized Energy Efficiency | Energy efficient product                      |
| Take-back                   | Take-back program available                   |

## Contractual warranty

|          |   |
|----------|---|
| Warranty | 3 years repair or replace (excluding battery) and 2 years for battery |
|----------|---|

Product Life Status : **Commercialised**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SMT1500X448](#)