



### Overview

|              |   |
|--------------|---|
| Presentation | High density, double-conversion on-line power protection with scalable runtime. |
| Lead time    | Usually in Stock  |

### General

|                                     |   |
|-------------------------------------|---|
| Provided equipment                  | CD with software<br>Documentation CD<br>Installation guide<br>Rack Mounting brackets<br>Rack Mounting support rails<br>USB cable<br>Warranty card |
| Product web sub-family              | High density  |
| Performance multiplier              | 1   |
| Number of tare power                | 25 W  |
| Number of power module free slots   | 0   |
| Number of power module filled slots | 0   |
| Redundant                           | No  |
| Size UPS version                    | Internetworking<br>Server<br>Telecom  |
| UPS size                            | S   |
| Value multiplier                    | 1   |

### Physical

|                     |                        |
|---------------------|------------------------|
| Cable length        | 8 ft (2.44 m)          |
| Number of rack unit | 2U                     |
| Color               | Black                  |
| Depth               | 25.00 in (63.5 cm)     |
| Height              | 3.35 in (8.5 cm)       |
| Mounting Location   | Front                  |
| Mounting position   | Horizontal             |
| Mounting preference | Lower                  |
| Product Weight      | 69.00 lb(US) (31.3 kg) |
| Mounting Mode       | Rack-mounted           |
| Two post mountable  | 0                      |
| USB compatible      | Yes                    |
| Width               | 17.01 in (43.2 cm)     |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Input

|                       |                         |
|-----------------------|-------------------------|
| Input Frequency       | 40 - 70 Hz auto-sensing |
| Plug standard         | NEMA L5-30P             |
| Number of cables      | 1                       |
| Nominal Input Voltage | 120 V                   |

## Output

|                                  |   |
|----------------------------------|---|
| Kw Rating                        | 2700 W  |
| Max Configurable Power (Watts)   | 2700 W  |
| Harmonic distortion              | Less than 2%  |
| Output Frequency (sync to mains) | 50/60 Hz +/- 3 Hz sync to mains   |
| Crest factor                     | 3 : 1   |
| Topology                         | Double Conversion Online  |
| Waveform Type                    | Sine wave   |
| Nb of power socket outlets       | 8 NEMA 5-20R<br>1 NEMA L5-30R   |
| Bypass type                      | Internal Bypass (Automatic and Manual)  |
| Curve equation                   | Efficiency  |
| Curve fixed loss                 | 0.0174  |
| Curve load maximum               | 100 %   |
| Curve load minimum               | 2 %   |
| Curve proportional loss          | 0.0134  |
| Curve square loss                | 0.0509  |
| Curve X-axis maximum             | 100 %   |
| Curve test cond ID               | Curve fit of data measured in accordance with the ENERGY STAR Test Method for Uninterruptible Power Supplies. All measurements taken in normal mode(s), at typical environmental conditions, with 120V/60Hz electrical input and balanced resistive load (PF = 1.0) output. |
| Curve X-axis minimum             | 0 %   |
| Curve X-axis title               | Load  |
| Curve X-axis units               | Percentage  |
| Curve Y-axis maximum             | 100 %   |
| Curve Y-axis minimum             | 50 %  |
| Curve Y-axis title               | Efficiency  |
| Curve Y-axis units               | Percentage  |
| Graph display                    | 1   |
| Output voltage                   | 120 V   |
| Maximum configurable power in VA | 3000 VA   |
| Rated power in VA                | 3000 VA   |

## Conformance

|                        |  |
|------------------------|--|
| Product Certifications | ENERGY STAR V2.0 (USA)   |
| Standards              | CSA C22.2 No.107.3-05<br>FCC Part 15 class A<br>OSHDP<br>UL 1778 |

## Environmental

|                                       |                                  |
|---------------------------------------|----------------------------------|
| Ambient Air Temperature for Operation | 32...104 °F (0...40 °C)          |
| Relative Humidity                     | 0...95 % non-condensing          |
| Operating altitude                    | 0...10000 ft                     |
| Ambient Air Temperature for Storage   | 5...113 °F (-15...45 °C)         |
| Storage Relative Humidity             | Non-condensing 0...95 %          |
| Storage altitude                      | 0...50000 ft (0.00...15240.00 m) |
| Acoustic level                        | 55 dBA                           |
| Heat dissipation                      | 805 Btu/h                        |

|                          |      |
|--------------------------|------|
| Show note OP temperature | No   |
| IP degree of protection  | IP20 |

### Batteries & Runtime

|                              |   |
|------------------------------|---|
| Battery Type                 | Lead-Acid battery   |
| Included Battery Modules     | 1   |
| Typical recharge time        | 3 h   |
| RBC Quantity                 | 1   |
| Liquid Electrolyte Value     | 0   |
| Battery Voltage              | 96V   |
| Battery curve                | D   |
| Battery Charge Power (Watts) | 151 W rated   |
| Battery power in VAh         | 454 VAh runtime   |
| Battery life                 | 3...5 year(s)   |
| Battery option               | SRT96RMBP 1 1362 VAh<br>SRT96RMBP 2 2270 VAh<br>SRT96RMBP 3 3178 VAh<br>SRT96RMBP 4 4086 VAh<br>SRT96RMBP 5 4994 VAh<br>SRT96RMBP 6 5902 VAh<br>SRT96RMBP 8 7718 VAh<br>SRT96RMBP 10 9534 VAh |
| Extendable Run Time          | 1   |

### Communications & Management

|                           |  |
|---------------------------|--|
| Free slots                | 1  |
| Control panel             | Multi-function LCD status and control console      |
| Audible Alarm             | Audible and visible alarms prioritized by severity |
| Emergency Power Off (EPO) | Yes  |

### Surge Protection and Filtering

|                     |       |
|---------------------|-------|
| Surge energy rating | 340 J |
|---------------------|-------|







### Ordering and shipping details

|                     |                         |
|---------------------|-------------------------|
| Package weight(Lbs) | 88.01 lb(US) (39.92 kg) |
|---------------------|-------------------------|

### Packing Units

|                              |                    |
|------------------------------|--------------------|
| Package 1 Height             | 9.69 in (24.6 cm)  |
| Package 1 width              | 23.58 in (59.9 cm) |
| Package 1 Length             | 34.29 in (87.1 cm) |
| Number of Units in Package 3 | 6                  |

### Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product   |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| Energy Star                |  <a href="#">ENERGY STAR UPS V2.0 (USA)</a>  |
| REACH Regulation           |  <a href="#">REACH Declaration</a>   |
| EU RoHS Directive          | Compliant  <a href="#">EU RoHS Declaration</a>   |
| Mercury free               | Yes   |
| RoHS exemption information |  <a href="#">Yes</a>   |
| Environmental Disclosure   |  <a href="#">Product Environmental Profile</a>   |
| Circularity Profile        |  <a href="#">End Of Life Information</a>   |

---

|                             |                             |
|-----------------------------|-----------------------------|
| Optimized Energy Efficiency | Energy efficient product    |
| Take-back                   | Take-back program available |

---

### Contractual warranty

---

|          |   |
|----------|---|
| Warranty | 3 years repair or replace (excluding battery) and 2 years for battery |
|----------|---|

---

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SRT3000RMXLA](#)