

# SRT3000RMXLT

APC Smart-UPS On-Line, 3kVA, Rackmount  
2U, 208V, 2x L6-20R+1x L6-30R NEMA  
outlets, SmartSlot, Extended runtime, W/ rail kit



## Overview

Lead time	Usually in Stock
-----------	------------------



## Main

Main Input Voltage	208 V
Other Input Voltage	240 V
Main Output Voltage	208 V
Other Output Voltage	240 V
Kw Rating	2700 W
Rated power in VA	3000 VA
Plug standard	NEMA L6-20P
Nb of power socket outlets	2 NEMA L6-20R 1 NEMA L6-30R
Number of rack unit	2U
Cable length	10 ft (3.05 m)
Number of cables	1
Battery Type	Lead-Acid battery
Provided equipment	CD with software Documentation CD Installation guide Rack mounting hardware Rack Mounting brackets Rack Mounting support rails USB cable Warranty card

## General

Product web sub-family	High density
Number of power module free slots	0
Number of power module filled slots	0
Redundant	No

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Physical

Color	Black
Height	3.35 in (8.5 cm)
Width	17.01 in (43.2 cm)
Depth	25.00 in (63.5 cm)
Net Weight	69.00 lb(US) (31.3 kg)
Mounting Location	Front
Mounting preference	Lower
Mounting Mode	Rack-mounted
Two post mountable	0
USB compatible	Yes
Mounting position	Horizontal

## Input

Input Frequency	40 - 70 Hz auto-sensing
Efficiency at full load	100...275 V adjustable (half load)

## Output

Max Configurable Power (Watts)	2700 W
Harmonic distortion	Less than 2%
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains
Crest factor	3 : 1
Topology	Double Conversion Online
Waveform Type	Sine wave
Bypass type	Internal Bypass (Automatic and Manual)
Maximum configurable power in VA	3000 VA

## Conformance

Product Certifications	ENERGY STAR V2.0 (USA)
Standards	CSA C22.2 No.107.3-05 FCC Part 15 class A OSH PD UL 1778

## Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 % non-condensing
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 % Non-condensing
Storage altitude	0...50000 ft (0.00...15240.00 m)
Acoustic level	55 dBA
Heat dissipation	773 Btu/h
IP degree of protection	IP20

## Batteries & Runtime

Included Battery Modules	2
Typical recharge time	3 h
RBC Quantity	1
Additional information	Configurable for 208 or 240 nominal output voltage
Battery Voltage	96V
Battery Charge Power (Watts)	165 W rated
Battery power in VAH	497 VAh runtime
Battery Life	3...5 year(s)

Battery option	SRT96RMBP 1 1491 VAh SRT96RMBP 2 2485 VAh SRT96RMBP 3 3479 VAh SRT96RMBP 4 4473 VAh SRT96RMBP 5 5467 VAh SRT96RMBP 6 6461 VAh SRT96RMBP 8 8449 VAh SRT96RMBP 10 10437 VAh
Extendable Run Time	1

### Communications & Management

Free slots	1
Control panel	Multi-function LCD status and control console
Audible Alarm	Audible and visible alarms prioritized by severity
Emergency Power Off (EPO)	Yes

### Surge Protection and Filtering

Surge energy rating	340 J
---------------------	-------







### Ordering and shipping details

GTIN	731304317654
Package weight(Lbs)	88.01 lb(US) (39.92 kg)

### Packing Units

Package 1 Height	9.69 in (24.6 cm)
Package 1 width	23.58 in (59.9 cm)
Package 1 Length	34.29 in (87.1 cm)
Number of Units in Package 3	6

### Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
ENERGY STAR®	 <a href="#">ENERGY STAR UPS V2.0 (USA)</a>
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	 <a href="#">End Of Life Information</a>
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

### Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery
----------	---

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SRT3000RMXLT](#)