



## Overview

Lead time	Usually Ships within 2 Weeks
-----------	------------------------------

## General

Provided equipment	User manual
--------------------	-------------

## Physical

Number of rack unit	5U
Color	Black
Depth	19.49 In (49.5 cm)
Height	17.48 In (44.4 cm)
Product Weight	146.30 Lb(US) (66.36 kg)
Width	8.70 In (22.1 cm)

## Input

Nominal Input Voltage	DC
-----------------------	----

## Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 Ft (0.00...15240.00 m)

## Batteries & Runtime

Battery Type	Lead-Acid battery
Included Battery Modules	0
Battery Slots Empty	0
RBC Quantity	2
Additional information	For use with "SUA" 2200/3000VA 5U rack/tower models. Can be used with 3U models with SUA039 extension cable.
Liquid Electrolyte Value	0

## Ordering and shipping details

GTIN	00731304244301
Package weight(Lbs)	167.33 Lb(US) (75.9 kg)

## Packing Units

Package 1 Height	22.01 In (55.9 cm)
Package 1 width	15.00 In (38.1 cm)
Package 1 Length	30.00 In (76.2 cm)
Number of Units in Package 3	2

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
Take-back	Take-back program available

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Product Life Status : **Commercialised**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SUA48XLBP](#)