

Power Cord with Locking System for Inlet Filters IL 13, IL 13 P, IL 19



- Locking system for standardized IEC C14/C20 inlet filter
- No accidental disconnection
- Rated current up to 10 A (C13 plug), up to 15 A (C13P plug), and up to 20 A (C19 plug)
- Fits any Schaffner IEC C14/C20 inlet filter
- Retrofit for any IEC C14/C20 inlet
- Various power line plugs for international usage



Approvals



The locking system has a tensile force of typical 200N. It is recommended to use it with flange mount filters. For details refer to our Application Note "Using IEC Lock Power Cords with IEC Inlets and Filters"

Schaffner power cords with IEC lock guard against accidental disconnection of all electrical appliances with an IEC inlet. No exchange or modification of the IEC inlet or IEC inlet filter system is needed. Easy retrofit for all electronic equipments and devices.

Technical specifications IL 13/IL 13 P

Maximum continuous operating voltage	250 VAC, 50/60 Hz
Rated currents	10 A for C13 plug, 15 A for C13P plug
High potential test voltage	P→ PE 2000 VAC (1 min 50 Hz) P → N 2000 VAC (1 min 50 Hz)
Protection category	IP 20 according IEC 60529
Temperature range (operation and storage)	-25°C to +70°C
Connector (load side)	IEC C13 according to IEC/EN 60320-2-2 with IEC Lock UL 498, CSA C22.2 no. 42 (for cold conditions) pin temp. 70°C, up to 15 A, Protection Class I
Connector (line side) and cables	Please refer to table on page 2 and 3
Flammability corresponding to	Plugs: UL 94 V-2 or better; Cable: IEC 60332-1 Cat. F2

Features and benefits

- Power cord with locking system for IEC inlets
- Protection class I (IL 13, IL 13 P)
- Suitable for use with any C14 IEC inlet (IL 13, IL 13 P) and C20 IEC inlet (IL 19)
- Fits the complete Schaffner IEC inlet filter program with C14 IEC inlet and C20 IEC inlet (IL 19)
- Max. pin temperature 70°C

Typical applications

- Data centers
- Industrial equipment
- Medical devices
- In-vitro diagnostic devices
- Broadcasting stations
- Mobile applications

Technical specifications IL 19

Maximum continuous operating voltage	250 VAC, 50/60 Hz
Rated currents	16 A (IEC), 20 A (UL)
Operating frequency	50 to 400 Hz
High potential test voltage	P→ PE 2000 VAC (1 min 50 Hz) P → N 2000 VAC (1 min 50 Hz)
Protection category	IP 20 according IEC 60529
Temperature range (operation and storage)	-25°C to +70°C
Connector (load side)	IEC C19 according to IEC/EN 60320-2-2 with IEC lock, UL 498, CSA C22.2 no. 42 (for cold conditions) pin temp. 70°C, up to 20 A, Protection Class I
Connector (line side) and cables	please refer to table on page 4
Flammability corresponding to	Plugs: UL 94 V-2 or better; Cable: IEC 60332-1 Cat. F2

Cable selection table IL 13

IL 13-C14-H05-3100-X*	IEC cable assembly with locking system for IEC C14 inlet, EU version
IL 13-C14-SVT-3100-X*	IEC cable assembly with locking system for IEC C14 inlet, US version
IL 13-CH1-H05-3100-X*	IEC cable assembly with locking system for IEC C14 inlet, CH version
IL 13-EU1-H05-3100-X*	IEC cable assembly with locking system for IEC C14 inlet, EU version
IL 13-JP1-HVCTF-3125-X*	IEC cable assembly with locking system for IEC C14 inlet, JP version
IL 13-SE-H05-3100-X*	IEC cable assembly with locking system for IEC C14 inlet, stripped ends
IL 13-UK1-H05-3100-X*	IEC cable assembly with locking system for IEC C14 inlet, UK version
IL 13-US1-SVT-3100-X*	IEC cable assembly with locking system for IEC C14 inlet, US version
IL 13-US2-SJT-3100-X*	IEC cable assembly with locking system for IEC C14 inlet, US version, hospital grade

To compile a complete part number, please replace the X* with the required length (please refer to table below for available length per cable type):

- X* options = 200, 300, 400, 500 or 1000 cm; 183, 275 or 366 cm (6, 9 or 12 feet)

Available combinations IL 13

To compile a complete part number exchange the letters (IL13-yyy-zzz-aaaa-bbb-c) with the data from the table below.

Load side IL13		Line side plug	Cable type	Cable core	Rating	Cable length*		Cable color		Cert.			
IL13		yyy	zzz	aaaa		bbb		c					
IL13	IEC C13 Female plug, straight, lock	IEC C14, male, straight	C14	H05VV-F	H05	3x1.00mm²	3100	250VAC 10A	6 feet 200 cm 9 feet 300 cm 12 feet 366 400 cm 500 cm 1000 cm	183 200 275 300 366 400 500 1000	Black Blue Orange Red White	- B O R W	CB KC KEMA SAA
		Australian plug 3 pins	AU1										
		SEV1011, straight	CH1										
		CEE 7/VII, right angled	EU1										
		CEE 7/VII, straight	EU2										
		Italian Plug	IT1										
		Israel Plug	IL1										
		Korean Plug	KC1										
		South African Plug	SA1										
		Stripped Ends	SE										
BS1363, right angled fused 5A	UK1												
	BS1363, right angled fused 10A	UK2											
IL13	IEC C13 Female plug, straight, lock	IEC C14, male, straight	C14	HVCTF	HVCTF	3x1.25mm² 3x2.00mm²	3125 3200	125VAC 12A 15A	100 cm 200 cm 300 cm 400 cm 500 cm	100 200 300 400 500	Black Blue Orange Red White	- B O R W	PSE
		Japanese Plug JIS C8303 insulated sleeves	JP1										
		Stripped Ends	SE										
IL13	IEC C13 Female plug, straight, lock	IEC C14, male, straight	C14	SJT SVT	SJT SVT	AWG 18 AWG 16 AWG 14	3100 3130 3160	125VAC 10A 13A 15A	6 feet 200 cm 9 feet 300 cm 12 feet 366 400 cm 500 cm 1000 cm	183 200 275 300 366 400 500 1000	Black Blue Orange Red White	- B O R W	UL cUL
		Stripped Ends	SE										
		NEMA5-15, straight	US1										
		NEMA5-15, straight, hospital grade	US2										
IL13	IEC C13 Female plug, straight, lock	IEC C14, male, straight	C14	RVV	RVV	3x1.00mm²	3100	250VAC 10A	200 cm	200	Black Blue Orange Red White	- B O R W	CCC
		Chinese plug	CN1										
		Stripped Ends	SE										
IL13	IEC C13 Female plug, straight, lock	IEC C14, male, straight	C14	BIS 694 1000V	BIS694	3x1.00mm²	3100	250VAC 10A	200 cm	200	Black Blue Orange Red White	- B O R W	CB
		Indian plug 3 Pin	IN1										
		Stripped Ends	SE										

*feet values are calculated to the matching length in cm

Cable selection table IL 13 P

IL 13 P-C14-H05-3100-X*	IEC cable assembly with locking system + for IEC C14 inlet, EU version
IL 13 P-CH1-H05-3100-X*	IEC cable assembly with locking system + for IEC C14 inlet, CH version
IL 13 P-EU1-H05-3100-X*	IEC cable assembly with locking system + for IEC C14 inlet, EU version
IL 13 P-JP1-HVCTF-3125-X*	IEC cable assembly with locking system + for IEC C14 inlet, JP version
IL 13 P-SE-H05-3100-X*	IEC cable assembly with locking system + for IEC C14 inlet, stripped ends
IL 13 P-UK1-H05-3100-X*	IEC cable assembly with locking system + for IEC C14 inlet, UK version
IL 13 P-US1-SJT-3160-X*	IEC cable assembly with locking system + for IEC C14 inlet, US version

To compile a complete part number, please replace the X* with the required length (please refer to table below for available length per cable type):

- X* options = 200, 300, 400, 500 or 1000 cm; 183, 275 or 366 cm (6, 9 or 12 feet)

Available combinations IL 13 P

To compile a complete part number exchange the letters (IL13P-yyy-zzz-aaaa-bbb-c) with the data from the table below.

Load side IL13P		Line side plug		Cable type		Cable core		Rating	Cable length*		Cable color		Cert.
IL13P		yyy		zzz		aaaa			bbb		c		
IL13P	IEC C13 + Female plug, straight, lock	IEC C14, male, straight Australian plug 3 pins SEV1011, straight CEE 7/VII, right angled CEE 7/VII, straight Italian Plug Israel Plug Korean Plug South African Plug Stripped Ends BS1363, right angled fused 5A BS1363, right angled fused 10A	C14 AU1 CH1 EU1 EU2 IT1 IL1 KC1 SA1 SE UK1 UK2	H05VV-F	H05	3x1.00mm ²	3100	250VAC 10A	6 feet 200 cm 9 feet 300 cm 12 feet 400 cm 500 cm 1000 cm	183 200 275 300 366 400 500 1000	Black Blue Orange Red White	- B O R W	CB KC KEMA SAA
IL13P	IEC C13 + Female plug, straight, lock	IEC C14, male, straight Japanese Plug JIS C8303 insulated sleeves Stripped Ends	C14 JP1 SE	HVCTF	HVCTF	3x1.25mm ² 3x2.00mm ²	3125 3200	125VAC 12A 15A	100 cm 200 cm 300 cm 400 cm 500 cm	100 200 300 400 500	Black Blue Orange Red White	- B O R W	PSE
IL13P	IEC C13 + Female plug, straight, lock	IEC C14, male, straight Stripped Ends NEMAS-15, straight NEMAS-15, straight, hospital grade	C14 SE US1 US2	SJT SVT	SJT SVT	AWG 18 AWG 16 AWG 14	3100 3130 3160	125VAC 10A 13A 15A	6 feet 200 cm 9 feet 300 cm 12 feet 400 cm 500 cm 1000 cm	183 200 275 300 366 400 500 1000	Black Blue Orange Red White	- B O R W	UL cUL
IL13P	IEC C13 + Female plug, straight, lock	IEC C14, male, straight Chinese plug Stripped Ends	C14 CN1 SE	RVV	RVV	3x1.00mm ²	3100	250VAC 10A	200 cm	200	Black Blue Orange Red White	- B O R W	CCC
IL13P	IEC C13 + Female plug, straight, lock	IEC C14, male, straight Indian plug 3 Pin Stripped Ends	C14 IN1 SE						200 cm	200	Black Blue Orange Red White	- B O R W	CB

*feet values are calculated to the matching length in cm

Cable selection table IL 19

IL 19-C20-H05-3150-X*	IEC cable assembly with locking system for IEC C20 inlet, EU version
IL 19-C20-SJT-3160-X*	IEC cable assembly with locking system for IEC C20 inlet, US version
IL 19-EU1-H05-3150-X*	IEC cable assembly with locking system for IEC C20 inlet, EU version
IL 19-SE-H05-3150-X*	IEC cable assembly with locking system for IEC C20 inlet, stripped ends
IL 19-UK1-H05-3150-X*	IEC cable assembly with locking system for IEC C20 inlet, UK version
IL 19-US1-SJT-3160-X*	IEC cable assembly with locking system for IEC C20 inlet, US version

To compile a complete part number, please replace the X* with the required length (please refer to table below for available length per cable type):
- X* options = 200, 300, 400, 500 or 1000 cm; 183, 275 or 366 cm (6, 9 or 12 feet)

Available combinations IL 19

To compile a complete part number exchange the letters (IL19-yyy-zzz-aaaa-bbb-c) with the data from the table below.

Load side IL19		Line side plug		Cable type		Cable core		Rating*	Cable length**		Cable color		Cert.
IL19		yyy		zzz		aaaa			bbb		c		
IL19	IEC C19 Female plug, straight, lock	IEC C20, male, straight Australian plug 3 pins SEV1011, straight CEE 7/VII, right angled or straight Italian Plug South Africa plug Stripped Ends BS1363, right angled fused 13A	C20	H05VV-F	H05	3x1.50mm²	3150	16A	6 feet	183	Black Blue Orange Red White	- B O R W	CB KEMA SAA
			AU1					15A	200 cm	200			
			CH1					16A	9 feet	275			
			EU1					16A	300 cm	300			
			IT1					16A	12 feet	366			
			SA1					16A	400 cm	400			
			SE					16A	500 cm	500			
IL19	IEC C19 Female plug, straight, lock	IEC C20, male, straight Japanese Plug JIS C8303 insulated sleeves Stripped Ends	C20	HVCTF	HVCTF	3x2.00mm²	3200	15A	100 cm	100	Black Blue Orange Red White	- B O R W	PSE
			JP1						200 cm	200			
			SE						300 cm	300			
									400 cm	400			
									500 cm	500			
IL19	IEC C19 Female plug, straight, lock	IEC C20, male, straight Stripped Ends NEMA5-15, straight Nema 5-20P	C20	SJT SVT	SJT SVT	AWG14 AWG12	3160 3205	125V	6 feet	183	Black Blue Orange Red White	- B O R W	UL cUL
			SE					15A	200 cm	200			
			US1					20A	9 feet	275			
			US4						300 cm	300			
									12 feet	366			
									400 cm	400			
									500 cm	500			
IL19	IEC C19 Female plug, straight, lock	Chinese plug	CN1	RVVF	RVVF	3x1.50mm²	3150	16A	200 cm	200	black	-	CCC

* if not seperately mentioned 250VAC is rated voltage
** feet values are calculated to the matching length in cm



Headquarters, global innovation and development

Switzerland

Schaffner Group

Industrie Nord
Nordstrasse 11e
4542 Luterbach
T +41 32 681 66 26
info@schaffner.com



Sales and application centers

China

Schaffner EMC Ltd. Shanghai

T20-3 C, No 565 Chuangye Road,
Pudong district
201201 Shanghai
T +86 21 3813 9500
cschina@schaffner.com
www.schaffner.com.cn

Finland

Schaffner Oy

Sauvonrinne 19 H
08500 Lohja
T +358 50 468 7284
finlandsales@schaffner.com

France

Schaffner EMC S.A.S.

16-20 Rue Louis Rameau
95875 Bezons
T +33 1 34 34 30 60
F +33 1 39 47 02 28
francesales@schaffner.com

Germany

Schaffner Deutschland GmbH

Schoemperlenstrasse 12B
76185 Karlsruhe
T +49 721 56910
germanysales@schaffner.com

India

Schaffner India Pvt. Ltd

REGUS WORLD TRADE CENTRE
WTC, 22nd Floor Unit No 2238, Brigade
Gateway Campus, 26/1, Dr. Rajkumar Road
Malleshwaram (W)
560055 Bangalore
T +91 80 67935355
indiasales@schaffner.com

Italy

Schaffner EMC S.r.l.

Via Ticino, 30
20900 Monza (MB)
T +39 039 21 41 070
italysales@schaffner.com

Japan

Schaffner EMC K.K.

Taiju-Seimei Sangenjaya Bldg.
1-32-12, Kamiuma, Setagaya-ku
154-0011 Tokyo
T +81 3 5712 3650
F +81 3 5712 3651
japansales@schaffner.com
www.schaffner.jp

Singapore

Schaffner EMC Pte Ltd.

#05-09, Kg Ubi Ind. Estate
408705 Singapore
T +65 6377 3283
F +65 6377 3281
singaporesales@schaffner.com

Spain

Schaffner EMC España

Calle Caléndula 93, Miniparc III, Edificio E
El Soto de Moraleja, Alcobendas
28109 Madrid
T +34 917 912 900
F +34 917 912 901
spainsales@schaffner.com

Sweden

Schaffner EMC AB

Östermalmstorg 1
114 42 Stockholm
T +46 8 5050 2425
swedensales@schaffner.com
www.schaffner.com

Switzerland

Schaffner EMV AG

Industrie Nord
Nordstrasse 11e
4542 Luterbach
T +41 32 681 66 88
T +41 32 681 66 26
switzerlandsales@schaffner.com

Taiwan

Schaffner EMV Ltd.

20 Floor-2, No 97, Section 1, XinTai 5th Road
22175 XiZhi District New Taipei City 22175
T +886 2 2697 5500
F +886 2 2697 5533
taiwansales@schaffner.com
www.schaffner.com.tw

Thailand

Schaffner EMC Co. Ltd.

Northern Region Industrial Estate
67 Moo 4 Tambon Ban Klang
Amphur Muangng P.O. Box 14
51000 Lamphun
T +66 53 58 11 04
F +66 53 58 10 19
thailandsales@schaffner.com

United Kingdom

Schaffner Ltd.

1, Oakmede Place
Binfield
RG42 4JF Berkshire
T +44 118 9770070
F +44 118 9792969
uksales@schaffner.com

USA

Schaffner EMC Inc.

52 Mayfield Avenue
Edison, New Jersey
T +1 732 225 9533
F +1 732 225 4789
usasales@schaffner.com
www.schaffnerusa.com

To find your local partner within Schaffner's global network: www.schaffner.com

© 2021 Schaffner Group

The content of this document has been carefully checked and understood. However, neither Schaffner nor its subsidiaries assume any liability whatsoever for any errors or inaccuracies of this document and the consequences thereof. Published specifications are subject to change without notice. Product suitability for any area of application must ultimately be determined by the customer. In all cases, products must never be operated outside their published specifications. Schaffner does not guarantee the availability of all published products. This disclaimer shall be governed by substantive Swiss law and resulting disputes shall be settled by the courts at the place of business of Schaffner Holding AG. Latest publications and a complete disclaimer can be downloaded from the Schaffner website. All trademarks recognized.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Schaffner:

[IL13-C14-SVT-3100-183](#) [IL13-EU1-H05-3100-200](#) [IL13-US1-SVT-3100-183](#) [IL13-UK1-H05-3100-200](#) [IL13-US2-SJT-3100-183](#) [IL13-US2-SJT-3100-275](#) [IL13-US2-SJT-3100-366](#) [IL13-EU1-H05-3100-300](#) [IL19-C20-H05-3150-200](#) [IL19-US1-SJT-3160-183](#) [IL13P-US1-SJT-3160-275](#) [IL19-UK1-H05-3150-200](#) [IL19-EU1-H05-3150-200](#) [IL13-EU1-H05-3100-400](#) [IL13-SE-H05-3100-500](#) [IL13P-US1-SJT-3160-366](#) [IL19-SE-H05-3150-200](#) [IL19-C20-SJT-3160-183](#) [IL13-US1-SVT-3100-366](#) [IL13P-US1-SJT-3160-183](#) [IL13-US1-SVT-3100-275](#) [IL13-C14-H05-3100-200](#) [IL13P-CH1-H05-3100-200](#) [IL13-BR1-H05-3100-100](#) [IL13-BR1-H05-3100-200](#) [IL13-SE-H05-3100-200](#) [IL13P-US1-SVT-3100-183](#) [IL13-C14-SJT-3100-300](#) [IL13-JP1-HVCTF-3125-200](#) [IL13-CH1-H05-3100-200](#) [IL13-JP1-IS-HVCTF-3125-200](#) [IL13P-EU1-H05-3100-300](#) [IL13P-R-US1-SVT-3100-275](#) [IL13P-U-CH1-H05-3100-300](#) [IL13P-U-EU1-H05-3100-300](#) [IL13P-U-EU2-H05-3100-300](#) [IL13P-U-US1-SJT-3160-300](#) [IL13P-U-US2-SJT-3160-300](#) [IL13P-D-UK1-H05-3100-300](#) [IL13P-D-US1-SJT-3160-300](#) [IL13P-D-CH1-H05-3100-300](#) [IL13P-D-SA1-H05-3100-300](#) [IL13P-D-EU1-H05-3100-300](#) [IL13P-D-US2-SJT-3160-300](#)