




Product availability: Stock - Normally stocked in distribution facility



Main

Range of product	8501X
Relay type	Control relay
Product or component type	Adder deck

Complementary

Rated breaking capacity	6 A at: 120 V AC for: inductive load control circuit per UL 508 3 A at: 240 V AC for: inductive load control circuit per UL 508 1.5 A at: 480 V AC for: inductive load control circuit per UL 508 1.2 A at: 600 V AC for: inductive load control circuit per UL 508 10 A at: <= 600 V AC for: resistive load control circuit per UL 508 1.1 A at: 125 V DC for: inductive load control circuit per UL 508 0.55 A at: 250 V DC for: inductive load control circuit per UL 508 0.2 A at: 301...600 V DC for: inductive load control circuit per UL 508 4 A at: 125 V DC for: resistive load control circuit per UL 508 0.8 A at: 250 V DC for: resistive load control circuit per UL 508
[Icm] rated short-circuit making capacity	60 A at: 120 V AC for: inductive load control circuit per UL 508 30 A at: 240 V AC for: inductive load control circuit per UL 508 15 A at: 480 V AC for: inductive load control circuit per UL 508 12 A at: 600 V AC for: inductive load control circuit per UL 508 10 A at: <= 600 V AC for: resistive load control circuit per UL 508 1.1 A at: 125 V DC for: inductive load control circuit per UL 508 0.55 A at: 250 V DC for: inductive load control circuit per UL 508 0.2 A at: 301...600 V DC for: inductive load control circuit per UL 508 4 A at: 125 V DC for: inductive load control circuit per UL 508 0.8 A at: 250 V DC for: resistive load control circuit per UL 508
Contacts Configuration	2 NO 2 standard contact cartridges
Electrical connection	Screw clamp terminals
Wire Gauge	AWG 18...AWG 12 copper
Terminal Tightening Torque	1.02...1.36 N.m control circuit screw terminals


Environment

Product certifications	CE UL recognized E78403 CCN NKCR2 CSA LR60905 class 3211 02
------------------------	---

Ordering and shipping details

Category	21159 - 8501 X ACCESSORIES
Discount Schedule	CP2
GTIN	00785901537335
Nbr. of units in pkg.	1
Package weight(Lbs)	0.5100000000000001
Returnability	Y
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1332 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[8501XB20](#)