

Product availability: Non-Stock - Not normally stocked in distribution facility



### Main

Range of product	9007
Series name	Severe duty mill
Product or component type	Limit switch
Device application	Universal mill switch
Device short name	9007T/FT
Body type	Fixed
Head type	Rotary head
Sale per indivisible quantity	1

### Complementary

Base plate style	Style B
Body material	Cast zinc
Fixing mode	By the body
Movement of operating head	Rotary
Type of operator	Stay put without operating lever
Contact sequence number	7
Function available	-
Switch actuation	From left or right CW and CCW
Type of approach	Lateral approach
Electrical connection	Screw-clamp terminals AWG 22...AWG 12
Cable entry	1 entry for M20 - 20 mm BS 4568
Number of poles	1
Switch function	SPDT-DB
Contact form	Form Z
Contact operation	Snap action
Contacts usage	Maintained
Contacts material	Silver flashed copper
Positive opening	Without
Minimum torque for tripping	2.5 lbf.in
Maximum actuation speed	90 ft/min with 45° cam angle, levers only 130 ft/min with 30° cam angle, levers only
Tripping angle	10 °
Maximum displacement angle	85 °
Repeat accuracy	+/- 0.004 in linear travel of cam on 1.5 in lever arm
Contact code designation	A600 480 V AC 6.25 A NEMA rating designation A600 240 V AC 12.5 A NEMA rating designation A600 120 V AC 20 A NEMA rating designation P600 600 V DC 0.2 A NEMA rating designation P600 250 V DC 1 A NEMA rating designation P600 120 V DC 5 A NEMA rating designation A600 600 V AC 5 A NEMA rating designation
[Ithe] conventional enclosed thermal current	20 A
[Ui] rated insulation voltage	600 V 3 IEC 609470-1 600 V 3 UL 508 600 V 3 CSA C22.2 No 14

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

[Uimp] rated impulse withstand voltage	2.5 kV AC for 1 minute CE 2.2 kV AC for 1 minute UL 2.64 kV AC for 1 minute CSA
Short-circuit protection	20 A Bussmann class CC KTK-R-21 fuse non-time delay
Width	2.25 in
Height	4.66 in
Depth	2.44 in
Product weight	2.5 lb(US)
Terminals description ISO n°1	A (left side contact) B (right side contact)

## Environment

Shock resistance	30 gn 9 ms IEC 60068-2-27
Vibration resistance	10 gn 10...55 Hz IEC 60068-2-6
NEMA degree of protection	NEMA 1 Nema type 250 NEMA 2 Nema type 250 NEMA 4 Nema type 250 NEMA 12 Nema type 250 NEMA 13 Nema type 250
IP degree of protection	IP67 IEC 60529
Electrical shock protection class	Class 0 IEC 61140
Ambient air temperature for operation	-10...185 °F
Ambient air temperature for storage	-10...185 °F
Protective treatment	Corrosion resistant gray paint

## Ordering and shipping details

Category	21497 - 9007 FT,T OILTIGHT AND FOUNDRY
Discount Schedule	DS1
GTIN	00785901169284
Nbr. of units in pkg.	1
Package weight(Lbs)	2.5
Returnability	N
Country of origin	MX

## Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[9007TUB7M11](#)