



## Overview

Lead time	Usually in Stock
-----------	------------------

## General

Provided equipment	User Manual
Performance multiplier	1
Number of tare power	13 W
Number of power module free slots	0
Number of power module filled slots	0
Redundant	No
Size UPS version	Workstation
UPS size	WS
Value multiplier	1

## Physical

Cable length	5 ft (1.52 m)
Color	Charcoal
Depth	11.34 in (28.8 cm)
Height	3.46 in (8.8 cm)
Mounting preference	No preference
Net Weight	9.04 lb(US) (4.1 kg)
Mounting Mode	Not rack-mountable
Two post mountable	0
USB compatible	No
Width	6.30 in (16 cm)

## Input

Input Frequency	50/60 Hz +/- 3 Hz auto-sensing
Plug standard	NEMA 5-15P
Efficiency at full load	88...139 V
Number of cables	1
Nominal Input Voltage	120 V

## Output

Kw Rating	200 W
Max Configurable Power (Watts)	200 W
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains
Topology	Standby
Waveform Type	Stepped approximation to a sinewave
Nb of power socket outlets	3 NEMA 5-15R 3 NEMA 5-15R surge
Curve equation	Efficiency
Curve fixed loss	0.0078
Curve load maximum	100 %
Curve load minimum	1 %
Curve proportional loss	0
Curve square loss	0.0019
Curve X-axis maximum	100 %
Curve test cond ID	Curve fit of data measured in accordance with the US DOE Test Procedure for Uninterruptible Power Supplies. All measurements taken in normal mode(s), at typical environmental conditions, with 120V/60Hz electrical input and balanced resistive load (PF = 1.0) output.
Curve X-axis minimum	0 %
Curve X-axis title	Load
Curve X-axis units	Percentage
Curve Y-axis maximum	100 %
Curve Y-axis minimum	50 %
Curve Y-axis title	Efficiency
Curve Y-axis units	Percentage
Graph display	1
Output voltage	120 V
Maximum configurable power in VA	350 VA
Rated power in VA	350 VA
Transfer Time	8ms typical : 12ms maximum

## Conformance

Product Certifications	CUL Listed California (CEC) Battery Charger NOM
Standards	FCC Part 15 class B FCC part 68 UL 497A UL 498 UL 1778
Equipment protection policy	Lifetime : \$75000

## Environmental

Ambient air temperature for operation	32...104 °F (0...40 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)
Acoustic level	45 dBA
Heat dissipation	14 Btu/h
Show note OP temperature	No

## Batteries & Runtime

Battery Type	Lead-Acid battery
Battery Slots Empty	0
Typical recharge time	16 h
RBC Quantity	1
Liquid Electrolyte Value	0
Battery curve	C
Battery Charge Power (Watts)	2 W rated
Battery power in VAH	31 VAh runtime
Battery life	3...5 year(s)
Battery graph comments	This graph is based on actual measured runtime data. All measurements were taken with new, fully charged batteries and a balanced resistive load (PF = 1.0). Actual runtimes may vary from the values of this graph. Actual runtimes are dependent on several variables including battery age, battery charge level, environmental conditions and characteristics of the connected load.
Extendable Run Time	0

## Communications & Management

Control panel	LED status display with On Line : On Battery : Replace Battery and Building Wiring Fault
Audible Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm

## Surge Protection and Filtering

Surge energy rating	365 J
Filtering	Full time multi-pole noise filtering : 5% IEEE surge let-through : zero clamping response time : mee
Data line protection	RJ45 10/100 Base-T Ethernet protection





## Ordering and shipping details

Category	11309 - APC RESALE PRODUCTS
GTIN	00785901258902
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	PH

## Packing Units

Package 1 Height	5.04 in (12.8 cm)
Package 1 width	7.99 in (20.3 cm)
Package 1 Length	14.61 in (37.1 cm)
SCC14	10731304258909
Number of Units in Package 2	2
Package 2 Weight	21.12 lb(US) (9.58 kg)
Package 2 Length	15 in (381.00 mm)
Number of Units in Package 3	72

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>

---

Circularity Profile	<a href="#">End Of Life Information</a>
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

---

### Contractual warranty

---

Warranty	3 years repair or replace
----------	---------------------------

---

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[BE350G](#)