


Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range of product	Linergy
Product or component type	Cable end
Cable end size	Medium
Standards	NF C 63-023
Type of packing	Dispenser pack
Quantity per set	5 sets of 100
Cable cross section	0 in ² (1.5 mm ²)

Complementary

Cable end type	Twin conductor
Additional information	Without marker tag holder
Color	Black
Bezel material	Halogen-free plastic
Tube material	Copper conforming to ISO 1337
Number of cables	2
AWG gauge	AWG 16
Bezel size	Ø 3.6 x 6.6 mm
Tube diameter	0.1 in (2.5 mm)
Length	0.59 in (15 mm)
Tube length	0.31 in (8 mm)
Product weight	0.34 lb(US) (0.155 kg)


Environment

Product certifications	CCSAus
Ambient air temperature for operation	-4...221 °F (-20...105 °C)

Ordering and shipping details

Category	22621 - IEC PANEL ACCESSORIES
Discount Schedule	I
GTIN	00785901112891
Nbr. of units in pkg.	500
Package weight(Lbs)	0.01
Returnability	N
Country of origin	DE

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0440 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[AZ5DE015](#)