

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range of product	OsiSense XU
Series name	Application assembly
Specific application of photoelectric detector	Detection of reference and colour marks in packaging Use of fiber optics in vibratory environments (robot arms) Monitoring position or presence of parts on an assembly or packing machine Detection of objects on small conveyor
Sensor name	XUY
Sensor design	Fiber design
Emission	Red LED

Complementary

Electronic sensor type	Photo-electric sensor
Material	Plastic
Enclosure material	Polycarbonate
Pulse frequency	8 kHz
Type of output signal	Discrete
Output type	Solid state
Discrete output function	1 NO or 1 NC programmable
Discrete output type	PNP and NPN
Electrical connection	1 male connector M8, 4 pins
Cable length	6.56 ft (2 m)
Supply circuit type	DC
[Us] rated supply voltage	12...24 V DC with reverse polarity protection
Supply voltage limits	10...30 V DC
Voltage state 0 guaranteed	< 1.4 V
Voltage state 1 guaranteed	> 3 V
Switching capacity in mA	100 mA for overload and short-circuit protection
Switching frequency	< 1 kHz
Voltage drop	< 2 V (closed state)
Current consumption	<= 40 mA (no-load)
Delay response	<= 5 ms for plastic fibre optics 2.2 mm
Delay recovery	<= 5 ms for plastic fibre optics 2.2 mm
Setting-up	Sensitivity adjustment with teach mode
Product weight	0.12 lb(US) (0.056 kg)

Environment

Product certifications	CULus CE
Ambient air temperature for operation	32...140 °F (0...60 °C)
Ambient air temperature for storage	-4...176 °F (-20...80 °C)
Immunity to ambient light	<= 10000 lux with natural light <= 20000 lux with incandescent bulb
IP degree of protection	IP65 conforming to IEC 60529

Ordering and shipping details

Category	22481 - SENSORS, PHOTOELECTRIC
Discount Schedule	DS2
GTIN	003389119010009
Nbr. of units in pkg.	1
Package weight(Lbs)	0.12
Returnability	N
Country of origin	FR

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0706 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XUYAFPCO946S](#)